56 Sparta Avenue • Newton, New Jersey 07860 (973) 300-3000 Sales • (973) 300-3600 Fax www.thorlabs.com




# S40R - April 27, 2018

Item # S40R was discontinued on April 27, 2018. For informational purposes, this is a copy of the website content at that time and is valid only for the stated product.

# MOUNTED OPTICAL SLITS

- ▶ 12 Slit Widths Available Ranging from 5-200 µm
- Ø1" Housing is SM1 Compatible
- High Damage Threshold



Hide Overview

#### OVERVIEW

#### **Optical Slit Dimensions & Material**

- Slit Widths Available: 5 200 µm (See Table to Right for Details)
- Slit Length: 3 mm
- Slit Thickness: 12.7 µm
- Housing: Aluminum or Black Stainless Steel with Ø1" Outer Diameter x 0.10" Thick
- Slit Material: 302 Stainless Steel w/ Black Oxide Finish
- Unmounted Slit: Ø3/8" (9.5 mm) x 0.0005" (12.8 μm) Thick
- Position Tolerance of Slit: Ø0.006" (Ø0.15 mm) within the Foil Disk

### **Damage Thresholds**

- 5x10<sup>4</sup> W/mm<sup>2</sup>, 75 ns Pulse @ 700 nm
- 1x10<sup>5</sup> W/mm<sup>2</sup>, 10 ns Pulse @ 700 nm
- 1x10<sup>3</sup> W/mm<sup>2</sup>, CW @ 10.6 μm

Item # Slit Width Tolerance **Housing Material** S5RH 5 µm ±1 μm **Black Stainless Steel** S10RH 10 µm ±1 µm S15R 15 µm ±1 µm Aluminum S20RH 20 µm ±2 μm Black Stainless Steel S30RH 30 µm ±2 μm **S40**R 40 µm ±2 μm Aluminum S50RH 50 µm ±2 µm Black Stainless Steel S100RH 100 µm ±4 μm S150R 150 µm ±4 µm Aluminum S200RH 200 µm ±4 μm **Black Stainless Steel** 

These optical slits are mounted in a Ø1" plate, perfect for mounting in our SM1-series lens tubes (SM1L03). The slit in the foil disk is not necessarily aligned horizontally or vertically during the assembly process.

If you do not see what you need in our stocked offerings below, it is possible to special order slits that are fabricated from different substrate materials, have different slit sizes, incorporate multiple slits in one foil, or provide different slit configurations. Customized housings are also available. Please contact Technical

#### Hide Mounted Optical Slits

## **Mounted Optical Slits**

Part Number	Description	Price	Availability
S5RH	NEW! Ø1" Mounted Slit, 5 $\pm$ 1 $\mu m$ Wide, 3 mm Long	\$116.00	Today
S15R	Ø1" Mounted Slit, 15 ± 1 $\mu$ m Wide, 3 mm Long	\$104.00	Lead Time
S10RH	NEW! Ø1" Mounted Slit, 10 ± 1 µm Wide, 3 mm Long	\$110.00	Today
S20RH	Ø1" Mounted Slit, 20 ± 2 μm Wide, 3 mm Long	\$110.00	Today
S30RH	NEW! Ø1" Mounted Slit, 30 ± 2 µm Wide, 3 mm Long	\$101.00	Today
S40R	Ø1" Mounted Slit, 40 ± 2 μm Wide, 3 mm Long	\$95.75	Lead Time
S50RH	NEW! Ø1" Mounted Slit, 50 ± 2 µm Wide, 3 mm Long	\$95.75	Today
S100RH	NEW! Ø1" Mounted Slit, 100 ± 4 μm Wide, 3 mm Long	\$95.75	Today
S150R	Ø1" Mounted Slit, 150 ± 4 µm Wide, 3 mm Long	\$95.75	Today
S200RH	Ø1" Mounted Slit, 200 ± 4 µm Wide, 3 mm Long	\$95.75	Today

