



## WARNING ATENCIÓN

**WARNING:** Contains gas under pressure; may explode if heated. Protect from sunlight. Store in a well-ventilated place.

**ATENCIÓN:** Contiene gas a presión; puede explotar si se calienta. Proteger de la luz solar. Almacenar en un lugar bien ventilado.

### FOR PROFESSIONAL OR INDUSTRIAL USE ONLY.

Techspray, EcoLine, TechBrush and the Techspray design logo are trademarks of Techspray.

### ÚNICAMENTE PARA USO PROFESIONAL O INDUSTRIAL.

Techspray, EcoLine, TechBrush y el logotipo de Techspray son marcas de Techspray.

**DIRECTIONS: CAUTION:** Can must be held in an upright position when spraying. Do not tilt can more than 40 degrees during spraying operation or shake during use. Before use, press actuator to clear valve of any liquid product. Use short burst to prevent cooling of can. Note: Do not use on photographic negatives without first clearing valve.

### CHEMICAL COMPONENTS (CAS No.)

Trans-1,3,3,3-Tetrafluoropropene- HFO-1234ze (29118-24-9)

24-Hour Emergency Phone  
24 Heures Numéro D'appel Téléphonique D'urgence  
24 Horas Número De Teléfono Para Llamada De Urgencia:  
(800) 424-9300 or/ou/ó +1 703-527-3887



8125 Cobb Center Dr., Kennesaw, GA 30152  
800-858-4043 | www.techspray.com  
Assembled in USA with U.S. and imported Components.  
DOT 2Q



## ECO-DUSTER 1580-10S

**Precautions:** Avoid contact with eyes or skin. Wear gloves and eye protection. Do not breathe fumes, vapours or spray mist released from this product. If ventilation is insufficient, wear suitable respiratory protection. Avoid heating of aerosol containers. Do not use near heat or ignition source. Do not use in a closed space. Firefighters must wear self-contained breathing apparatus. Seek medical attention for adverse effects due to exposure.



### FIRST AID

**Eye contact:** Flush with water for at least 20 minutes with eyelids held open during flushing.

**Skin contact:** Wash well with soap and water. For frostbite, seek immediate medical attention.

**Inhalation:** Remove victim to fresh air, support breathing if required.

**Ingestion:** If conscious, give 2 glasses of water. Do not induce vomiting. Get medical attention immediately. **Note:** Adrenaline and other similar stimulants should NOT be used for treatment.

**Précautions:** Éviter tout contact avec les yeux ou la peau. Porter des gants et un dispositif de protection des yeux. Éviter de respirer les fumées, vapeurs ou les jets de pulvérisation. Si la ventilation est insuffisante, porter un appareil respiratoire approprié. Éviter de chauffer les contenants. Ne pas utiliser à proximité de chaleur ou d'une source d'inflammation. Ne pas utiliser dans un espace fermé. Les pompiers doivent porter un appareil respiratoire autonome. Consulter un médecin en cas d'effets contraires suite à l'exposition.

### PREMIERS SOINS

**Contact avec les yeux:** Laver à grande eau pendant 20 minutes en gardant les paupières ouvertes.

**Contact avec la peau:** Bien laver la peau avec de l'eau et du savon. En cas de gelures, procurer immédiatement des soins médicaux.

**Inhalation:** Placer la personne incommodée au grand air, pratiquer la respiration artificielle au besoin.

**Ingestion:** Si la personne est consciente, lui faire boire 2 verres d'eau. La faire vomir seulement aux instructions d'un médecin. Consulter immédiatement un médecin. **Note:** NE PAS utiliser d'adrénaline ni d'autres stimulants pour le traitement.

SEE MATERIAL SAFETY DATA SHEET FOR THIS PRODUCT  
VOIR LA FICHE SIGNALÉTIQUE DE CE PRODUIT



# TECHSPRAY RENEW™

HIGH PERFORMANCE ECO-CLEANING™

# RENEW-DUSTER ULTRA PURE DUSTER

## 1580-10S

Net Wt.: 10 wt. oz. (284 grams)

- Non-Flammable
- Low Global Warming Potential
- Non-Ozone Depleting

### CAUTION/ATTENTION

CONTAINER MAY EXPLODE IF HEATED  
CE CONTENANT PEUT EXPLOSER S'IL EST CHAUFFÉ  
READ CAUTIONS ON BACK PANEL.  
LISEZ LES ATTENCTIONS SUR LE PANNEAU ARRIÈRE.  
ENERGIZED EQUIPMENT USE ONLY



SPECS • MSDS

RoHS Compliant

Low GWP