



DIVERSIFIED
TESTING LABORATORIES, INC.
WORLDWIDE SERVICE

“We Test Per Your Request”

336 WEST FRONT STREET
P.O. BOX 4004
BURLINGTON, NORTH CAROLINA 27215
PHONE (336) 227-7710 • FAX (336) 227-1175
www.diversifiedtestinglabs.com

May 29, 2024

THORLABS LTD.
204 Lancaster Way Business Park
Ely, Cambridgeshire CB6 3NX
United Kingdom

Reference: Laboratory Test Report
Lab Identification No. 59873
Invoice No. 91213

One (1) sample, identified as **R&DTABLES – Rubberized Thorlabs Protective Material**, was received and tested in accordance with the Classification Fire Test: BFD IX-1 issued by the Office of Fire Marshal of the Boston Fire Department (Revised 5/03). The results are as follows:

Test Results

<u>Specimen Number</u>	<u>After Flame (sec)</u>		<u>After Glow (sec)</u>		<u>Char Length (in)</u>	
	<u>Length</u>	<u>Width</u>	<u>Length</u>	<u>Width</u>	<u>Length</u>	<u>Width</u>
1	0.0	0.0	0.0	0.0	3.3	3.2
2	0.0	0.0	0.0	0.0	3.5	3.3
3	0.0	0.0	0.0	0.0	3.2	3.6
Avg.						3.4

The sample submitted **meets** the minimum requirements of the above standard. After flame shall not exceed two seconds. Flame propagation (char length) and after flame shall not extend beyond six inches from the bottom edge of the specimen. Propagating afterglow shall not exceed forty seconds; non-propagating afterglow in the charred area shall not exceed eighty seconds.

Sincerely,

Brian S. Dement

BSD/mr

