

Scan Report

Single Fiber - IEC PC 2.50 mm



SC-PC3

Date & Time of Scan: Thu, Aug 15, 2019 11:50 PM
Username: admin

Connector ID: SC-PC3

Product ID: MCS101-1

Result: PASS



PASS/FAIL MEASUREMENTS

Parameter	Min	Max	Value	Result
Radius of Curvature (mm)	5	30	24.681	Pass
Fiber Height (nm)	-92.479	100	40.072	Pass
Apex Offset (um)	0	70	12.034	Pass

Thorlabs Inc.

56 Sparta Avenue
Newton, NJ 07860
USA

Tel: 1-973-300-3000

Fax: 1-973-300-3600

Web: thorlabs.com

Operator ID:
Operator1

ADDITIONAL MEASUREMENTS

Parameter	Value
Apex Offset X (um)	11.484
Apex Offset Y (um)	-3.597

Sample Parameters

Sample Name:
PC Connector

Product Type:
Standard Connector

Fiber Diameter:
126

Nominal Y-Angle:
0

Ferrule Type:
Ceramic