

For current pricing, please see our website.

Updated 2/1/12 LF

CHAPTERS

Fiber Patch Cables

Bare Fiber

Fiber Optomechanics

Fiber Components

Test and Measurement

SECTIONS

SM Patch Cables

PM Patch Cables

MM Patch Cables

Fiber Bundles





Multimode Patch Cables: SMA to SMA



M28L01

Features

- Shipped from Stock
- SMA 905 Connectors on Both Ends
- Step-Index Multimode Fiber
- Ø3 mm or Ø3.8 mm Reinforced Outer Jacket
- Custom Cables Available with Same-Day Turnaround



ITEM #	CORE	NA	LENGTH	\$	£	€	RMB	STBR ^a	LTBR ^b	FIBER	JACKET ^c
M14L01	Ø50 µm	0.22	1 m	\$ 45.50	£ 32.76	€ 39.59	¥ 362.64	12 mm	24 mm	AFS50/125Y (Page 1057)	FT030
M14L02			2 m	\$ 51.70	£ 37.22	€ 44.98	¥ 412.05				
M14L05			5 m	\$ 70.10	£ 50.47	€ 60.99	¥ 558.70				
M15L01	Ø105 µm	0.22	1 m	\$ 48.10	£ 34.63	€ 41.85	¥ 383.36	12 mm	24 mm	AFS105/125Y (Page 1057)	FT030
M15L02			2 m	\$ 52.90	£ 38.09	€ 46.02	¥ 421.61				
M15L05			5 m	\$ 67.80	£ 48.82	€ 58.99	¥ 540.37				
M25L01	Ø200 µm	0.22	1 m	\$ 84.00	£ 60.48	€ 73.08	¥ 669.48	9 mm	18 mm	FG200LCC (Page 1058)	FT030
M25L02			2 m	\$ 90.00	£ 64.80	€ 78.30	¥ 717.30				
M25L05			5 m	\$ 108.00	£ 77.76	€ 93.96	¥ 860.76				
M38L01	Ø200 µm	0.39	1 m	\$ 62.90	£ 45.29	€ 54.72	¥ 501.31	9 mm	18 mm	FT200EMT (Page 1061)	FT030
M38L02			2 m	\$ 65.70	£ 47.30	€ 57.16	¥ 523.63				
M28L01			1 m	\$ 80.00	£ 57.60	€ 69.60	¥ 637.60				
M28L02	Ø400 µm	0.39	2 m	\$ 85.00	£ 61.20	€ 73.95	¥ 677.45	20 mm	40 mm	FT400EMT (Page 1061)	FT030
M28L05			5 m	\$ 97.00	£ 69.84	€ 84.39	¥ 773.09				
M40L01			1 m	\$ 64.90	£ 46.73	€ 56.46	¥ 517.25				
M40L02	Ø400 µm	0.48	2 m	\$ 69.70	£ 50.18	€ 60.64	¥ 555.51	22 mm	65 mm	BFL48-400 (Page 1062)	FT030
M37L01			1 m	\$ 93.60	£ 67.39	€ 81.43	¥ 745.99				
M37L02	Ø550 µm	0.22	2 m	\$ 136.00	£ 97.92	€ 118.32	¥ 1,083.92	30 mm	60 mm	FG550LEC (Page 1058)	FT038
M29L01	Ø600 µm	0.39	1 m	\$ 89.00	£ 64.08	€ 77.43	¥ 709.33	30 mm	60 mm	FT600EMT (Page 1061)	FT038
M29L02			2 m	\$ 99.00	£ 71.28	€ 86.13	¥ 789.03				
M29L05			5 m	\$ 108.00	£ 77.76	€ 93.96	¥ 860.76				
M41L01	Ø600 µm	0.48	1 m	\$ 68.60	£ 49.39	€ 59.68	¥ 546.74	32 mm	95 mm	BFL48-600 (Page 1062)	FT038
M41L02			2 m	\$ 77.10	£ 55.51	€ 67.08	¥ 614.49				
M35L01			1 m	\$ 83.20	£ 59.90	€ 72.38	¥ 663.10				
M35L02	Ø1000 µm	0.39	2 m	\$ 106.40	£ 76.61	€ 92.57	¥ 848.01	50 mm	100 mm	FT1000EMT (Page 1061)	FT038

NEW
NEW

NEW
NEW

^aShort-Term Bend Radius

^bLong-Term Bend Radius

^cSee Page 1151