

DFMB - Feb. 19, 2016

Item # DFMB was discontinued on Feb. 19, 2016. For informational purposes, this is a copy of the website content at that time and is valid only for the stated product.

30 MM CAGE-COMPATIBLE FLUORESCENCE FILTER CUBE

- ► Holds Two Fluorescence Filters and One Dichroic Mirror
- ▶ 30 mm Cage System and Ø1" Lens Tube Compatible
- ► Quickly Interchange Between Filters with Repeatable Alignment



DFM



Hide Overview

Features

Prealigned
 Fluorescence Filter
 Holder Within a 30
 mm Cage Cube

Maximum Filter Thicknesses		
Excitation	5 mm	
Emission	3.5 mm	
Dichroic	1.1 mm	

Fluorescence filter sets can be easily mounted in the DFM filter Cube (filters sold separately).

- Swap Between Fluorescence Filter Sets Using Additional DFMT1 Tops
- · Kinematic Design Provides Repeatable Alignment
- · Compatible with 30 mm Cage and SM1 Lens Tube Systems
- Cubes with Premounted Filter Sets Available Upon Request



Click to Enlarge Each filter cube holds a fluorescence filter set: one dichroic mirror, one excitation filter, and one emission filter.

Thorlabs' DFM Fluorescence Filter Cube is designed to hold a fluorescence filter set (dichroic mirror, excitation filter, and emission filter) in a 30 mm cage-compatible cube for home-built microscopy setups. The light-tight filter cube consists of a base and top lid with an insert to hold filter set components. The kinematic design allows for easy swapping between mounted filter sets without requiring realignment. The DFM includes one DFMT1 top piece for mounting a filter set; DFMT1 tops for mounting additional filter sets are sold separately below.

mirror, one excitation filter, and one emission filter.

The base unit (DFMB) has four SM1-threaded (1.035"-40) ports for compatibility with our smission filter.

SM1 lens tubes. Four 4-40 tapped holes surround each port for compatibility with our 30 smillers.

Click to Enlarge DFM Dichroic Filter Cube Employed in a Confocal Microscope (All Parts Sold Separately)

mm cage system. The bottom surface contains an 1/4"-20 (M6) tap that is directly compatible with our Ø1" posts or Ø1.5" posts. For details on all of the mechanical features, please see the *Diagrams* tab.

As shown in the animation to the right, the top with insert (DFMT1) is designed to hold a 25 mm x 36 mm dichroic mirror and two Ø25 mm filters (excitation and emission). The dichroic mirror is clamped in place



Click to Enlarge
The DFM has two
excitation (EX) and two
emission (EM) filter
ports. Ports labeled
with the same number
should be used
together.



Click to Enlarge The DFM features write-on labels for filter management.

using a design that provides uniform pressure without causing deformation to the mirror, and is locked in place using the included 3/32" hex key. Only light force is required to mount the mirror; we recommend screwing in both screws most of the way before final tightening.

Excitation and emission filters can be mounted in two possible configurations (see the diagram to the left) and are held using the included SM1RR Retaining Rings, which can be tightened or loosened with our SPW606 or SPW602 Spanner Wrenches (sold separately). The SM1-threaded (1.035"-40) holes in the two DFMT1 emission ports are oriented at a 3° angle with respect to the face


of the bottom of the cube, thereby eliminating unwanted reflections. To help keep track of your filter sets, spaces are provided on the top to write the specific mirror and filters that are mounted in each cube.

Mounting Service

If any of our imaging filters is ordered at the same time as the DFM, Thorlabs will premount the filters at no additional charge. In order to take advantage of this option, please contact Tech Support prior to ordering.

DIAGRAMS

Hide Diagrams



Hide Fluorescence Filter Cubes

Fluorescence Filter Cubes

Part Number	Description	Price	Availability
DFM/M	Customer Inspired!Kinematic Dichroic Filter Mount, 30 mm Cage Cube (Metric)	\$304.00	Today
DFM	Customer Inspired!Kinematic Dichroic Filter Mount, 30 mm Cage Cube	\$304.00	Today

Hide Fluorescence Filter Cube Tops and Bottoms

Fluorescence Filter Cube Tops and Bottoms

Part Number	Description	Price	Availability
DFMB/M	30 mm Cage Cube Base for Turning Cubes and Fluorescence Filter Cubes (Metric)	\$103.00	Today
DFMT1	Customer Inspired!Kinematic Dichroic Filter 30 mm Cage Cube, Top Only (Imperial and Metric Compatible)	\$201.00	Today
DFMB	30 mm Cage Cube Base for Turning Cubes and Fluorescence Filter Cubes	\$103.00	Today