

Breadboard Support Frames – Rigid, Non-Isolating



Casters Sold Separately

Features

- Support Frames Accommodate Breadboard Sizes as Large as 8' x 4' (2400 mm x 1200 mm)
- Solid, All Steel Construction
- Sturdy Welded Design
- Manual Leveling Pads to Compensate for Uneven Floors
- Set of 4 Casters Available
1540 lbs (700 kg) Maximum Load (PWA061 See Price Box Below)

Specifications

- **Load Capacity:** 1545 lbs (700 kg)
- **Height Adjustment Range:**
 - Leveling Pads: $\pm 0.375"$ (± 9.5 mm)
 - Leveling Feet: $\pm 0.2"$ (± 5 mm)
- **Finish:** Black Paint

This series of rigid frames is designed to provide a economical solution for supporting optical breadboards in a laboratory or production environment and is ideal for applications where vibration isolation is not a critical factor. This series of frames is available in two heights: 800 mm or 700 mm.

Rigid Support Frames, 32" (800 mm) Height

Stocked for Immediate Delivery

ITEM#*	\$	£	€	RMB	DESCRIPTION
PFL52501	\$ 1,094.80	£ 759.00	€ 972.00	¥ 9,244.60	Frame for Rigid Support Breadboard, 2.5' x 2.5' (750 x 750 mm)
PFL52510	\$ 1,094.80	£ 759.00	€ 972.00	¥ 9,244.60	Frame for Rigid Support Breadboard, 3' x 2' (900 x 600 mm)
PFL52502	\$ 1,101.60	£ 763.70	€ 978.10	¥ 9,302.00	Frame for Rigid Support Breadboard, 3' x 2.5' (900 x 750 mm)
PFL52505	\$ 1,108.40	£ 768.40	€ 984.10	¥ 9,359.40	Frame for Rigid Support Breadboard, 3' x 3' (900 x 900 mm)
PFL52511	\$ 1,098.40	£ 761.50	€ 975.20	¥ 9,275.00	Frame for Rigid Support Breadboard, 4' x 2' (1200 x 600 mm)
PFL52503	\$ 1,113.50	£ 772.00	€ 988.60	¥ 9,402.50	Frame for Rigid Support Breadboard, 4' x 2.5' (1200 x 750 mm)
PFL52506	\$ 1,123.70	£ 779.00	€ 997.70	¥ 9,488.60	Frame for Rigid Support Breadboard, 4' x 3' (1200 x 900 mm)
PFL52508	\$ 1,150.90	£ 797.90	€ 1,021.80	¥ 9,718.30	Frame for Rigid Support Breadboard, 4' x 4' (1200 x 1200 mm)
PFL52504	\$ 1,122.00	£ 777.80	€ 996.20	¥ 9,474.20	Frame for Rigid Support Breadboard, 5' x 2.5' (1500 x 750 mm)
PFL52507	\$ 1,132.20	£ 784.90	€ 1,005.20	¥ 9,560.40	Frame for Rigid Support Breadboard, 5' x 3' (1500 x 900 mm)
PFL52509	\$ 1,159.40	£ 803.80	€ 1,029.40	¥ 9,790.00	Frame for Rigid Support Breadboard, 5' x 4' (1500 x 1200 mm)

*Please contact your local sales office for a quotation including shipping.

Rigid Support Frames, 28" (700 mm) Height

Call for Lead Time

ITEM#*	\$	£	€	RMB	DESCRIPTION
PFL51501	\$ 1,084.60	£ 751.90	€ 963.00	¥ 9,158.40	Frame for Rigid Support Breadboard, 2.5' x 2.5' (750 x 750 mm)
PFL51510	\$ 1,084.80	£ 752.10	€ 963.10	¥ 9,160.10	Frame for Rigid Support Breadboard, 3' x 2' (900 x 600 mm)
PFL51502	\$ 1,091.40	£ 756.60	€ 969.00	¥ 9,215.90	Frame for Rigid Support Breadboard, 3' x 2.5' (900 x 750 mm)
PFL51505	\$ 1,098.20	£ 761.30	€ 975.00	¥ 9,273.30	Frame for Rigid Support Breadboard, 3' x 3' (900 x 900 mm)
PFL51511	\$ 1,098.40	£ 761.50	€ 975.20	¥ 9,275.00	Frame for Rigid Support Breadboard, 4' x 2' (1200 x 600 mm)
PFL51503	\$ 1,103.30	£ 764.90	€ 979.60	¥ 9,316.30	Frame for Rigid Support Breadboard, 4' x 2.5' (1200 x 750 mm)
PFL51506	\$ 1,113.50	£ 772.00	€ 988.60	¥ 9,402.50	Frame for Rigid Support Breadboard, 4' x 3' (1200 x 900 mm)
PFL51508	\$ 1,140.70	£ 790.80	€ 1,012.80	¥ 9,632.10	Frame for Rigid Support Breadboard, 4' x 4' (1200 x 1200 mm)
PFL51504	\$ 1,111.80	£ 770.80	€ 987.10	¥ 9,388.10	Frame for Rigid Support Breadboard, 5' x 2.5' (1500 x 750 mm)
PFL51507	\$ 1,122.00	£ 777.80	€ 996.20	¥ 9,474.20	Frame for Rigid Support Breadboard, 5' x 3' (1500 x 900 mm)
PFL51509	\$ 1,149.20	£ 796.70	€ 1,020.30	¥ 9,703.90	Frame for Rigid Support Breadboard, 5' x 4' (1500 x 1200 mm)

*Please contact your local sales office for a quotation including shipping.

Casters

ITEM#	\$	£	€	RMB	DESCRIPTION
PWA061	\$ 114.50	£ 79.40	€ 101.70	¥ 966.90	Set of 4 Casters, 1540 lbs (700 kg) Maximum Load