




REV. #	DESCRIPTION:	NAME/DATE:
1	INITIAL WORKING DRAWING	XX XX/XX/XX



SPECIFICATIONS:
 COATING RADIAL ANGLE: 270 ± 1
 SPECTRAL RANGE: 240-1200nm
 COATING: FRONT ND, BACK UNCOATED
 IRREGULARITY (PER cm) : $< \lambda$
 SURFACE QUALITY: 60-40 SCRATCH-DIG
 WEDGE: < 3 arcmin.
 OPTICAL DENSITY TOLRANCE: 5% (AT BOTH EXTREMES)
 LINEARITY OF DENSITY: 5%

TOLERANCES

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
LINEAR TOLERANCES:
 TWO PLACE DECIMAL: ± 0.010
 THREE PLACE DECIMAL: ± 0.005
 ANGULAR: $\pm 30'$
 SURFACE FINISH: 32 MICROINCHES
 PARALLELISM: 0.002
 FLATNESS: 0.002
 STRAIGHTNESS: 0.002
 CONCENTRICITY: 0.002
 PERPENDICULARITY: 0.002
 THREAD: CLASS 2 FIT

	NAME	DATE
DRAWN	AP	01/12/2007
ENG APPR.	TO	01/12/2007
MFG APPR.	TO	01/12/2007

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THORLABS, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THORLABS, INC. IS PROHIBITED.

THORLABS INC. PO BOX 366
 NEWTON NJ

TITLE: MOUNTED ROUND CONTINUOUSLY VARIABLE NDC FILTER

MATERIAL: UV FUSED SILICA/ALUMINUM **SIZE** A **REV.** B

SCALE: 1:1 **SHEET** 1 OF 1

DWG. NO. 10655-E01 **PART NO.** NDC-50C-2M

NOTE:
 FOR INFORMATION ONLY.
 NOT INTENDED FOR MANUFACTURING.