



Fiber Optic Stripping Tool

STRONGLY RECOMMENDED
Best Choice Stripping Tool



- Foolproof, No-Nick Design
- Fast, Reliable Fiber Stripping
- Self-Aligning Blade Set Assures Concentric Scoring of Buffer or Coating

Single Mode, Multimode, and Polarization-Maintaining Fibers



Fiber Polishing Kits

Complete set of accessories for polishing and connectorizing fibers.

See Page 956

Tool Selection

- Note your CLADDING and COATING* diameters along with their respective high side tolerances.
- Look down the sixth column of the table below for your fiber size.
- With your fiber size identified in the chart below, scan across to the corresponding CLADDING RANGE and COATING RANGE columns. Ensure that your fiber dimensions plus the high side tolerances fall within the range listed; if they do, then refer to the corresponding ITEM# to place your order. If the maximum fiber dimensions fall outside the range shown, order the next larger tool.

ITEM#	\$	£	€	RMB	TYPICAL FIBER CLADDING/COATING	CLADDING RANGE	COATING* RANGE
T06S13	\$ 68.00	£ 47.20	€ 60.40	¥ 574.20	125 µm / 250 µm	125 - 135 µm	250 - 343 µm
T08S13	\$ 68.00	£ 47.20	€ 60.40	¥ 574.20	125 µm / 250 µm	125 - 175 µm	250 - 343 µm
T08S40	\$ 68.00	£ 47.20	€ 60.40	¥ 574.20	125 µm / 900 µm	125 - 175 µm	889 - 1016 µm
T10S13	\$ 68.00	£ 48.00	€ 61.00	¥ 575.00	200 µm / 300 µm	180 - 230 µm	250 - 343 µm
T12S16	\$ 65.30	£ 45.30	€ 58.00	¥ 551.40	250 µm / 430 µm	235 - 280 µm	343 - 407 µm
T12S18	\$ 65.30	£ 45.30	€ 58.00	¥ 551.40	250 µm / 430 µm	235 - 280 µm	407 - 457 µm
T12S21	\$ 65.30	£ 45.30	€ 58.00	¥ 551.40	250 µm / 500 µm	235 - 280 µm	457 - 533 µm
T12S25	\$ 65.30	£ 45.30	€ 58.00	¥ 551.40	250 µm / 580 µm	235 - 280 µm	533 - 635 µm
T16S31	\$ 64.00	£ 44.40	€ 56.90	¥ 540.50	360 µm / 650 µm	335 - 380 µm	635 - 787 µm
T18S31	\$ 64.00	£ 44.40	€ 56.90	¥ 540.50	400 µm / 730 µm	385 - 430 µm	635 - 787 µm
T21S31	\$ 64.00	£ 44.40	€ 56.90	¥ 540.50	460 µm / 730 µm	435 - 500 µm	635 - 787 µm
T23S46	\$ 64.00	£ 44.40	€ 56.90	¥ 540.50	500 µm / 1000 µm	505 - 550 µm	1016 - 1168 µm
T28S46	\$ 65.90	£ 45.70	€ 58.60	¥ 556.50	630 µm / 1040 µm	605 - 680 µm	1016 - 1168 µm
M34S52	\$ 66.50	£ 46.10	€ 59.10	¥ 561.60	770 µm / 1250 µm	755 - 830 µm	1168 - 1321 µm
M37S46	\$ 66.50	£ 46.10	€ 59.10	¥ 561.60	860 µm / 1080 µm	835 - 900 µm	1016 - 1168 µm
NEW M37S63	\$ 66.50	£ 46.10	€ 59.10	¥ 561.60	860 µm / 1400 µm	835 - 900 µm	1397 - 1600 µm
M44S63	\$ 66.50	£ 46.10	€ 59.10	¥ 561.60	1035 µm / 1400 µm	905 - 1050 µm	1397 - 1600 µm
M44S67	\$ 66.50	£ 46.10	€ 59.10	¥ 561.60	1035 µm / 1600 µm	905 - 1050 µm	1600 - 1702 µm
M54S76	\$ 66.50	£ 46.10	€ 59.10	¥ 561.60	1250 µm / 1850 µm	1055 - 1350 µm	1778 - 1930 µm
M63S86	\$ 77.70	£ 53.90	€ 69.00	¥ 656.20	1550 µm / 2000 µm	1390 - 1600 µm	2057 - 2184 µm

*Coating refers to the jacket, buffer, or coating that is being removed.

