

LASER OPTICAL DENSITY CERTIFICATION

R AB7

Supplier: Thorlabs Limited
Purchase Order Number: EO-265946
Part Number: Dellner Rev D Sample
Requirements: EN 12254: 2010(E), Paragraph 5.3 Resistance to Laser Radiation, Table 2. 315-1400 nm Range.

Cert. Number: 51498
Date: September 23, 2015

TEST PARAMETERS

Coating Type: N/A
Test Wavelength: 1064 nm
Polarization: Random
Pulsewidth (square): 2 ms
Spot Diameter (1/e): 1.008 mm
Test Prep: N₂ blow
Quantity: 3

Substrate Material: Fabric
Incidence Angle: 0°
PRF : 20 Hz
Transverse Mode: TEM₀₀
Axial Modes: Multiple
Number of Sites: 1
Exposure Duration: 1000 shots/site

TEST RESULTS:

<u>Sample</u>	<u>Measurement Level</u>
8	Sample maintains AB7 during irradiation.
8	Sample maintains AB7 during irradiation.
8	Sample maintains AB7 during irradiation.

COMMENTS: Laser penetrates samples at AB8.

Spica Technologies certifies that this sample has been exposed to the parameters described above. All test and calibration data are maintained on file. All instrument calibration is traceable to NIST.

Test conducted by _____


Spica
Technologies Inc.

18 Clinton Drive #3
Hollis, NH 03049
www.spicatech.com
603-882-8233