

FINAL INSPECTION REPORT

2x2 50:50 PM Narrowband Coupler

Item #: PN1064R5A2
 SN: t017601

Center Wavelength: 1064 nm
 Coupling Ratio Specification
 Signal Output: 46 % - 54 %
 Tap Output: 46 % - 54 %
 Bandwidth: ± 15 nm
 Maximum Optical Power^a
 With Connectors or Bare Fiber: 1 W
 Spliced: 5 W
 Fiber Type: Corning PM 98-U25D

| Test Data ^b | |
|-----------------------------|---------------------------------------|
| Excess Loss ^c | ≤ 0.5 dB |
| Input-Output Path | White (Input) – White (Signal Output) |
| Coupling Ratio ^d | 50.5 % |
| Insertion Loss ^e | 3.37 dB |
| PER ^f | 26 dB |
| Input-Output Path | White (Input) – Red (Tap Output) |
| Coupling Ratio ^d | 49.5 % |
| Insertion Loss ^e | 3.45 dB |
| PER ^f | 25 dB |

- a. Specifies the maximum power allowed through the component. Performance and reliability under high power conditions must be determined within the user's setup.
- b. All values are measured at room temperature without connectors through the white input port.
- c. Ratio of the input optical power to the total optical power from all output ports. It is measured at the center wavelength.
- d. Does not include losses, as this is a measurement of the output power distribution only.
- e. Includes both the split of the power between the two outputs, as well as any optical losses in the coupler.
- f. Measured with a slow axis launch at room temperature with connectors at the center wavelength through the white input port.