

FINAL INSPECTION REPORT

1x2 99:1 PM Narrowband Coupler

Item #: PN1480R1A1
 SN: T045912

Center Wavelength: 1480 nm
 Coupling Ratio Specification
 Signal Output: 98.5 % - 99.5 %
 Tap Output: 0.5 % - 1.5 %
 Bandwidth: ± 15 nm
 Maximum Optical Power^a
 With Connectors or Bare Fiber: 1 W
 Spliced: 5 W
 Fiber Type: YOFC PM1017-C+ (1550)

Test Data ^b	
Excess Loss ^c	0.13 dB
Input-Output Path	White (Input) – White (Signal Output)
Coupling Ratio ^d	99 %
Insertion Loss ^e	0.17 dB
PER ^f	25.5 dB
Input-Output Path	White (Input) – Red (Tap Output)
Coupling Ratio ^d	1 %
Insertion Loss ^e	20.13 dB
PER ^f	24.8 dB

- a. Specifies the maximum power allowed through the component. Performance and reliability under high power conditions must be determined within the user's setup.
- b. All values, except PER, are measured at room temperature without connectors through the white input port.
- c. Ratio of the input optical power to the total optical power from all output ports. It is measured at the center wavelength.
- d. Does not include losses, as this is a measurement of the output power distribution only.
- e. Includes both the split of the power between the two outputs, as well as any optical losses in the coupler.
- f. Measured with a slow axis launch at room temperature with connectors at the center wavelength through the white input port.

Verified by: _____