

[View Product Family](#)

LASER DIODES: Ø3.8 mm, TO-46, Ø5.6 mm, Ø9 mm, AND Ø9.5 mm TO CANS

- ▶ Ø3.8 mm, TO-46, Ø5.6 mm, Ø9 mm, and Ø9.5 mm Laser Diodes
- ▶ Center Wavelengths Ranging from 375 nm to 4.60 µm
- ▶ Output Powers from 0.2 mW to 2 W

Application Idea
Our Laser Diode Driver Kits Include an LD Controller, TEC Controller, LD/TEC Mount, and Accessories



[Hide Overview](#)

OVERVIEW

Features

- Fabry-Perot (FP), Distributed Feedback (DFB), Volume Holographic Grating (VHG), Diode-Pumped Solid-State (DPSS), Quantum Cascade (QCL), Interband Cascade (ICL), and Vertical-Cavity Surface-Emitting Laser (VCSEL) Diodes
- Output Powers from 0.2 mW to 2 W
- Center Wavelengths Available from 375 nm to 9.5 µm
- Easily Choose a Compatible Mount Using Our LD Pin Codes
- Compatible with Thorlabs' Laser Diode and TEC Controllers

TO-packaged laser diodes are available in standard Ø3.8 mm, Ø5.6 mm, or Ø9 mm TO cans, as well as TO-46 or Ø9.5 mm cans. We have categorized the pin configurations into standard A, B, C, D, E, F, G, and H pin codes (see the diagram below). This pin code allows the user to easily determine compatible mounts.

Some of our diodes that are offered in header packages can be converted to a sealed TO can package by request, as indicated in the tables below. Please contact Tech Support for details.

Notes on Center Wavelength

While the center wavelength is listed for each diode, this is only a typical number. The center wavelength of a particular diode varies from production run to production run. Thus, the diode you receive may not operate at the typical center wavelength. Diodes can be temperature tuned, which will alter the lasing wavelength. A number of items below are listed as Wavelength Tested, which means that the dominant

| Laser Diode Selection Guide ^a |
|---|
| Shop by Package / Type |
| TO Can (Ø3.8, TO-46, Ø5.6, Ø9, and Ø9.5 mm) |
| TO Can Pigtail, Collimator Output (SM) |
| TO Can Pigtail (SM) |
| TO Can Pigtail (PM) |
| TO Can Pigtail (MM) |
| Fabry-Perot Butterfly Package |
| FBG-Stabilized Butterfly Package |
| VHG-Stabilized Butterfly Package (MM) |
| MIR Fabry-Perot QCL and ICL, TO Can |
| MIR Fabry-Perot QCL, Two-Tab C-Mount |
| MIR Fabry-Perot QCL, D-Mount |
| MIR Fabry-Perot QCL, High Heat Load |
| Chip on Submount |
| Single-Frequency Lasers |
| DFB TO Can Pigtail |
| DFB Butterfly Package |
| VHG-Stabilized TO Can |
| VHG-Stabilized TO Can Pigtail (SM) |
| VHG-Stabilized Butterfly Package |



Click to Enlarge
Ø9 mm TO-Can Laser
Diode Secured in Post-
Mounted LM9F Holder


Wavelength Tested that do not have the "Choose Item" option, please contact Tech Support with inquires about specific wavelengths.

Laser Mode and Linewidth

We offer laser diodes with different output characteristics (power, wavelength, beam size, shape, etc.). Most lasers offered here are single transverse mode (single mode, or SM) and a few are designed for higher-power, multiple-transverse-mode (multimode, or MM) operation. Our wavelength stabilized VHG laser diodes, sold below, have excellent single mode performance. Some single mode laser diodes can be operated with limited single-longitudinal-mode characteristics (see tables below for additional information). For better side mode suppression ratio (SMSR) performance, consider devices such as DFB lasers, VHG-stabilized lasers, DBR lasers, or external cavity lasers. Thorlabs single-frequency lasers are highlighted in green in the tables below; in particular, our VHG-stabilized, DFB, DBR, and external cavity lasers have very narrow linewidths (≤ 20 MHz for the VHG-stabilized and DFB lasers and < 100 kHz for the DBR and ECL lasers). Please see our Laser Diode Tutorial for more information on these topics and laser diodes in general.



Laser diodes are sensitive to electrostatic shock. Please take the proper precautions when handling the device (see our electrostatic shock accessories). Laser diodes are also sensitive to optical feedback, which can cause significant fluctuations in the output power of the laser diode depending on the application. See our optical isolators for potential solutions to this problem. Tech Support staff are available to help you select a laser diode and to discuss possible operation issues.

Pin Codes



Laser Diode pin codes indicate which mounts and diodes are compatible. The drawings do not represent exact wiring diagrams.

| Pin Code | Monitor Photodiode | Pin Code | Monitor Photodiode |
|----------|--------------------|----------|--------------------|
| A | Yes | E | No |
| B | Yes | F | Yes |
| C | Yes | G | No |
| D | Yes | H | No |



For warranty information for laser diodes, please refer to the *LD Operation* tab.

- ECL Butterfly Package
- DBR Butterfly Package
- ULN Hybrid Extended Butterfly Package
- MIR DFB QCL, Two-Tab C-Mount
- MIR DFB QCL, D-Mount
- MIR DFB QCL and ICL, High Heat Load

Shop By Wavelength

- a. Our complete selection of laser diodes is available on the *LD Selection Guide* tab above.

| Webpage Features | |
|-----------------------------|---|
| | Clicking this icon opens a window that contains specifications and mechanical drawings. |
| | Clicking this icon allows you to download our standard support documentation. |
| Choose Item | Clicking the words "Choose Item" opens a drop-down list containing all of the in-stock lasers around the desired center wavelength. The red icon next to the serial number then allows you to download L-I-V and spectral measurements for that serial-numbered device. |

[Hide Collimation Tutorial](#)

COLLIMATION TUTORIAL

Choosing a Collimation Lens for Your Laser Diode


Since the output of a laser diode is highly divergent, collimating optics are necessary. Aspheric lenses do not introduce spherical aberration and therefore are commonly chosen when the collimated laser beam is to be between one and five millimeters. A simple example will illustrate the key specifications to consider when choosing the correct lens for a given application. The second example below is an extension of the procedure, which will show how to circularize an elliptical beam.

Example 1: Collimating a Diverging Beam

- Laser Diode to be Used: L780P010
- Desired Collimated Beam Diameter: Ø3 mm (Major Axis)

When choosing a collimation lens, it is essential to know the divergence angle of the source being used and the desired output diameter. The specifications for the L780P010 laser diode indicate that the typical parallel and perpendicular FWHM beam divergences are 8° and 30°, respectively. Therefore, as the light diverges, an elliptical beam will result. To collect as much light as possible during the collimation process, consider the larger of these two divergence angles in any calculations (i.e., in this case, use 30°). If you wish to convert your elliptical beam into a round one, we suggest using an anamorphic prism pair, which magnifies one axis of your beam; for details, see Example 2 below.

Assuming that the thickness of the lens is small compared to the radius of curvature, the thin lens approximation can be used to determine the appropriate focal length for the asphere. Assuming a divergence angle of 30° (FWHM) and desired beam diameter of 3 mm:



Note that the focal length is generally not equal to the needed distance between the light source and the lens.

With this information known, it is now time to choose the appropriate collimating lens. Thorlabs offers a large selection of aspheric lenses. For this application, the ideal lens is a molded glass aspheric lens with focal length near 5.6 mm and our -B antireflection coating, which covers 780 nm. The C171TMD-B (mounted) or 354171-B (unmounted) aspheric lenses have a focal length of 6.20 mm, which will result in a collimated beam diameter (major axis) of 3.3 mm. Next, check to see if the numerical aperture (NA) of the diode is smaller than the NA of the lens:

$$0.30 = \text{NA}_{\text{Lens}} > \text{NA}_{\text{Diode}} \approx \sin(15^\circ) = 0.26$$

Up to this point, we have been using the full-width at half maximum (FWHM) beam diameter to characterize the beam. However, a better practice is to use the $1/e^2$ beam diameter. For a Gaussian beam profile, the $1/e^2$ diameter is almost equal to 1.7X the FWHM diameter. The $1/e^2$ beam diameter therefore captures more of the laser diode's output light (for greater power delivery) and minimizes far-field diffraction (by clipping less of the incident light).

A good rule of thumb is to pick a lens with an NA twice that of the laser diode NA. For example, either the A390-B or the A390TM-B could be used as these lenses each have an NA of 0.53, which is more than twice the approximate NA of our laser diode (0.26). These lenses each have a focal length of 4.6 mm, resulting in an approximate major beam diameter of 2.5 mm. In general, using a collimating lens with a short focal length will result in a small collimated beam diameter and a large beam divergence, while a lens with a large focal length will result in a large collimated beam diameter and a small divergence.


Example 2: Circularizing an Elliptical Beam

Using the laser diode and aspheric lens chosen above, we can use an anamorphic prism pair to convert our collimated, elliptical beam into a circular beam.

Whereas earlier we considered only the larger divergence angle, we now look at the smaller beam divergence of 8°. From this, and using the effective focal length of the A390-B aspheric lens chosen in Example 1, we can determine the length of the semi-minor axis of the elliptical beam after collimation:

$$r' = f * \tan(\Theta'/2) = 4.6 \text{ mm} * \tan(4^\circ) = 0.32 \text{ mm}$$

The minor beam diameter is double the semi-minor axis, or 0.64 mm. In order to magnify the minor diameter to be equal to the major diameter of 2.5 mm, we will need an anamorphic prism pair that yields a magnification of 3.9. Thorlabs offers both mounted and unmounted prism pairs. Mounted prism pairs provide the benefit of a stable housing to preserve alignment, while unmounted prism pairs can be positioned at any angle to achieve the exact desired magnification.



The PS883-B mounted prism pair provides a magnification of 4.0 for a 950 nm wavelength beam. Because shorter wavelengths undergo greater magnification when

passing through the prism pair, we can expect our 780 nm beam to be magnified by slightly more than 4.0X. Thus, the beam will still maintain a small degree of ellipticity.

Alternatively, we can use the PS871-B unmounted prism pair to achieve the precise magnification of the minor diameter necessary to produce a circular beam. Using the data available here, we see that the PS871-B achieves a magnification of 4.0 when the prisms are positioned at the following angles for a 670 nm wavelength beam:

α_1 : +34.608°

α_2 : -1.2455°

Refer to the diagram to the right for α_1 and α_2 definitions. Our 780 nm laser will experience slightly less magnification than a 670 nm beam passing through the prisms at these angles. Some trial and error may be required to achieve the exact desired magnification. In general:

- To increase magnification, rotate the first prism clockwise (increasing α_1) and rotate the second prism counterclockwise (decreasing α_2).
- To reduce magnification, rotate the first prism counterclockwise (decreasing α_1) and rotate the second prism clockwise (increasing α_2).

Remember that the prism pair introduces a linear offset between the input and output beams which increases with greater magnification.

[Hide LD Operation](#)

LD OPERATION

Video Insight: Setting Up a TO Can Laser Diode

Installing a TO can laser diode in a mount and setting it up to run under temperature and current control presents many opportunities to make a mistake that could damage or destroy the laser. This step-by-step guide includes tips for keeping humans and laser diodes safe from harm.

When operated within their specifications, laser diodes have extremely long lifetimes. Most failures occur from mishandling or operating the lasers beyond their maximum ratings. Laser diodes are among the most static-sensitive devices currently made and proper ESD protection should be worn whenever handling a laser diode. Due to their extreme electrostatic sensitivity, laser diodes cannot be returned after their sealed package has been opened. Laser diodes in their original sealed package can be returned for a full refund or credit.

Handling and Storage Precautions

Because of their extreme susceptibility to damage from electrostatic discharge (ESD), care should be taken whenever handling and operating laser diodes.

Wrist Straps

Use grounded anti-static wrist straps whenever handling diodes.

Anti-Static Mats

Always work on grounded anti-static mats.

Laser Diode Storage

When not in use, short the leads of the laser together to protect against ESD damage.

Operating and Safety Precautions

Use an Appropriate Driver

Laser diodes require precise control of operating current and voltage to avoid overdriving the laser. In addition, the laser driver should provide protection against power supply transients. Select a laser driver appropriate for your application. **Do not use a voltage supply with a current-limiting resistor** since it does not provide sufficient regulation to protect the laser diode.

Power Meters

When setting up and calibrating a laser diode with its driver, use a NIST-traceable power meter to precisely measure the laser output. It is usually safest to measure the laser diode output directly before placing the laser in an optical system. If this is not possible, be sure to take all optical losses (transmissive, aperture stopping, etc.) into consideration when determining the total output of the laser.

Reflections

Flat surfaces in the optical system in front of a laser diode can cause some of the laser energy to reflect back onto the laser's monitor photodiode, giving an erroneously high photodiode current. If optical components are moved within the system and energy is no longer reflected onto the monitor photodiode, a constant-power feedback loop will sense the drop in photodiode current and try to compensate by increasing the laser drive current and possibly overdriving the laser. Back reflections can also cause other malfunctions or damage to laser diodes. To avoid this, be sure that all surfaces are angled 5-10°, and when necessary, use optical isolators to attenuate direct feedback into the laser.

Heat Sinks

Laser diode lifetime is inversely proportional to operating temperature. Always mount the laser diode in a suitable heat sink to remove excess heat from the laser package.

Voltage and Current Overdrive

Be careful not to exceed the maximum voltage and drive current listed on the specification sheet with each laser diode, even momentarily. Also, reverse voltages as little as 3 V can damage a laser diode.

ESD-Sensitive Device

Laser diodes are susceptible to ESD damage even during operation. This is particularly aggravated by using long interface cables between the laser diode and its driver due to the inductance that the cable presents. Avoid exposing the laser diode or its mounting apparatus to ESD at all times.

ON/OFF and Power-Supply-Coupled Transients

Due to their fast response times, laser diodes can be easily damaged by transients less than 1 μ s. High-current devices such as soldering irons, vacuum pumps, and fluorescent lamps can cause large momentary transients, and thus surge-protected outlets should always be used when working with laser diodes.

If you have any questions regarding laser diodes, please contact Thorlabs Technical Support for assistance.

[Hide Laser Safety](#)

LASER SAFETY

Laser Safety and Classification

Safe practices and proper usage of safety equipment should be taken into consideration when operating lasers. The eye is susceptible to injury, even from very low levels of laser light. Thorlabs offers a range of laser safety accessories that can be used to reduce the risk of accidents or injuries. Laser emission in the visible and near infrared spectral ranges has the greatest potential for retinal injury, as the cornea and lens are transparent to those wavelengths, and the lens can focus the laser energy onto the retina.

Safe Practices and Light Safety Accessories









- Laser safety eyewear must be worn whenever working with Class 3 or 4 lasers.
- Regardless of laser class, Thorlabs recommends the use of laser safety eyewear whenever working with laser beams with non-negligible powers, since metallic tools such as screwdrivers can accidentally redirect a beam.
- Laser goggles designed for specific wavelengths should be clearly available near laser setups to protect the wearer from unintentional laser reflections.
- Goggles are marked with the wavelength range over which protection is afforded and the minimum optical density within that range.
- Laser Safety Curtains and Laser Safety Fabric shield other parts of the lab from high energy lasers.
- Blackout Materials can prevent direct or reflected light from leaving the experimental setup area.
- Thorlabs' Enclosure Systems can be used to contain optical setups to isolate or minimize laser hazards.
- A fiber-pigtailed laser should always be turned off before connecting it to or disconnecting it from another fiber, especially when the laser is at power levels above 10 mW.



- All beams should be terminated at the edge of the table, and laboratory doors should be closed whenever a laser is in use.
- Do not place laser beams at eye level.
- Carry out experiments on an optical table such that all laser beams travel horizontally.
- Remove unnecessary reflective items such as reflective jewelry (e.g., rings, watches, etc.) while working near the beam path.
- Be aware that lenses and other optical devices may reflect a portion of the incident beam from the front or rear surface.
- Operate a laser at the minimum power necessary for any operation.
- If possible, reduce the output power of a laser during alignment procedures.
- Use beam shutters and filters to reduce the beam power.
- Post appropriate warning signs or labels near laser setups or rooms.
- Use a laser sign with a lightbox if operating Class 3R or 4 lasers (i.e., lasers requiring the use of a safety interlock).
- Do not use Laser Viewing Cards in place of a proper Beam Trap.


Laser Classification

Lasers are categorized into different classes according to their ability to cause eye and other damage. The International Electrotechnical Commission (IEC) is a global organization that prepares and publishes international standards for all electrical, electronic, and related technologies. The IEC document 60825-1 outlines the safety of laser products. A description of each class of laser is given below:


| Class | Description | Warning Label |
|--|---|---|
| 1 | This class of laser is safe under all conditions of normal use, including use with optical instruments for intrabeam viewing. Lasers in this class do not emit radiation at levels that may cause injury during normal operation, and therefore the maximum permissible exposure (MPE) cannot be exceeded. Class 1 lasers can also include enclosed, high-power lasers where exposure to the radiation is not possible without opening or shutting down the laser. |  |
| 1M | Class 1M lasers are safe except when used in conjunction with optical components such as telescopes and microscopes. Lasers belonging to this class emit large-diameter or divergent beams, and the MPE cannot normally be exceeded unless focusing or imaging optics are used to narrow the beam. However, if the beam is refocused, the hazard may be increased and the class may be changed accordingly. |  |
| 2 | Class 2 lasers, which are limited to 1 mW of visible continuous-wave radiation, are safe because the blink reflex will limit the exposure in the eye to 0.25 seconds. This category only applies to visible radiation (400 - 700 nm). |  |
| 2M | Because of the blink reflex, this class of laser is classified as safe as long as the beam is not viewed through optical instruments. This laser class also applies to larger-diameter or diverging laser beams. |  |
| 3R | Class 3R lasers produce visible and invisible light that is hazardous under direct and specular-reflection viewing conditions. Eye injuries may occur if you directly view the beam, especially when using optical instruments. Lasers in this class are considered safe as long as they are handled with restricted beam viewing. The MPE can be exceeded with this class of laser; however, this presents a low risk level to injury. Visible, continuous-wave lasers in this class are limited to 5 mW of output power. |  |
| 3B | Class 3B lasers are hazardous to the eye if exposed directly. Diffuse reflections are usually not harmful, but may be when using higher-power Class 3B lasers. Safe handling of devices in this class includes wearing protective eyewear where direct viewing of the laser beam may occur. Lasers of this class must be equipped with a key switch and a safety interlock; moreover, laser safety signs should be used, such that the laser cannot be used without the safety light turning on. Laser products with power output near the upper range of Class 3B may also cause skin burns. |  |
| 4 | This class of laser may cause damage to the skin, and also to the eye, even from the viewing of diffuse reflections. These hazards may also apply to indirect or non-specular reflections of the beam, even from apparently matte surfaces. Great care must be taken when handling these lasers. They also represent a fire risk, because they may ignite combustible material. Class 4 lasers must be equipped with a key switch and a safety interlock. |  |
| All class 2 lasers (and higher) must display, in addition to the corresponding sign above, this triangular warning sign. | |  |

[Hide 375 - 405 nm TO Can Laser Diodes](#)

375 - 405 nm TO Can Laser Diodes

| Item # | Info | Wavelength | Power ^{a,b} | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^c | Compatible Socket | Wavelength Tested | Laser Mode |
|-------------------------|---|------------|----------------------|--|---------|----------|---------------------------------|-------------------|-------------------|------------------------|
| L375P70MLD ^d |  | 375 nm | 70 mW | 110 mA / 140 mA | Ø5.6 mm | F | Yes | - | No | Single Transverse Mode |










| | | | | | | | | | | |
|---------------------------|---|--------|-----------------|------------------|---------|---|-----|--------|-----|------------------------|
| L404P400M |  | 404 nm | 400 mW | 370 mA / 410 mA | Ø5.6 mm | G | No | S7060R | No | Multimode |
| L405P20 |  | 405 nm | 20 mW | 38 mA / 55 mA | Ø5.6 mm | B | Yes | S7060R | No | Single Transverse Mode |
| L405G2^e |  | 405 nm | 35 mW | 50 mA / 75 mA | Ø3.8 mm | G | No | S038S | Yes | Single Transverse Mode |
| DL5146-101S |  | 405 nm | 40 mW | 70 mA / 100 mA | Ø5.6 mm | B | Yes | S7060R | No | Single Transverse Mode |
| L405A1 |  | 405 nm | 175 mW (Min) | 150 mA / 200 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| L405G1 |  | 405 nm | 1000 mW | 900 mA / 1200 mA | Ø9 mm | G | No | S8060 | No | Multimode |

- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Typical value unless otherwise noted.
- c. Laser diodes with a built-in monitor photodiode can operate at constant power.
- d. A temperature-controlled mount such as our LDM56F(/M) is recommended for general use.
- e. The L405G2 is tested to ensure a center wavelength tolerance of ± 1 nm.

| Part Number | Description | Price | Availability |
|--------------------|--|---|------------------|
| L375P70MLD | 375 nm, 70 mW, Ø5.6 mm, F Pin Code, Laser Diode | \$5,223.29 | Today |
| L404P400M | 404 nm, 400 mW, Ø5.6 mm, G Pin Code, MM Laser Diode | \$753.14 Volume Pricing Available | Today |
| L405P20 | 405 nm, 20 mW, Ø5.6 mm, B Pin Code, Laser Diode | \$58.21 Volume Pricing Available | Today |
| L405G2 | 405 nm, 35 mW, Ø3.8 mm, G Pin Code, Laser Diode | \$104.93 Volume Pricing Available | Lead Time |
| DL5146-101S | 405 nm, 40 mW, Ø5.6 mm, B Pin Code Laser Diode | \$95.93 Volume Pricing Available | Today |
| L405A1 | 405 nm, 175 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$805.23 | Today |
| L405G1 | 405 nm, 1000 mW, Ø9 mm, G Pin Code, MM Laser Diode | \$780.30 | Today |

[Hide 450 - 520 nm TO Can Laser Diodes](#)

450 - 520 nm TO Can Laser Diodes

| Item # | Info | Wavelength | Power ^{a,b} | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^c | Compatible Socket | Wavelength Tested | Laser Mode |
|--------------------|---|------------|----------------------|---|---------|-----------------|------------------------------------|----------------------|----------------------|------------------------|
| L450G3 |  | 450 nm | 100 mW (Min) | 80 mA / 110 mA | Ø3.8 mm | G | No | S038S | No | Single Transverse Mode |
| L450G2 |  | 450 nm | 100 mW (Min) | 80 mA / 110 mA | Ø5.6 mm | G | No | S7060R | No | Single Transverse Mode |
| L450P1600MM |  | 450 nm | 1600 mW | 1200 mA / 1500 mA | Ø5.6 mm | G | No | S7060R | No | Multimode |
| L473P100 |  | 473 nm | 100 mW | 120 mA / 150 mA | Ø5.6 mm | F+ ^d | Yes | - | No | Single Transverse Mode |
| L488P60 |  | 488 nm | 60 mW | 75 mA / 110 mA | Ø5.6 mm | B | Yes | S7060R | No | Single Transverse Mode |
| L515A1 |  | 515 nm | 10 mW | 50 mA / 100 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| L520A1 |  | 520 nm | 30 mW (Min) | 80 mA / 100 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| PL520 |  | 520 nm | 50 mW | 150 mA / 160 mA | Ø3.8 mm | G | No | S038S | No | Single Transverse Mode |
| L520P50 |  | 520 nm | 50 mW | 150 mA / 160 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| L520A2 |  | 520 nm | 110 mW (Min) | 225 mA / 330 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |

- Please see the blue info icons (i) above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- Typical value unless otherwise noted.
- Laser diodes with a built-in monitor photodiode can operate at constant power.
- This laser diode has a built in Zener diode to help protect against damage from small levels of electrostatic discharge and reverse potential on the laser diode. A temperature-controlled mount such as our LDM56F(/M) or LDM90(/M) is recommended for general use.

| Part Number | Description | Price | Availability |
|-------------|---|-------------------------------------|--------------|
| L450G3 | 450 nm, 100 mW, Ø3.8 mm, G Pin Code, Laser Diode | \$138.57 | Today |
| L450G2 | 450 nm, 100 mW, Ø5.6 mm, G Pin Code, Laser Diode | \$126.90 | Today |
| L450P1600MM | 450 nm, 1600 mW, Ø5.6 mm, G Pin Code, MM, Laser Diode | \$94.74 | Today |
| L473P100 | 473 nm, 100 mW, Ø5.6 mm, F+ Pin Code, Laser Diode | \$3,032.68 | Today |
| L488P60 | 488 nm, 60 mW, Ø5.6 mm, B Pin Code, Laser Diode | \$2,793.99 | Today |
| L515A1 | 515 nm, 10 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$30.68 Volume Pricing Available | Today |
| L520A1 | 520 nm, 30 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$76.29 | Today |
| PL520 | 520 nm, 50 mW, Ø3.8 mm, G Pin Code Laser Diode | \$89.69 Volume Pricing Available | Today |
| L520P50 | 520 nm, 50 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$76.61 Volume Pricing Available | Today |
| L520A2 | 520 nm, 110 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$155.40 | Today |

[Hide 532 nm TO Can DPSS Lasers](#)

532 nm TO Can DPSS Lasers

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode | Compatible Socket | Wavelength Tested | Laser Mode |
|-----------------------|------|------------|--------------------|--|-------------------------------------|----------|--------------------|-------------------|-------------------|------------------------|
| DJ532-10 ^b | i | 532 nm | 10 mW | 220 mA / 250 mA | Ø9.5 mm (Non-Standard) ^c | A | Yes ^d | - | No | Single Transverse Mode |
| DJ532-40 ^b | i | 532 nm | 40 mW | 330 mA / 400 mA | Ø9.5 mm (Non-Standard) ^c | E | No | - | No | Single Transverse Mode |



- Please see the blue info icons (i) above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- Click here for more information on our 532 nm Diode Pumped Solid State Lasers.
- These lasers have the same pin spacing as our Ø5.6 mm laser diodes. They are compatible with the LDM56 Laser Diode Mount using the LDM56DJ DPSS Laser Mounting Flange.
- The monitor photodiode of the DJ532-10 measures the power of the pump source, not the 532 nm output. Therefore, we recommend operating these diodes in constant current mode.


| Part Number | Description | Price | Availability |
|-------------|---------------------------------------|----------|--------------|
| DJ532-10 | 532 nm, 10 mW, A Pin Code, DPSS Laser | \$175.81 | Today |
| DJ532-40 | 532 nm, 40 mW, E Pin Code, DPSS Laser | \$212.64 | Today |

[Hide 633 - 635 nm TO Can Laser Diodes](#)

633 - 635 nm TO Can Laser Diodes

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|-----------|------|------------|--------------------|--|---------|----------|---------------------------------|-------------------|-------------------|------------------------|
| HL63163DG | i | 633 nm | 100 mW | 170 mA / 230 mA | Ø5.6 mm | G | No | S7060R | No | Single Transverse Mode |
| L635P5 | i | 635 nm | 5 mW | 30 mA / 45 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| HL6312G | i | 635 nm | 5 mW | 50 mA / 85 mA | Ø9 mm | A | Yes | S8060 or S8060-4 | No | Single Transverse Mode |

| | | | | | | | | | | |
|---------|---|--------|-------|----------------|-------|---|-----|------------------|----|------------------------|
| HL6320G |  | 635 nm | 10 mW | 60 mA / 95 mA | Ø9 mm | A | Yes | S8060 or S8060-4 | No | Single Transverse Mode |
| HL6322G |  | 635 nm | 15 mW | 75 mA / 100 mA | Ø9 mm | A | Yes | S8060 or S8060-4 | No | Single Transverse Mode |


- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.

| Part Number | Description | | | | | | | Price | | Availability |
|-------------|--|--|--|--|--|--|--|--------------------------------------|--|--------------|
| HL63163DG | 633 nm, 100 mW, Ø5.6 mm, G Pin Code, Laser Diode | | | | | | | \$337.37 Volume Pricing Available | | Today |
| L635P5 | 635 nm, 5 mW, Ø5.6 mm, A Pin Code, Laser Diode | | | | | | | \$27.67 Volume Pricing Available | | Today |
| HL6312G | 635 nm, 5 mW, Ø9 mm, A Pin Code, Laser Diode | | | | | | | \$24.94 Volume Pricing Available | | Today |
| HL6320G | 635 nm, 10 mW, Ø9 mm, A Pin Code, Laser Diode | | | | | | | \$47.24 Volume Pricing Available | | Today |
| HL6322G | 635 nm, 15 mW, Ø9 mm, A Pin Code, Laser Diode | | | | | | | \$79.00 Volume Pricing Available | | Today |

[Hide 637 - 639 nm TO Can Laser Diodes](#)

637 - 639 nm TO Can Laser Diodes

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|-----------|---|------------|--------------------|--|--------------------|----------|---------------------------------|---------------------|-------------------|------------------------|
| L637P5 |  | 637 nm | 5 mW | 20 mA / 25 mA | Ø5.6 mm | C | Yes | S7060R | No | Single Transverse Mode |
| HL63142DG |  | 637 nm | 100 mW | 140 mA / 180 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| HL63133DG |  | 637 nm | 170 mW | 250 mA / 320 mA | Ø5.6 mm | G | No | S7060R | No | Single Transverse Mode |
| HL6388MG |  | 637 nm | 250 mW | 340 mA / 430 mA | Ø5.6 mm | H | No | S7060R | No | Multimode |
| L637G1 |  | 637 nm | 1200 mW | 1100 mA / 1500 mA | Ø9 mm ^c | G | No | Custom ^c | No | Multimode |
| L638P040 |  | 638 nm | 40 mW | 92 mA / 115 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| L638P150 |  | 638 nm | 150 mW | 230 mA / 300 mA | Ø3.8 mm | G | No | S038S | No | Single Transverse Mode |
| L638P200 |  | 638 nm | 200 mW | 280 mA / 330 mA | Ø5.6 mm | G | No | S7060R | No | Single Transverse Mode |
| L638P700M |  | 638 nm | 700 mW | 820 mA / 1000 mA | Ø5.6 mm | G | No | S7060R | No | Multimode |
| HL6358MG |  | 639 nm | 10 mW | 40 mA / 50 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| HL6323MG |  | 639 nm | 30 mW | 100 mA / 130 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |

- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.
- c. A socket is included to assist with soldering. The leads on this diode have a larger 0.6 mm diameter than the typical 0.45 mm diameter for a Ø9 mm package. This makes it incompatible with mounts and sockets that are designed to fit a standard Ø9 mm TO can package, such as our LDM90 mount.


| Part Number | Description | | | | | | | Price | | Availability |
|-------------|---|--|--|--|--|--|--|--------------------------------------|--|--------------|
| L637P5 | Customer Inspired! 637 nm, 5 mW, Ø5.6 mm, C Pin Code, Laser Diode | | | | | | | \$15.68 Volume Pricing Available | | Today |
| HL63142DG | 637 nm, 100 mW, Ø5.6 mm, A Pin Code, Laser Diode | | | | | | | \$321.92 Volume Pricing Available | | Today |
| HL63133DG | 637 nm, 170 mW, Ø5.6 mm, G Pin Code, Laser Diode | | | | | | | \$190.07 Volume Pricing Available | | Today |
| HL6388MG | 637 nm, 250 mW, Ø5.6 mm, H Pin Code, MM, Laser Diode | | | | | | | \$65.93 Volume Pricing Available | | Today |
| L637G1 | 637 nm, 1200 mW, Ø9 mm, G Pin Code, MM, Laser Diode | | | | | | | \$178.09 Volume Pricing Available | | Today |

| | | | |
|-----------|--|--------------------------------------|---------|
| L638P040 | 638 nm, 40 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$112.85 Volume Pricing Available | 3 Weeks |
| L638P150 | 638 nm, 150 mW, Ø3.8 mm, G Pin Code, Laser Diode | \$54.74 | Today |
| L638P200 | 638 nm, 200 mW, Ø5.6 mm, G Pin Code, Laser Diode | \$153.73 | Today |
| L638P700M | 638 nm, 700 mW, Ø5.6 mm, G Pin Code, MM, Laser Diode | \$72.17 Volume Pricing Available | Today |
| HL6358MG | 639 nm, 10 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$17.94 Volume Pricing Available | 3 Weeks |
| HL6323MG | 639 nm, 30 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$150.87 Volume Pricing Available | Today |

[Hide 640 nm - 660 nm TO Can Laser Diodes](#)

640 nm - 660 nm TO Can Laser Diodes









| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|----------|---|------------|--------------------|--|---------|----------|---------------------------------|-------------------|-------------------|------------------------|
| HL6362MG |  | 640 nm | 40 mW | 90 mA / 110 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| HL6364DG |  | 642 nm | 60 mW | 120 mA / 155 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| HL6366DG |  | 642 nm | 80 mW | 150 mA / 175 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| HL6385DG |  | 642 nm | 150 mW | 250 mA / 350 mA | Ø5.6 mm | H | No | S7060R | No | Single Transverse Mode |
| L650P007 |  | 650 nm | 7 mW | 28 mA / 35 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| HL6501MG |  | 658 nm | 30 mW | 75 mA / 120 mA | Ø5.6 mm | C | Yes | S7060R | No | Single Transverse Mode |
| L658P040 |  | 658 nm | 40 mW | 75 mA / 110 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| HL6544FM |  | 660 nm | 50 mW | 115 mA / 135 mA | Ø5.6 mm | G | No | S7060R | No | Single Transverse Mode |
| HL6545MG |  | 660 nm | 120 mW | 170 mA / 210 mA | Ø5.6 mm | H | No | S7060R | No | Single Transverse Mode |
| L660P120 |  | 660 nm | 120 mW | 175 mA / 210 mA | Ø5.6 mm | C | Yes | S7060R | No | Single Transverse Mode |


- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.

| Part Number | Description | Price | Availability |
|-------------|--|--------------------------------------|--------------|
| HL6362MG | 640 nm, 40 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$136.61 Volume Pricing Available | Today |
| HL6364DG | 642 nm, 60 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$180.56 Volume Pricing Available | Today |
| HL6366DG | 642 nm, 80 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$229.27 Volume Pricing Available | Today |
| HL6385DG | 642 nm, 150 mW, Ø5.6 mm, H Pin Code, Laser Diode | \$356.39 Volume Pricing Available | Today |
| L650P007 | 650 nm, 7 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$15.08 Volume Pricing Available | Today |
| HL6501MG | 658 nm, 30 mW, Ø5.6 mm, C Pin Code, Laser Diode | \$28.63 Volume Pricing Available | Today |
| L658P040 | 658 nm, 40 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$31.77 Volume Pricing Available | Today |
| HL6544FM | 660 nm, 50 mW, Ø5.6 mm, G Pin Code, Laser Diode | \$38.91 Volume Pricing Available | Today |
| HL6545MG | 660 nm, 120 mW, Ø5.6 mm, H Pin Code, Laser Diode | \$51.09 Volume Pricing Available | Today |
| L660P120 | 660 nm, 120 mW, Ø5.6 mm, C Pin Code, Laser Diode | \$116.73 Volume Pricing Available | Today |

[Hide 670 nm - 730 nm TO Can Laser Diodes](#)

670 nm - 730 nm TO Can Laser Diodes

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|----------|---|------------|--------------------|--|---------|----------|---------------------------------|-------------------|-------------------|------------------------|
| L670VH1 |  | 670 nm | 1 mW | 2.5 mA / 2.8 mA | TO-46 | H | No | S8060 | No | Single Transverse Mode |
| HL6748MG |  | 670 nm | 10 mW | 30 mA / 45 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| HL6714G |  | 670 nm | 10 mW | 55 mA / 90 mA | Ø9 mm | A | Yes | S8060 or S8060-4 | No | Single Transverse Mode |
| HL6756MG |  | 670 nm | 15 mW | 35 mA / 45 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| HL6750MG |  | 685 nm | 50 mW | 70 mA / 120 mA | Ø5.6 mm | C | Yes | S7060R | No | Single Transverse Mode |
| HL6738MG |  | 690 nm | 30 mW | 85 mA / 115 mA | Ø5.6 mm | C | Yes | S7060R | No | Single Transverse Mode |
| HL7001MG |  | 705 nm | 40 mW | 75 mA / 100 mA | Ø5.6 mm | C | Yes | S7060R | No | Single Transverse Mode |
| HL7302MG |  | 730 nm | 40 mW | 75 mA / 100 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |

- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.



| Part Number | Description | Price | Availability |
|-------------|--|--------------------------------------|--------------|
| L670VH1 | 670 nm, 1 mW, TO-46, H Pin Code, VCSEL Diode | \$164.67 | Today |
| HL6748MG | 670 nm, 10 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$31.19 Volume Pricing Available | Today |
| HL6714G | 670 nm, 10 mW, Ø9 mm, A Pin Code, Laser Diode | \$59.11 Volume Pricing Available | Today |
| HL6756MG | 670 nm, 15 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$70.69 Volume Pricing Available | Today |
| HL6750MG | 685 nm, 50 mW, Ø5.6 mm, C Pin Code, Laser Diode | \$93.24 Volume Pricing Available | Today |
| HL6738MG | 690 nm, 30 mW, Ø5.6 mm, C Pin Code, Laser Diode | \$56.43 Volume Pricing Available | Today |
| HL7001MG | Customer Inspired! 705 nm, 40 mW, Ø5.6 mm, C Pin Code, Laser Diode | \$420.53 Volume Pricing Available | Today |
| HL7302MG | 730 nm, 40 mW, Ø5.6 mm, A Pin Code, Diode | \$420.53 Volume Pricing Available | Today |









[Hide 760 nm - 795 nm TO Can Laser Diodes](#)



760 nm - 795 nm TO Can Laser Diodes



Note: The rows shaded green below denote single-frequency laser diodes.

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|----------|---|------------|--------------------|--|---------|----------|---------------------------------|-------------------|-------------------|-------------------------------|
| L760VH1 |  | 760 nm | 0.5 mW | 3 mA (Max) | TO-46 | H | No | S8060 or S8060-4 | No | Single Frequency ^c |
| L763VH1 |  | 763 nm | 0.5 mW | 3 mA (Max) | TO-46 | H | No | S8060 or S8060-4 | No | Single Frequency ^c |
| L780P010 | | 780 nm | 10 mW | 24 mA / 40 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse |

| |  | | | | | | | | | Mode |
|---------------------------------|---|--------|---------|---------------------------|--------------------|---|-----|------------------|-----|-------------------------------|
| L785P5 |  | 785 nm | 5 mW | 28 mA / 40 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| L785P25 |  | 785 nm | 25 mW | 45 mA / 60 mA | Ø5.6 mm | B | Yes | S7060R | No | Single Transverse Mode |
| L785P090 |  | 785 nm | 90 mW | 125 mA / 165 mA | Ø5.6 mm | C | Yes | S7060R | No | Single Transverse Mode |
| LD785-SEV300^d |  | 785 nm | 300 mW | 500 mA (Max) ^e | Ø9 mm ^f | E | No | S8060 or S8060-4 | Yes | Single Frequency ^c |
| LD785-SH300^g |  | 785 nm | 300 mW | 400 mA / 450 mA | Ø9 mm | H | No | S8060 or S8060-4 | Yes | Single Transverse Mode |
| LD785-SE400^g |  | 785 nm | 400 mW | 550 mA / 600 mA | Ø9 mm | E | No | S8060 or S8060-4 | Yes | Single Transverse Mode |
| L795VH1 |  | 795 nm | 0.25 mW | 1.2 mA / 1.5 mA | TO-46 | H | No | S8060 or S8060-4 | No | Single Frequency ^c |

- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.
- c. Single Longitudinal Mode and Single Transverse Mode
- d. In order to achieve the specified performance, we recommend using the LDM90/(M) Laser Diode Mount and, when collimated, an NIR Optical Isolator; single frequency performance when collimated is only guaranteed with >35 dB isolation of back reflections. This volume holographic grating (VHG) laser diode is also available in an SM pigtail package with internal isolator.
- e. The power can be tuned across the operating current range, given in the serial-number-specific documentation, while maintaining wavelength-stabilized, single-frequency performance within a stabilized temperature range.
- f. The Ø9 mm package for the LD785-SEV300 is 4.30 mm (0.17") thick, which is more than the standard Ø9 mm package thickness of 1.50 mm (0.06"). The diode will still be compatible with all Ø9 mm laser diode mounts; please see the *Drawing* tab in the blue info icon () above for full package specifications. Mounting this diode in the LDM90/(M) mount requires two 2-56 screws, included with this diode.
- g. This diode is exceptionally sensitive to optical feedback. Any reflection with more than 2% of the incident power has the potential to permanently damage the diode.

| Part Number | Description | Price | Availability |
|---------------------|---|-------------------------------------|--------------|
| L760VH1 | 760 nm, 0.5 mW, TO-46, H Pin Code, VCSEL Diode | \$695.64 | Today |
| L763VH1 | 763 nm, 0.5 mW, TO-46, H Pin Code, VCSEL Diode | \$695.64 | Today |
| L780P010 | 780 nm, 10 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$27.45 Volume Pricing Available | Today |
| L785P5 | 785 nm, 5 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$12.93 Volume Pricing Available | Today |
| L785P25 | 785 nm, 25 mW, Ø5.6 mm, B Pin Code, Laser Diode | \$43.36 Volume Pricing Available | 3 Weeks |
| L785P090 | 785 nm, 90 mW, Ø5.6 mm, C Pin Code, Laser Diode | \$50.49 | Today |
| LD785-SEV300 | Customer Inspired! 785 nm, 300 mW, Ø9 mm TO Can, E Pin Code, VHG Wavelength-Stabilized Single-Frequency Laser Diode | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! CWL = 784.3 nm, P = 302.6 mW (I = 400 mA), 20 °C | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! CWL = 784.4 nm, P = 292.3 mW (I = 400 mA), 20 °C | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! CWL = 784.3 nm, P = 287.1 mW (I = 400 mA), 20 °C | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! CWL = 784.4 nm, P = 317.7 mW (I = 400 mA), 20 °C | \$1,640.53 | Today |
| LD785- | Customer Inspired! CWL = 784.4 nm, P = 304.3 mW (I = 400 mA), 20 °C | \$1,640.53 | Today |








| | | | |
|--------------|--|--------------------------------------|---------|
| SEV300 | | | |
| LD785-SEV300 | Customer Inspired! CWL = 784.5 nm, P = 296.3 mW (I = 400 mA),20 °C | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! | \$1,640.53 | Today |
| LD785-SEV300 | Customer Inspired! CWL = 784.4 nm, P = 294.3 mW (I = 400 mA),20 °C | \$1,640.53 | 3 Weeks |
| LD785-SEV300 | Customer Inspired! CWL = 784.5 nm, P = 302.2 mW (I = 400 mA),20 °C | \$1,640.53 | 3 Weeks |
| LD785-SH300 | 785 nm, 300 mW, Ø9 mm, H Pin Code, Laser Diode | \$333.81 Volume Pricing Available | 3 Weeks |
| LD785-SH300 | CWL = 787.8 nm, P = 300.0 mW (I = 369 mA), 25 °C | \$333.81 Volume Pricing Available | 3 Weeks |
| LD785-SH300 | CWL = 788.7 nm, P = 300.0 mW (I = 371 mA), 25 °C | \$333.81 Volume Pricing Available | 3 Weeks |
| LD785-SE400 | 785 nm, 400 mW, Ø9 mm, E Pin Code, Laser Diode | \$424.09 Volume Pricing Available | Today |
| LD785-SE400 | CWL = 787.7 nm, P = 400.0 mW (I = 532 mA), 25 °C | \$424.09 Volume Pricing Available | 3 Weeks |
| LD785-SE400 | CWL = 790.3 nm, P = 400.0 mW (I = 529 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD785-SE400 | CWL = 789.3 nm, P = 400.0 mW (I = 531 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD785-SE400 | CWL = 791.5 nm, P = 400.0 mW (I = 510 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD785-SE400 | CWL = 790.4 nm, P = 400.0 mW (I = 519 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD785-SE400 | CWL = 789.4 nm, P = 400.0 mW (I = 521 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD785-SE400 | CWL = 790.0 nm, P = 400.0 mW (I = 530 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| | | | |



| | | | |
|-------------|--|---|---------|
| LD785-SE400 | CWL = 790.9 nm, P = 400.0 mW (I = 526 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD785-SE400 | CWL = 789.8 nm, P = 400.0 mW (I = 542 mA), 25 °C | \$424.09 Volume Pricing Available | 3 Weeks |
| LD785-SE400 | CWL = 791.1 nm, P = 400.0 mW (I = 538 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD785-SE400 | | \$424.09 Volume Pricing Available | Today |
| LD785-SE400 | CWL = 790.6 nm, P = 400.0 mW (I = 527 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD785-SE400 | CWL = 790.9 nm, P = 400.0 mW (I = 521 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD785-SE400 | CWL = 790.0 nm, P = 400.0 mW (I = 532 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| L795VH1 | 795 nm, 0.25 mW, TO-46, H Pin Code, VCSEL Diode | \$164.67 | Today |

[Hide 808 nm TO Can Laser Diodes](#)

808 nm TO Can Laser Diodes

Note: The rows shaded green below denote single-frequency laser diodes.

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|---------------------------|---|------------|--------------------|---|--------------------|-------------|------------------------------------|----------------------|----------------------|-------------------------------|
| M9-808-0150 |  | 808 nm | 150 mW | 180 mA / 220 mA | Ø9 mm | A | Yes | S8060 or S8060-4 | No | Single Transverse Mode |
| L808P200 |  | 808 nm | 200 mW | 260 mA / 300 mA | Ø5.6 mm | A | Yes | S7060R | No | Multimode |
| L808H1 |  | 808 nm | 300 mW | 400 mA / 450 mA | Ø9 mm | H | No | S8060 or S8060-4 | Yes | Single Transverse Mode |
| L808P500MM |  | 808 nm | 500 mW | 650 mA / 700 mA | Ø5.6 mm | A | Yes | S7060R | No | Multimode |
| LD808-SE500 ^c |  | 808 nm | 500 mW | 750 mA / 800 mA | Ø9 mm ^d | E | No | S8060 or S8060-4 | Yes | Single Transverse Mode |
| LD808-SEV500 ^e |  | 808 nm | 500 mW | 800 mA (Max) ^f | Ø9 mm ^d | E | No | S8060 or S8060-4 | Yes | Single Frequency ^g |
| L808P1000MM |  | 808 nm | 1000 mW | 1100 mA / 1500 mA | Ø9 mm | E | No | S8060 or S8060-4 | No | Multimode |





















- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.
- c. This diode is exceptionally sensitive to optical feedback. Any reflection with more than 2% of the incident power has the potential to permanently damage the diode.
- d. The Ø9 mm package for this diode is 4.30 mm (0.17") thick, which is more than the standard Ø9 mm package thickness of 1.50 mm (0.06"). The diode will still be compatible with all Ø9 mm laser diode mounts; please see the *Drawing* tab in the blue info icon () above for full package specifications. Mounting this diode in the LDM90(/M) mount requires two 2-56 screws, included with this diode.
- e. In order to achieve the specified performance, we recommend using the LDM90(/M) Laser Diode Mount and, when collimated, an NIR Optical Isolator; single frequency performance when collimated is only guaranteed with >35 dB isolation of back reflections.
- f. The power can be tuned across the operating current range, given in the serial-number-specific documentation, while maintaining wavelength-stabilized, single-frequency performance within a stabilized temperature range.
- g. Single Longitudinal Mode and Single Transverse Mode



| Part Number | Description | Price | Availability |
|--------------|--|--|--------------|
| M9-808-0150 | 808 nm, 150 mW, Ø9 mm, A Pin Code, Laser Diode | \$536.95 Volume Pricing Available | Today |
| L808P200 | 808 nm, 200 mW, Ø5.6 mm, A Pin Code, MM, Laser Diode | \$76.03 Volume Pricing Available | Today |
| L808H1 | 808 nm, 300 mW, Ø9 mm, H Pin Code, Laser Diode | \$329.34 | Today |
| L808P500MM | 808 nm, 500 mW, Ø5.6 mm, A Pin Code, MM, Laser Diode | \$44.85 | Lead Time |
| LD808-SE500 | 808 nm, 500 mW, Ø9 mm, E Pin Code, Laser Diode | \$727.02 | Today |
| LD808-SE500 | CWL = 809.0 nm, P = 450.0 mW (I = 596 mA), 25 °C | \$727.02 | 3 Weeks |
| LD808-SE500 | CWL = 806.2 nm, P = 450.0 mW (I = 607 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 808.2 nm, P = 450.0 mW (I = 597 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 808.6 nm, P = 450.0 mW (I = 593 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 805.7 nm, P = 450.0 mW (I = 593 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 809.6 nm, P = 450.0 mW (I = 603 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 809.5 nm, P = 450.0 mW (I = 599 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 805.6 nm, P = 450.0 mW (I = 612 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 808.4 nm, P = 450.0 mW (I = 587 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 803.1 nm, P = 450.0 mW (I = 616 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 802.4 nm, P = 450.0 mW (I = 615 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 808.1 nm, P = 450.0 mW (I = 586 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 808.5 nm, P = 450.0 mW (I = 589 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 809.1 nm, P = 450.0 mW (I = 597 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 809.1 nm, P = 450.0 mW (I = 597 mA), 25 °C | \$727.02 | Today |
| LD808-SE500 | CWL = 809.3 nm, P = 450.0 mW (I = 603 mA), 25 °C | \$727.02 | Today |
| LD808-SEV500 | 808 nm, 500 mW, Ø9 mm TO Can, E Pin Code, VHG Wavelength-Stabilized Single-Frequency Laser Diode | \$1,761.69 Volume Pricing Available | Today |
| LD808-SEV500 | CWL = 808.2 nm, P = 567.6 mW (I = 750 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| LD808-SEV500 | CWL = 808.0 nm, P = 550.4 mW (I = 750 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| LD808-SEV500 | CWL = 807.9 nm, P = 552.4 mW (I = 750 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| LD808-SEV500 | CWL = 808.1 nm, P = 547.5 mW (I = 750 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| LD808-SEV500 | CWL = 807.8 nm, P = 541.8 mW (I = 750 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| LD808-SEV500 | CWL = 807.9 nm, P = 545.6 mW (I = 750 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| L808P1000MM | 808 nm, 1000 mW, Ø9 mm, E Pin Code, MM, Laser Diode | \$88.51 | Today |

[Hide 820 nm - 895 nm TO Can Laser Diodes](#)

820 nm - 895 nm TO Can Laser Diodes

Note: The rows shaded green below denote single-frequency laser diodes.

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|---------------------------|---|------------|--------------------|--|--------------------|----------|---------------------------------|-------------------|-------------------|-------------------------------|
| L820P100 |  | 820 nm | 100 mW | 145 mA / 210 mA | Ø5.6 mm | C | Yes | S7060R | No | Single Transverse Mode |
| L820P200 |  | 820 nm | 200 mW | 250 mA / 340 mA | Ø5.6 mm | C | Yes | S7060R | No | Single Transverse Mode |
| HL8338MG |  | 830 nm | 50 mW | 75 mA / 100 mA | Ø5.6 mm | C | Yes | S7060R | No | Single Transverse Mode |
| L830H1 |  | 830 nm | 250 mW | 400 mA (Max) | Ø9 mm | H | No | S8060 or S8060-4 | Yes | Single Transverse Mode |
| LD830-SE650 ^c |  | 830 nm | 650 mW | 900 mA / 1050 mA | Ø9 mm ^d | E | No | S8060 or S8060-4 | Yes | Single Transverse Mode |
| LD830-MA1W |  | 830 nm | 1000 mW | 2000 mA (Max) | Ø9 mm | A | Yes | S8060 or S8060-4 | Yes | Multimode |
| LD830-ME2W |  | 830 nm | 2000 mW | 3 A (Max) | Ø9 mm ^d | E | No | S8060 or S8060-4 | Yes | Multimode |
| L840P200 |  | 840 nm | 200 mW | 255 mA / 340 mA | Ø5.6 mm | C | Yes | S7060R | No | Single Transverse Mode |
| L850VH1 |  | 850 nm | 1 mW | 6 mA (Max) | TO-46 | H | No | S8060 | No | Single Frequency ^e |
| L850P010 |  | 850 nm | 10 mW | 50 mA / 70 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| L850P030 |  | 850 nm | 30 mW | 65 mA / 95 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| L852P50 |  | 852 nm | 50 mW | 75 mA / 100 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| L852P100 |  | 852 nm | 100 mW | 120 mA / 170 mA | Ø9 mm | A | Yes | S8060 or S8060-4 | No | Single Transverse Mode |
| L852P150 |  | 852 nm | 150 mW | 170 mA / 220 mA | Ø9 mm | A | Yes | S8060 or S8060-4 | No | Single Transverse Mode |
| L852SEV1 ^f |  | 852 nm | 270 mW | 350 mA / 400 mA ^g | Ø9 mm ^d | E | No | S8060 or S8060-4 | Yes | Single Frequency ^e |
| L852H1 |  | 852 nm | 300 mW | 415 mA (Max) | Ø9 mm | H | No | S8060 or S8060-4 | Yes | Single Transverse Mode |
| LD852-SE600 ^c |  | 852 nm | 600 mW | 950 mA / 1050 mA | Ø9 mm ^d | E | No | S8060 or S8060-4 | Yes | Single Transverse Mode |
| LD852-SEV600 ^f |  | 852 nm | 600 mW | 1050 mA (Max) ^g | Ø9 mm ^d | E | No | S8060 or S8060-4 | Yes | Single Frequency ^e |
| L880P010 |  | 880 nm | 10 mW | 30 mA / 40 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| L895VH1 |  | 895 nm | 0.2 mW | 1.4 mA / 2.0 mA | TO-46 | H | No | S8060 or S8060-4 | No | Single Frequency ^e |

- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.
- c. This diode is exceptionally sensitive to optical feedback. Any reflection with more than 2% of the incident power has the potential to permanently damage the diode.
- d. The Ø9 mm package for this diode is 4.30 mm (0.17") thick, which is more than the standard Ø9 mm package thickness of 1.50 mm (0.06"). The diode will still be compatible with all Ø9 mm laser diode mounts; please see the *Drawing* tab in the blue info icon () above for full package specifications. Mounting this diode in the LDM90(/M) mount requires two 2-56 screws, included with this diode.
- e. Single Longitudinal Mode and Single Transverse Mode
- f. In order to achieve the specified performance, we recommend using the LDM90(/M) Laser Diode Mount and, when collimated, an NIR Optical Isolator; single frequency performance when collimated is only guaranteed with >35 dB isolation of back reflections.
- g. The power can be tuned across the operating current range, given in the serial-number-specific documentation, while maintaining wavelength-stabilized, single-frequency performance within a stabilized temperature range.

| Part Number | Description | Price | Availability |
|-------------|--|--------------------------------------|--------------|
| L820P100 | 820 nm, 100 mW, Ø5.6 mm, C Pin Code, Laser Diode | \$49.90 | Today |
| L820P200 | 820 nm, 200 mW, Ø5.6 mm, C Pin Code, Laser Diode | \$99.50 | Today |
| HL8338MG | 830 nm, 50 mW, Ø5.6 mm, C Pin Code, Laser Diode | \$65.93 Volume Pricing Available | Today |
| L830H1 | 830 nm, 250 mW, Ø9 mm, H Pin Code, Laser Diode | \$274.44 | Today |
| LD830-SE650 | 830 nm, 650 mW, Ø9 mm, E Pin Code, Laser Diode | \$424.09 Volume Pricing Available | Today |
| LD830-SE650 | CWL = 833.0 nm, P = 650.0 mW (I = 895 mA), 25 °C | \$424.09 Volume Pricing Available | 3 Weeks |
| LD830-SE650 | CWL = 833.1 nm, P = 650.0 mW (I = 896 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD830-SE650 | CWL = 833.4 nm, P = 650.0 mW (I = 916 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD830-SE650 | CWL = 833.1 nm, P = 650.0 mW (I = 923 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD830-SE650 | CWL = 832.5 nm, P = 650.0 mW (I = 915 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD830-SE650 | CWL = 833.1 nm, P = 650.0 mW (I = 960 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD830-SE650 | CWL = 832.6 nm, P = 650.0 mW (I = 909 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD830-SE650 | CWL = 833.6 nm, P = 650.0 mW (I = 911 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD830-SE650 | CWL = 832.8 nm, P = 650.0 mW (I = 896 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD830-SE650 | CWL = 831.6 nm, P = 650.0 mW (I = 925 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD830-SE650 | CWL = 832.5 nm, P = 650.0 mW (I = 896 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD830-SE650 | CWL = 833.0 nm, P = 650.0 mW (I = 877 mA), 25 °C | \$424.09 Volume Pricing Available | Today |
| LD830-MA1W | 830 nm, 1 W, Ø9 mm, A Pin Code, MM, Laser Diode | \$302.92 | Today |
| LD830-ME2W | 830 nm, 2 W, Ø9 mm, E Pin Code, MM, Laser Diode | \$605.84 | Today |
| LD830-ME2W | CWL = 832.7 nm, P = 2000.0 mW (I = 2500 mA), 25 °C | \$605.84 | 3 Weeks |
| LD830-ME2W | CWL = 832.8 nm, P = 2000.0 mW (I = 2501 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 833.6 nm, P = 2000.0 mW (I = 2500 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 833.4 nm, P = 2000.0 mW (I = 2465 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 833.3 nm, P = 2000.0 mW (I = 2484 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 833.0 nm, P = 2000.0 mW (I = 2492 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 833.1 nm, P = 2000.0 mW (I = 2486 mA), 25 °C | \$605.84 | Today |




| | | | |
|------------|--|--------------------------------------|---------|
| LD830-ME2W | CWL = 833.4 nm, P = 2000.0 mW (I = 2501 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 832.8 nm, P = 2000.0 mW (I = 2477 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 832.3 nm, P = 2000.0 mW (I = 2499 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 832.7 nm, P = 2000.0 mW (I = 2479 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 832.8 nm, P = 2000.0 mW (I = 2480 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 832.8 nm, P = 2000.0 mW (I = 2482 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 832.1 nm, P = 2000.0 mW (I = 2455 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 833.2 nm, P = 2000.0 mW (I = 2472 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 832.1 nm, P = 2000.0 mW (I = 2461 mA), 25 °C | \$605.84 | Today |
| LD830-ME2W | CWL = 833.2 nm, P = 2000.0 mW (I = 2474 mA), 25 °C | \$605.84 | Today |
| L840P200 | 840 nm, 200 mW, Ø5.6 mm, C Pin Code, Laser Diode | \$54.16 | Today |
| L850VH1 | 850 nm, 1 mW, TO-46, H Pin Code, VCSEL Diode | \$164.67 | Today |
| L850P010 | 850 nm, 10 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$27.45 Volume Pricing Available | Today |
| L850P030 | 850 nm, 30 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$103.05 Volume Pricing Available | Today |
| L852P50 | 852 nm, 50 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$172.25 Volume Pricing Available | Today |
| L852P100 | 852 nm, 100 mW, Ø9 mm, A Pin Code, Laser Diode | \$228.08 Volume Pricing Available | Today |
| L852P150 | 852 nm, 150 mW, Ø9 mm, A Pin Code, Laser Diode | \$336.19 Volume Pricing Available | Today |
| L852SEV1 | 852 nm, 270 mW, Ø9 mm TO Can, E Pin Code, VHG Wavelength-Stabilized Single-Frequency Laser Diode | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.5 nm, P = 247.3 mW (I = 350 mA),25 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.9 nm, P = 272.0 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.6 nm, P = 248.8 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.6 nm, P = 246.8 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 853.0 nm, P = 267.5 mW (I = 350 mA),32 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.7 nm, P = 267.9 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.9 nm, P = 264.5 mW (I = 350 mA),32 °C | \$1,000.00 | 3 Weeks |
| L852SEV1 | CWL = 852.9 nm, P = 264.5 mW (I = 350 mA),32 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.6 nm, P = 265.9 mW (I = 350 mA),27 °C | \$1,000.00 | 3 Weeks |
| L852SEV1 | CWL = 852.7 nm, P = 262.2 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.9 nm, P = 260.4 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.7 nm, P = 258.0 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.9 nm, P = 254.5 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.9 nm, P = 265.5 mW (I = 350 mA),32 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.7 nm, P = 252.3 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 853.0 nm, P = 255.2 mW (I = 350 mA),32 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.9 nm, P = 268.2 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.9 nm, P = 277.8 mW (I = 350 mA),33 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.8 nm, P = 257.7 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 852.7 nm, P = 276.0 mW (I = 350 mA),27 °C | \$1,000.00 | Today |
| L852SEV1 | CWL = 853.0 nm, P = 278.3 mW (I = 350 mA),33 °C | \$1,000.00 | Today |
| L852H1 | 852 nm, 300 mW, Ø9 mm, H Pin Code, Laser Diode | \$384.22 | Today |
| | | | |


| | | | |
|-------------|--|---|-------|
| LD852-SE600 | 852 nm, 600 mW, Ø9 mm, E Pin Code, Laser Diode | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 855.9 nm, P = 600.0 mW (I = 942 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 856.4 nm, P = 600.0 mW (I = 940 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 856.5 nm, P = 600.0 mW (I = 931 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 856.1 nm, P = 600.0 mW (I = 944 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.7 nm, P = 600.0 mW (I = 924 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.0 nm, P = 600.0 mW (I = 936 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.3 nm, P = 600.0 mW (I = 925 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 852.7 nm, P = 600.0 mW (I = 948 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.0 nm, P = 600.0 mW (I = 948 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.6 nm, P = 600.0 mW (I = 940 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.4 nm, P = 600.0 mW (I = 919 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.7 nm, P = 600.0 mW (I = 923 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 852.9 nm, P = 600.0 mW (I = 938 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.5 nm, P = 600.0 mW (I = 930 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 854.0 nm, P = 600.0 mW (I = 918 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 854.6 nm, P = 600.0 mW (I = 947 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.6 nm, P = 600.0 mW (I = 961 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.9 nm, P = 600.0 mW (I = 935 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| | | \$727.02 | |

| | | | |
|--------------|--|--|-------|
| LD852-SE600 | CWL = 852.7 nm, P = 600.0 mW (I = 936 mA), 25 °C | Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.7 nm, P = 600.0 mW (I = 929 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 856.6 nm, P = 600.0 mW (I = 979 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 854.3 nm, P = 600.0 mW (I = 935 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SE600 | CWL = 853.9 nm, P = 600.0 mW (I = 916 mA), 25 °C | \$727.02 Volume Pricing Available | Today |
| LD852-SEV600 | 852 nm, 600 mW, Ø9 mm TO Can, E Pin Code, VHG Wavelength-Stabilized Single-Frequency Laser Diode | \$1,761.69 Volume Pricing Available | Today |
| LD852-SEV600 | CWL = 852.5 nm, P = 603.1 mW (I = 970 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| LD852-SEV600 | CWL = 852.2 nm, P = 590.0 mW (I = 970 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| LD852-SEV600 | CWL = 852.9 nm, P = 631.5 mW (I = 970 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| LD852-SEV600 | CWL = 852.6 nm, P = 586.7 mW (I = 970 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| LD852-SEV600 | CWL = 852.9 nm, P = 593.0 mW (I = 970 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| LD852-SEV600 | CWL = 852.8 nm, P = 595.1 mW (I = 970 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| LD852-SEV600 | CWL = 852.5 nm, P = 563.5 mW (I = 970 mA),25 °C | \$1,761.69 Volume Pricing Available | Today |
| L880P010 | 880 nm, 10 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$58.21 Volume Pricing Available | Today |
| L895VH1 | 895 nm, 0.2 mW, H Pin Code, VCSEL Diode | \$164.67 | Today |

[Hide 904 nm - 960 nm TO Can Laser Diodes](#)

904 nm - 960 nm TO Can Laser Diodes

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|-------------|---|------------|--------------------|--|---------|----------|---------------------------------|-------------------|-------------------|------------------------|
| L904P010 |  | 904 nm | 10 mW | 50 mA / 70 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| M9-940-0200 |  | 940 nm | 200 mW | 270 mA / 320 mA | Ø9 mm | A | Yes | S8060 or S8060-4 | No | Single Transverse Mode |
| L960H1 |  | 960 nm | 250 mW | 400 mA / 430 mA | Ø9 mm | H | No | S8060 or S8060-4 | Yes | Single Transverse Mode |







- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.



| Part Number | Description | Price | Availability |
|-------------|---|--------------------------------------|--------------|
| L904P010 | 904 nm, 10 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$30.28 Volume Pricing Available | Today |
| M9-940-0200 | 940 nm, 200 mW, Ø9 mm, A Pin Code, Laser Diode | \$687.81 Volume Pricing Available | Today |
| L960H1 | 960 nm, 250 mW, Ø9 mm, H Pin Code, Laser Diode | \$274.44 Volume Pricing Available | Today |

[Hide 976 nm - 980 nm TO Can Laser Diodes](#)

976 nm - 980 nm TO Can Laser Diodes

Note: The rows shaded green below denote single-frequency laser diodes.

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|-----------------------|---|------------|--------------------|--|--------------------|----------|---------------------------------|-------------------|-------------------|-------------------------------------|
| L976SEV1 ^c |  | 976 nm | 270 mW | 350 mA / 400 mA ^d | Ø9 mm ^e | E | No | S8060 or S8060-4 | Yes | Single Frequency ^f |
| L980P010 |  | 980 nm | 10 mW | 25 mA / 40 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| L980P030 |  | 980 nm | 30 mW | 50 mA / 70 mA | Ø5.6 mm | A | Yes | S7060R | No | Single Transverse Mode |
| L980P100A |  | 980 nm | 100 mW | 150 mA / 190 mA | Ø5.6 mm | A | Yes | S7060R | No | Multimode |
| L980H1 |  | 980 nm | 200 mW | 300 mA (Max) | Ø9 mm | H | No | S8060 or S8060-4 | Yes | Single Transverse Mode ^g |
| L980P200 |  | 980 nm | 200 mW | 300 mA / 400 mA | Ø5.6 mm | A | Yes | S7060R | No | Multimode |



- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.
- c. In order to achieve the specified performance, we recommend using the LDM90(/M) Laser Diode Mount and, when collimated, an NIR Optical Isolator; single frequency performance when collimated is only guaranteed with >35 dB isolation of back reflections.
- d. The power can be tuned across the operating current range, given in the serial-number-specific documentation, while maintaining wavelength-stabilized, single-frequency performance within a stabilized temperature range.
- e. The Ø9 mm package for this diode is 4.30 mm (0.17") thick, which is more than the standard Ø9 mm package thickness of 1.50 mm (0.06"). The diode will still be compatible with all Ø9 mm laser diode mounts; please see the *Drawing* tab in the blue info icon () above for full package specifications. Mounting this diode in the LDM90(/M) mount requires two 2-56 screws, included with this diode.
- f. Single Longitudinal Mode and Single Transverse Mode
- g. At least 90% of the output power is within a single transverse mode.


| Part Number | Description | Price | Availability |
|-------------|--|------------|--------------|
| L976SEV1 | 976 nm, 270 mW, Ø9 mm TO Can, E Pin Code, VHG Wavelength-Stabilized Single-Frequency Laser Diode | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.7 nm, P = 262.5 mW (I = 350 mA),27 °C | \$1,530.00 | 3 Weeks |
| L976SEV1 | CWL = 976.2 nm, P = 248.9 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.3 nm, P = 245.9 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.5 nm, P = 251.5 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.6 nm, P = 263.6 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.5 nm, P = 255.9 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.3 nm, P = 254.8 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.2 nm, P = 245.3 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.3 nm, P = 245.9 mW (I = 350 mA),35 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.0 nm, P = 259.3 mW (I = 350 mA),25 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.6 nm, P = 263.4 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.4 nm, P = 233.4 mW (I = 350 mA),35 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.5 nm, P = 262.6 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.7 nm, P = 257.0 mW (I = 350 mA),35 °C | \$1,530.00 | Today |

| | | | |
|-----------|--|--------------------------------------|-------|
| L976SEV1 | CWL = 976.7 nm, P = 229.4 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.5 nm, P = 267.2 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L976SEV1 | CWL = 976.6 nm, P = 257.5 mW (I = 350 mA),27 °C | \$1,530.00 | Today |
| L980P010 | 980 nm, 10 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$31.77 Volume Pricing Available | Today |
| L980P030 | 980 nm, 30 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$78.70 Volume Pricing Available | Today |
| L980P100A | 980 nm, 100 mW, Ø5.6 mm, A Pin Code, MM, Laser Diode | \$124.73 Volume Pricing Available | Today |
| L980H1 | 980 nm, 200 mW, Ø9 mm, H Pin Code, Laser Diode | \$274.44 | Today |
| L980P200 | 980 nm, 200 mW, Ø5.6 mm, A Pin Code, Laser Diode | \$158.00 Volume Pricing Available | Today |

[Hide 1064 nm TO Can Laser Diodes](#)

1064 nm TO Can Laser Diodes

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|-------------|---|------------|--------------------|--|---------|----------|---------------------------------|-------------------|-------------------|------------------------|
| M9-A64-0200 |  | 1064 nm | 200 mW | 280 mA / 350 mA | Ø9 mm | A | Yes | S8060 or S8060-4 | No | Single Transverse Mode |
| L1064H1 |  | 1064 nm | 300 mW | 700 mA / 900 mA | Ø9 mm | H | No | S8060 or S8060-4 | Yes | Single Transverse Mode |
| L1064H2 |  | 1064 nm | 450 mW | 1100 mA / 1200 mA | Ø9 mm | E | No | S8060 or S8060-4 | No | Single Transverse Mode |

- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.




| Part Number | Description | Price | Availability |
|-------------|---|--------------------------------------|--------------|
| M9-A64-0200 | 1064 nm, 200 mW, Ø9 mm, A Pin Code, Laser Diode | \$496.55 Volume Pricing Available | Today |
| L1064H1 | 1064 nm, 300 mW, Ø9 mm, H Pin Code, Laser Diode | \$274.44 | Today |
| L1064H2 | 1064 nm, 450 mW, Ø9 mm, E Pin Code, Laser Diode | \$494.00 | Today |


[Hide 1270 nm - 1480 nm TO Can Laser Diodes](#)


1270 nm - 1480 nm TO Can Laser Diodes



Note: The rows shaded green below denote single-frequency laser diodes.

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|-------------------------|---|------------|--------------------|--|---------|----------|---------------------------------|-------------------|-------------------|-------------------------------|
| L1270P5DFB ^c |  | 1270 nm | 5 mW | 15 mA / 40 mA | Ø5.6 mm | D | Yes | - | Yes | Single Frequency ^d |
| L1290P5DFB ^c |  | 1290 nm | 5 mW | 16 mA / 40 mA | Ø5.6 mm | D | Yes | - | Yes | Single Frequency ^d |
| L1310P5DFB ^c |  | 1310 nm | 5 mW | 16 mA / 40 mA | Ø5.6 mm | D | Yes | - | Yes | Single Frequency ^d |

| | | | | | | | | | | |
|-------------------------------|---|---------|-----------------|------------------|---------|---|-----|------------------|-----|-------------------------------|
| FPL1053T^e |  | 1310 nm | 300 mW (Pulsed) | 750 mA / 1000 mA | Ø5.6 mm | E | No | S7060R | No | Single Transverse Mode |
| L1310G1 |  | 1310 nm | 2000 mW | 5 A / 8 A | Ø9 mm | G | No | S8060 or S8060-4 | No | Multimode |
| L1330P5DFB^c |  | 1330 nm | 5 mW | 14 mA / 40 mA | Ø5.6 mm | D | Yes | - | Yes | Single Frequency ^d |
| L1370G1 |  | 1370 nm | 2000 mW | 5 A / 8 A | Ø9 mm | G | No | S8060 or S8060-4 | No | Multimode |
| L1450G1 |  | 1450 nm | 2000 mW | 5 A / 8 A | Ø9 mm | G | No | S8060 or S8060-4 | No | Multimode |
| L1470P5DFB^c |  | 1470 nm | 5 mW | 19 mA / 40 mA | Ø5.6 mm | D | Yes | - | Yes | Single Frequency ^d |
| L1480G1 |  | 1480 nm | 2000 mW | 5 A / 8 A | Ø9 mm | G | No | S8060 or S8060-4 | No | Multimode |

- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.
- c. This diode includes an integrated aspheric focusing lens in the cap, allowing for the focus spot and numerical aperture to be matched to SMF-28e+ fiber.
- d. Single Longitudinal Mode and Single Transverse Mode
- e. This diode is available from stock in an open header package. It can be converted to a sealed TO can package by customer request. Please contact Tech Support for details.




| Part Number | Description | Price | Availability |
|-------------------|---|-------------------------------------|--------------|
| L1310P5DFB | 1310 nm, 5 mW, Ø5.6 mm, D Pin Code, DFB Laser Diode with Aspheric Lens Cap | \$92.36 Volume Pricing Available | Today |
| L1270P5DFB | Customer Inspired! 1270 nm, 5 mW, Ø5.6 mm, D Pin Code, DFB Laser Diode with Aspheric Lens Cap | \$92.36 Volume Pricing Available | Today |
| L1290P5DFB | Customer Inspired! 1290 nm, 5 mW, Ø5.6 mm, D Pin Code, DFB Laser Diode with Aspheric Lens Cap | \$92.36 Volume Pricing Available | Today |
| FPL1053T | 1310 nm, 300 mW Pulsed, Ø5.6 mm, E Pin Code | \$424.09 | Today |
| L1310G1 | 1310 nm, 2.0 W, Ø9 mm, G Pin Code, MM Laser Diode | \$350.55 | Today |
| L1330P5DFB | Customer Inspired! 1330 nm, 5 mW, Ø5.6 mm, D Pin Code, DFB Laser Diode With Aspheric Lens Cap | \$92.36 Volume Pricing Available | Today |
| L1370G1 | 1370 nm, 2.0 W, Ø9 mm, G Pin Code, MM Laser Diode | \$378.50 | Today |
| L1450G1 | 1450 nm, 2.0 W, Ø9 mm, G Pin Code, MM Laser Diode | \$351.72 | Today |
| L1470P5DFB | 1470 nm, 5 mW, Ø5.6 mm, D Pin Code, DFB Laser Diode with Aspheric Lens Cap | \$92.36 Volume Pricing Available | Today |
| L1480G1 | 1480 nm, 2.0 W, Ø9 mm, G Pin Code, MM Laser Diode | \$354.04 | Today |


[Hide 1490 nm - 1650 nm TO Can Laser Diodes](#)


1490 nm - 1650 nm TO Can Laser Diodes



Note: The rows shaded green below denote single-frequency laser diodes.

| Item # | Info | Wavelength | Power ^a | Typical/Max Drive Current ^a | Package | Pin Code | Monitor Photodiode ^b | Compatible Socket | Wavelength Tested | Laser Mode |
|-------------------------------|---|------------|--------------------|--|---------|----------|---------------------------------|-------------------|-------------------|-------------------------------|
| L1490P5DFB^c |  | 1490 nm | 5 mW | 24 mA / 40 mA | Ø5.6 mm | D | Yes | - | Yes | Single Frequency ^d |
| L1510P5DFB^c |  | 1510 nm | 5 mW | 20 mA / 40 mA | Ø5.6 mm | D | Yes | - | Yes | Single Frequency ^d |
| L1530P5DFB^c |  | 1530 nm | 5 mW | 21 mA / 40 mA | Ø5.6 mm | D | Yes | - | Yes | Single Frequency ^d |

| | | | | | | | | | | |
|-------------------------------|---|---------|-----------------|------------------|---------|---|-----|------------------|-----|-------------------------------|
| L1550P5DFB^c |  | 1550 nm | 5 mW | 20 mA / 40 mA | Ø5.6 mm | D | Yes | - | Yes | Single Frequency ^d |
| ML925B45F |  | 1550 nm | 5 mW | 30 mA / 50 mA | Ø5.6 mm | D | Yes | - | No | Single Transverse Mode |
| FPL1055T^e |  | 1550 nm | 300 mW (Pulsed) | 750 mA / 1000 mA | Ø5.6 mm | E | No | S7060R | No | Single Transverse Mode |
| L1550G1 |  | 1550 nm | 1700 mW | 5 A / 8 A | Ø9 mm | G | No | S8060 or S8060-4 | No | Multimode |
| L1570P5DFB^c |  | 1570 nm | 5 mW | 25 mA / 40 mA | Ø5.6 mm | D | Yes | - | Yes | Single Frequency ^d |
| L1575G1 |  | 1575 nm | 1700 mW | 5 A / 8 A | Ø9 mm | G | No | S8060 or S8060-4 | No | Multimode |
| FPL1054T^e |  | 1625 nm | 200 mW (Pulsed) | 750 mA / 1000 mA | Ø5.6 mm | E | No | S7060R | No | Single Transverse Mode |
| FPL1059T^e |  | 1650 nm | 225 mW (Pulsed) | 750 mA / 1000 mA | Ø5.6 mm | E | No | S7060R | No | Single Transverse Mode |


- a. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- b. Laser diodes with a built-in monitor photodiode can operate at constant power.
- c. This diode includes an integrated aspheric focusing lens in the cap, allowing for the focus spot and numerical aperture to be matched to SMF-28e+ fiber.
- d. Single Longitudinal Mode and Single Transverse Mode
- e. This diode is available from stock in an open header package. It can be converted to a sealed TO can package by customer request. Please contact Tech Support for details.

| Part Number | Description | Price | Availability |
|-------------------|--|--|--------------|
| L1550P5DFB | 1550 nm, 5 mW, Ø5.6 mm, D Pin Code, DFB Laser Diode with Aspheric Lens Cap | \$92.36 Volume Pricing Available | Today |
| L1490P5DFB | 1490 nm, 5 mW, Ø5.6 mm, D Pin Code, DFB Laser Diode with Aspheric Lens Cap | \$92.36 Volume Pricing Available | Today |
| L1510P5DFB | 1510 nm, 5 mW, Ø5.6 mm, D Pin Code, DFB Laser Diode with Aspheric Lens Cap | \$92.36 Volume Pricing Available | Today |
| L1530P5DFB | 1530 nm, 5 mW, Ø5.6 mm, D Pin Code, DFB Laser Diode with Aspheric Lens Cap | \$92.36 Volume Pricing Available | Today |
| ML925B45F | 1550 nm, 5 mW, Ø5.6 mm, D Pin Code, Laser Diode | \$57.61 Volume Pricing Available | Today |
| FPL1055T | 1550 nm, 300 mW Pulsed, Ø5.6 mm, E Pin Code | \$424.09 | Today |
| L1550G1 | 1550 nm, 1.7 W, Ø9 mm, G Pin Code, MM Laser Diode | \$355.20 | Today |
| L1570P5DFB | 1570 nm, 5 mW, Ø5.6 mm, D Pin Code, DFB Laser Diode with Aspheric Lens Cap | \$92.36 Volume Pricing Available | Today |
| L1575G1 | 1575 nm, 1.7 W, Ø9 mm, G Pin Code, MM Laser Diode | \$356.39 | Today |
| FPL1054T | 1625 nm, 200 mW Pulsed, Ø5.6 mm, E Pin Code | \$466.86 | Today |
| FPL1059T | 1650 nm, 225 mW Pulsed, Ø5.6 mm, E Pin Code | \$509.62 | Today |

[Hide 3.40 µm TO Can Fabry-Perot ICL](#)

3.40 µm TO Can Fabry-Perot ICL

| Item # | Info | Center Wavelength ^a | Power (Min) ^b | Max Operating Current ^b | Package ^c | Pin Code | Monitor Photodiode | Wavelength Tested | Laser Mode |
|----------|---|----------------------------------|--------------------------|------------------------------------|----------------------|----------|--------------------|-------------------|------------------------|
| IF3400T1 |  | 3.40 µm (2941 cm ⁻¹) | 30 mW | 600 mA | Ø9 mm | H | No | Yes | Single Transverse Mode |

- a. Fabry-Perot Lasers exhibit broadband emission. The center wavelength is defined as a weighted average over all the modes. Each device has a unique spectrum. To get the spectrum of a specific, serial-numbered device, click "Choose Item" below, then click on the Docs Icon next to the serial number of the device. If you need spectral characteristics different than those shown below, please contact Tech Support to request a custom laser.
- b. Please see the blue info icons () above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.

c. The Ø9 mm package for these diodes is 4.3 mm (0.17") thick, which is more than the standard 1.5 mm (0.06"). The laser will still be compatible with all Ø9 mm laser mounts; please see the *Drawing* tab in the blue info icon (i) above for full package specifications.

| Part Number | Description | Price | Availability |
|-------------|--|------------|--------------|
| IF3400T1 | Fabry-Perot Interband Cascade Laser, 3.40 µm CWL, 30 mW, Ø9 mm, H Pin Code | \$4,285.00 | Today |
| IF3400T1 | Center Wavelength: 3.26 µm, 30 mW (356 mA), 25 °C | \$4,285.00 | Today |
| IF3400T1 | Center Wavelength: 3.22 µm, 30 mW (298 mA), 25 °C | \$4,285.00 | Today |
| IF3400T1 | Center Wavelength: 3.23 µm, 30 mW (291 mA), 25 °C | \$4,285.00 | Today |
| IF3400T1 | Center Wavelength: 3.23 µm, 30 mW (265 mA), 25 °C | \$4,285.00 | Today |
| IF3400T1 | Center Wavelength: 3.24 µm, 30 mW (384 mA), 25 °C | \$4,285.00 | Today |
| IF3400T1 | Center Wavelength: 3.23 µm, 30 mW (365 mA), 25 °C | \$4,285.00 | Today |
| IF3400T1 | Center Wavelength: 3.24 µm, 30 mW (298 mA), 25 °C | \$4,285.00 | 3 Weeks |

[Hide 3.85 µm - 9.5 µm TO Can Fabry-Perot QCLs](#)

3.85 µm - 9.5 µm TO Can Fabry-Perot QCLs

| Item # | Info | Center Wavelength ^a | Power (Min) ^b | Max Operating Current ^b | Package ^c | Pin Code | Monitor Photodiode | Wavelength Tested | Laser Mode |
|----------|------|----------------------------------|--------------------------|------------------------------------|----------------------|----------|--------------------|-------------------|------------------------|
| QF3850T1 | i | 3.85 µm (2597 cm ⁻¹) | 200 mW | 600 mA | Ø9 mm | H | No | Yes | Single Transverse Mode |
| QF4050T2 | i | 4.05 µm (2469 cm ⁻¹) | 70 mW | 400 mA | Ø9 mm | H | No | Yes | Single Transverse Mode |
| QF4050T1 | i | 4.05 µm (2469 cm ⁻¹) | 300 mW | 600 mA | Ø9 mm | H | No | Yes | Single Transverse Mode |
| QF4600T2 | i | 4.60 µm (2174 cm ⁻¹) | 200 mW | 500 mA | Ø9 mm | H | No | Yes | Single Transverse Mode |
| QF4600T1 | i | 4.60 µm (2174 cm ⁻¹) | 400 mW | 800 mA | Ø9 mm | H | No | Yes | Single Transverse Mode |
| QF4600T3 | i | 4.60 µm (2174 cm ⁻¹) | 1000 mW | 800 mA | Ø9 mm | H | No | Yes | Single Transverse Mode |
| QF9500T1 | i | 9.5 µm (1053 cm ⁻¹) | 300 mW | 800 mA | Ø9 mm | H | No | Yes | Single Transverse Mode |

- a. Fabry-Perot Lasers exhibit broadband emission. The center wavelength is defined as a weighted average over all the modes. Each device has a unique spectrum. To get the spectrum of a specific, serial-numbered device, click "Choose Item" below, then click on the Docs Icon next to the serial number of the device. If you need spectral characteristics different than those shown below, please contact Tech Support to request a custom laser.
- b. Please see the blue info icons (i) above for absolute maximum power and current specifications. Do not exceed these values, whichever occurs first.
- c. The Ø9 mm package for these diodes is 4.3 mm (0.17") thick, which is more than the standard 1.5 mm (0.06"). The laser will still be compatible with all Ø9 mm laser mounts; please see the *Drawing* tab in the blue info icon (i) above for full package specifications

| Part Number | Description | Price | Availability |
|-------------|---|--|--------------|
| QF3850T1 | Fabry-Perot Quantum Cascade Laser, 3.85 µm CWL, 200 mW, Ø9 mm, H Pin Code | \$3,860.96 Volume Pricing Available | Today |
| QF3850T1 | Center Wavelength: 3.86 µm, 200 mW (368 mA), 25 °C | \$3,860.96 Volume Pricing Available | Today |
| QF4050T2 | Fabry-Perot Quantum Cascade Laser, 4.05 µm CWL, 70 mW, Ø9 mm, H Pin Code | \$1,606.50 | Today |
| QF4050T2 | Center Wavelength: 3.93 µm, 70 mW (218 mA), 25 °C | \$1,606.50 | Today |
| QF4050T2 | Center Wavelength: 3.94 µm, 70 mW (210 mA), 25 °C | \$1,606.50 | Today |
| QF4050T2 | Center Wavelength: 4.01 µm, 70 mW (228 mA), 25 °C | \$1,606.50 | 3 Weeks |
| QF4050T2 | Center Wavelength: 4.02 µm, 70 mW (251 mA), 25 °C | \$1,606.50 | 3 Weeks |

| | | | |
|----------|---|--|-----------|
| QF4050T2 | Center Wavelength: 4.02 μm , 70 mW (187 mA), 25 $^{\circ}\text{C}$ | \$1,606.50 | 3 Weeks |
| QF4050T1 | Fabry-Perot Quantum Cascade Laser, 4.05 μm CWL, 300 mW, Ø9 mm, H Pin Code | \$3,860.96 Volume Pricing Available | Today |
| QF4050T1 | Center Wavelength: 3.96 μm , 300 mW (415 mA), 25 $^{\circ}\text{C}$ | \$3,860.96 Volume Pricing Available | Today |
| QF4050T1 | Center Wavelength: 3.99 μm , 300 mW (468 mA), 25 $^{\circ}\text{C}$ | \$3,860.96 Volume Pricing Available | Today |
| QF4050T1 | Center Wavelength: 3.96 μm , 300 mW (381 mA), 25 $^{\circ}\text{C}$ | \$3,860.96 Volume Pricing Available | Today |
| QF4050T1 | Center Wavelength: 3.95 μm , 300 mW (427 mA), 25 $^{\circ}\text{C}$ | \$3,860.96 Volume Pricing Available | Today |
| QF4050T1 | Center Wavelength: 3.95 μm , 300 mW (395 mA), 25 $^{\circ}\text{C}$ | \$3,860.96 Volume Pricing Available | Today |
| QF4600T2 | Fabry-Perot Quantum Cascade Laser, 4.60 μm CWL, 200 mW, Ø9 mm, H Pin Code | \$1,981.35 Volume Pricing Available | Today |
| QF4600T2 | Center Wavelength: 4.56 μm , 200 mW (274 mA), 25 $^{\circ}\text{C}$ | \$1,981.35 Volume Pricing Available | 3 Weeks |
| QF4600T2 | Center Wavelength: 4.55 μm , 200 mW (278 mA), 25 $^{\circ}\text{C}$ | \$1,981.35 Volume Pricing Available | 3 Weeks |
| QF4600T2 | Center Wavelength: 4.55 μm , 200 mW (283 mA), 25 $^{\circ}\text{C}$ | \$1,981.35 Volume Pricing Available | Today |
| QF4600T2 | Center Wavelength: 4.56 μm , 200 mW (271 mA), 25 $^{\circ}\text{C}$ | \$1,981.35 Volume Pricing Available | Today |
| QF4600T2 | Center Wavelength: 4.55 μm , 200 mW (323 mA), 25 $^{\circ}\text{C}$ | \$1,981.35 Volume Pricing Available | Today |
| QF4600T2 | Center Wavelength: 4.56 μm , 200 mW (279 mA), 25 $^{\circ}\text{C}$ | \$1,981.35 Volume Pricing Available | Today |
| QF4600T2 | Center Wavelength: 4.56 μm , 200 mW (279 mA), 25 $^{\circ}\text{C}$ | \$1,981.35 Volume Pricing Available | Today |
| QF4600T1 | Fabry-Perot Quantum Cascade Laser, 4.60 μm CWL, 400 mW, Ø9 mm, H Pin Code | \$3,860.96 Volume Pricing Available | Today |
| QF4600T1 | Center Wavelength: 4.53 μm , 400 mW (518 mA), 25 $^{\circ}\text{C}$ | \$3,860.96 Volume Pricing Available | 3 Weeks |
| QF4600T1 | Center Wavelength: 4.59 μm , 400 mW (319 mA), 25 $^{\circ}\text{C}$ | \$3,860.96 Volume Pricing Available | Today |
| QF4600T1 | Center Wavelength: 4.60 μm , 400 mW (341 mA), 25 $^{\circ}\text{C}$ | \$3,860.96 Volume Pricing Available | Today |
| QF4600T1 | Center Wavelength: 4.61 μm , 400 mW (327 mA), 25 $^{\circ}\text{C}$ | \$3,860.96 Volume Pricing Available | Today |
| QF4600T1 | Center Wavelength: 4.61 μm , 400 mW (380 mA), 25 $^{\circ}\text{C}$ | \$3,860.96 Volume Pricing Available | Today |
| QF4600T3 | Fabry-Perot Quantum Cascade Laser, 4.60 μm CWL, 1000 mW, Ø9 mm, H Pin Code | \$5,997.60 Volume Pricing Available | Today |
| QF4600T3 | Center Wavelength: 4.62 μm , 1000 mW (610 mA), 25 $^{\circ}\text{C}$ | \$5,997.60 Volume Pricing Available | 3 Weeks |
| QF4600T3 | Center Wavelength: 4.61 μm , 1000 mW (562 mA), 25 $^{\circ}\text{C}$ | \$5,997.60 Volume Pricing Available | 3 Weeks |
| QF4600T3 | Center Wavelength: 4.62 μm , 1000 mW (640 mA), 25 $^{\circ}\text{C}$ | \$5,997.60 Volume Pricing Available | Today |
| QF4600T3 | Center Wavelength: 4.62 μm , 1000 mW (625 mA), 25 $^{\circ}\text{C}$ | \$5,997.60 Volume Pricing Available | Today |
| QF4600T3 | Center Wavelength: 4.62 μm , 1000 mW (609 mA), 25 $^{\circ}\text{C}$ | \$5,997.60 Volume Pricing Available | Today |
| QF9500T1 | Fabry-Perot Quantum Cascade Laser, 9.5 μm CWL, 300 mW, Ø9 mm, H Pin Code | \$3,860.96 Volume Pricing Available | Lead Time |

Specifications

Spectrum

L-I-V Curves

Far Field

Drawings

Optical Electrical Characteristics ($T_{CASE} = 25^{\circ}C$, $P = 35$ mW)

| Characteristic | Min | Typ. | Max | Unit |
|--|-----|------|-----|------|
| Center Wavelength | 404 | 405 | 406 | nm |
| Optical Output Power (CW) | - | 35 | - | mW |
| Operating Voltage | - | 4.9 | 5.7 | V |
| Beam Divergence (FWHM) - Parallel | - | 10 | - | deg. |
| Beam Divergence (FWHM) - Perpendicular | - | 21 | - | deg. |
| Operating Current | - | 50 | 75 | mA |
| Threshold Current | - | 25 | 50 | mA |
| Polarization Extinction Ratio (TE/TM) | - | 22 | - | dB |
| Slope Efficiency | 1.0 | 1.7 | - | W/A |

Absolute Maximum Ratings^a

| Characteristic | Value | Unit |
|----------------------------|-----------|------|
| Output Power (CW) | 80 | mW |
| Operating Current (CW) | 75 | mA |
| LD Reverse Voltage | 2 | V |
| Operating Case Temperature | 0 to 90 | °C |
| Storage Temperature | -40 to 90 | °C |

a. Absolute Maximum Rating specifications should never be exceeded. Operating beyond these conditions can seriously damage the laser. For more information, please see the [Laser Diode Tutorial](#).

General Specifications

| Characteristic | Value |
|--------------------|------------------------|
| Monitor Photodiode | No |
| Package | Ø3.8 mm |
| Pin Code | G |
| Compatible Socket | <u>S038S</u> |
| Laser Mode | Single Transverse Mode |
| Wavelength Tested | Yes |

Specifications


Spectrum

L-I-V Curves

Far Field

Drawings

L405G2 Sample Output Spectrum



This spectrum of an L405G2 laser diode was taken at a case temperature of 25 °C. The measurement was taken using Thorlabs' [OSA201 Spectrum Analyzer](#). These data are for one particular diode; the spectrum will vary from device to device. To view an Excel file that lists the measured spectral and far field data as well as L-I-V characteristic values of the sample laser diode shown above, please click [here](#).

Specifications


Spectrum

L-I-V Curves

Far Field

Drawings

L405G2 Sample L-I-V Characteristics



This sample data was taken at a case temperature of 25 °C and will vary for each device. To view an Excel file that lists the measured spectral and far field data as well as L-I-V characteristic values of the sample laser diode shown above, please click [here](#).

Specifications


Spectrum

L-I-V Curves

Far Field

Drawings

L405G2 Sample Far Field



This sample data was taken at a case temperature of 25 °C and will vary for each device. To view an Excel file that lists the measured spectral and far field data as well as L-I-V characteristic values of the sample laser diode shown above, please click [here](#).


Specifications

Spectrum

L-I-V Curves

Far Field

Drawings




Pin Diagram



② • Case

Pin Code G

Bottom View



L405G2 - 405 nm, 35 mW, Ø3.8 mm, G Pin Code, Laser Diode