

## M595L3 - June 12, 2020

Item # M595L3 was discontinued on June 12, 2020. For informational purposes, this is a copy of the website content at that time and is valid only for the stated product.

### MOUNTED LEDS

- ▶ UV, Visible, and IR Models Available
- ▶ Optimized Heat Management Results in Stable Output
- ▶ Internal SM1 (1.035"-40) Threading
- ▶ Collimation Adapters Available Separately



**M405LP1**  
405 nm LED,  
1200 mW Output Power



**M505L4**  
505 nm LED,  
400 mW Output Power



Mounted LED used as a  
Light Source for a DIY  
Cerna® Microscope

OVERVIEW

**Mounted LED Features**

- Wavelengths Ranging from 265 nm to 1650 nm (See LED Quick Links Table to the Right)
- White, Broadband, and Dual-Peak LEDs Also Available
- Integrated Memory Stores LED Operating Parameters
- Thermal Properties Optimized for Stable Output Power
- Microscope- and SM-Thread-Compatible Collimation Adapters Available
- 4-Pin Female Mating Connector for Custom Power Supplies can be Purchased Separately

Each Thorlabs uncollimated, mounted LED consists of a single LED mounted to the end of a heat sink with 6 mm deep, SM1 (1.035"-40) internal threads. LEDs with Ø1.20" heat sinks have the same outer diameter as an SM1 Lens Tube, allowing them to fit inside a 30 mm Cage System. A selection of our LEDs are mounted to larger heat sinks, as they generate more heat during operation. These heat sinks are enclosed in Ø57.0 mm vented plastic housings and include four 4-40 tapped holes on the front for integration with 30 mm cage systems.

Every LED features an EEPROM chip which stores information about the LED (e.g., current limit, wavelength, forward voltage). When controlled by a Thorlabs DC2200, DC4100, or DC4104 LED driver, the data can be used to implement smart safety features.

These mounted LEDs possess good thermal stability properties, eliminating the issue of degradation of optical output power due to increased LED temperature. For more details, please see the *Stability* tab.

Please note that mounted LEDs are not intended for use in household illumination applications.

**LED Collimation**

Our adjustable collimation adapters can translate a Ø1" (Ø25 mm) or Ø2" (Ø50 mm) lens by up to 11 mm or 20 mm, respectively. Each adjustable collimation adapter includes an internal SM2 (2.035"-40) thread adapter so that the LEDs can be easily integrated with Thorlabs' SM2-threaded components, such as our Ø2" lens tubes. These adapters are offered in versions with and without an AR-coated aspheric condenser lens.

In addition, microscope collimation adapters are available that incorporate an AR-coated aspheric lens. These adapters mate to the epi-illumination ports on select Leica DMI, Nikon Eclipse Ti, Olympus IX/BX, or Zeiss Axioskop microscopes. Thorlabs also offers mounted LEDs with pre-attached microscope collimation adapters.



Click to Enlarge  
The MWWHL4 LED and COP1-A microscope collimation adapter used as a trans-illumination source for an Olympus microscope.



Click to Enlarge  
View Imperial Product List

Item #	Qty	Description
<b>Imperial Product List</b>		
M385LP1	1	385 nm, 1650 mW (Min) Mounted LED, 1700 mA
CP33	1	SM1-Threaded 30 mm Cage Plate, 0.35" Thick, 2 Retaining Rings, 8-32 Tap
TR6	1	Ø1/2" Optical Post, SS, 8-32 Setscrew, 1/4"-20 Tap, L = 6"
ER3-P4	1	Cage Assembly Rod, 3" Long, Ø6 mm, 4 Pack
<input type="button" value="Add To Cart"/> <input type="button" value="Export"/> <input type="button" value="Forward"/>		

View Metric Product List

Item #	Qty	Description
<b>Metric Product List</b>		
M385LP1	1	385 nm, 1650 mW (Min) Mounted LED, 1700 mA
CP33/M	1	SM1-Threaded 30 mm Cage Plate, 0.35" Thick, 2 Retaining Rings, M4 Tap
TR150/M	1	Ø12.7 mm Optical Post, SS, M4 Setscrew, M6 Tap, L = 150 mm
ER3-P4	1	Cage Assembly Rod, 3" Long, Ø6 mm, 4 Pack
<input type="button" value="Add To Cart"/> <input type="button" value="Export"/> <input type="button" value="Forward"/>		

High-Power LED Inserted into CP33 Cage Plate and Mounted with Ø6 mm Cage Rods



Click to Enlarge  
MWWHL4 LED Mounted in an SM1RC Slip Ring

**LED Quick Links**

**Mounted LEDs**

Deep UV (265 - 340 nm)

UV (365 - 405 nm)

Cold Visible (420 - 565 nm)

Warm Visible (590 - 730 nm)

IR (780 - 1650 nm)

White (400 - 700 nm)

Broadband (470 - 850 nm)


**LED Collimation<sup>a</sup>**

Adjustable Collimation Adapters

Microscope Collimation Adapters

**LED Mating Connector**

**LED Drivers**

- We offer suggestions for how to collimate most of our LEDs. Click on the info icons (  ) below for details.

**Webpage Features**

Clicking this icon opens a window that contains specifications, mechanical drawings, and information about driver and collimator compatibility.

Clicking this icon allows you to download our standard support documentation.

We offer suggestions for collimating most LEDs. Click on the info icon (  ) for each LED below for details.

**Driver Options**

Thorlabs offers four drivers compatible with most or all of these LEDs: LEDD1B, DC2200, DC4100, and DC4104 (the latter two require the DC4100-HUB). See the tables below for driver compatibility info. The LEDD1B is capable of providing LED modulation frequencies up to 5 kHz, while DC4100 and DC4104 can modulate the LED at a rate up to 100 kHz. The DC2200 can provide modulation at up to 250 kHz if driven by an external source. In addition, the DC2200, DC4100, and DC4104 drivers are capable of reading the current limit from the EEPROM chip of the connected LED and automatically adjusting the maximum current setting to protect the LED.

**Multi-LED Source**

A customizable multi-LED source may be constructed using our mounted LEDs and other Thorlabs items. This source may be configured for integration with Thorlabs' versatile SM1 Lens Tube Systems and 30 mm Cage Systems. Please see the *Multi-LED Source* tab for a detailed item list and instructions.

Thorlabs also offers integrated, user-configurable 4-Wavelength High-Power LED Sources.




A mounted LED requires an LED driver to run; a collimation adapter (optional) collimates the diverging beam emitted by the LED. See the tables below to determine the appropriate LED driver. To determine the needed collimation adapter for a given LED, see the info icons (i) below.

RELATIVE POWER

Relative Power


The actual spectral output and total output power of any given LED will vary due to variations in the manufacturing process and operating parameters, such as temperature and current. Both a typical and minimum output power are specified to help you select an LED that suits your needs. Each mounted LED will provide at least the minimum specified output power at the maximum current. In order to provide a point of comparison for the relative powers of LEDs with different nominal wavelengths, the spectra in the plots below have been scaled to the minimum output power for each LED. This data is representative, not absolute. An Excel file with normalized and scaled spectra for all of the mounted LEDs can be downloaded here.

Deep UV LED Spectra Scaled to Min Power




Click to Enlarge

UV LED Spectra Scaled to Min Power




Click to Enlarge

Visible LED Spectra Scaled to Min Power




Click to Enlarge

IR LED Spectra Scaled to Min Power




Click for Details

White LED Spectra Scaled to Min Power




Click to Enlarge

Purple LED Spectrum Scaled to Min Power



Click to Enlarge

Broadband LED Spectrum Scaled to Min Power




Click to Enlarge

STABILITY


### LED Lifetime and Long-Term Power Stability

One characteristic of LEDs is that they naturally exhibit power degradation with time. Often this power degradation is slow, but there are also instances where large, rapid drops in power, or even complete LED failure, occur. LED lifetimes are defined as the time it takes a specified percentage of a type of LED to fall below some power level. The parameters for the lifetime measurement can be written using the notation  $B_{XX}/L_{YY}$ , where XX is the percentage of that type of LED that will provide less than YY percent of the specified output power after the lifetime has elapsed. Thorlabs defines the lifetime of our LEDs as  $B_{50}/L_{50}$ , meaning that 50% of the LEDs with a given item # will fall below 50% of the initial optical power at the end of the specified lifetime. For example, if a batch of 100 LEDs is rated for 150 mW of output power, 50 of these LEDs can be expected to produce an output power of  $\leq 75$  mW after the specified LED lifetime has elapsed.



Click to Enlarge

The sample plot to the right shows example data from long-term stability testing over a 45 day period for a 340 nm mounted LED, which had a lifetime of  $>3,000$  hours ( $\sim 125$  days). The small power drop experienced by the LED after it is turned on is typical behavior during the first few minutes of operation. It corresponds to the period of time required for the LED to warm up to the point where it is thermally stable. Please note that this graph represents the performance of a single LED; the performance of individual LEDs will vary within the stated specifications.



Click to Enlarge


Our 340 nm mounted LED has a typical lifetime of  $>3,000$  hours. In this case, the unit under test continued to provide more than 90% of its initial power after 45 days.

### Optimized Thermal Management

The thermal dissipation performance of these mounted LEDs has been optimized for stable power output. The heat sink is directly mounted to the LED mount so as to provide optimal thermal contact. By doing so, the degradation of optical output power that can be attributed to increased LED junction temperature is minimized (see the graph to the left).

COLLIMATION

### Obtaining a Well-Collimated Beam

After installing the chosen collimation package on a mounted LED, the distance between the lens and the LED may need to be adjusted to ensure that the LED is properly collimated. A well-collimated beam has minimal divergence and will not converge at any point in the beam path (see images below for comparison). Be advised that, due to the high emitter surface area of the LED, the output beam cannot be perfectly collimated. Divergence data for select LEDs is provided in the below table as a reference; see the info icons (  ) below for the recommended collimating optic for each LED.

1. Power on the LED and check to see if it is properly collimated. It is easiest to check that the beam is collimated by noting the changes in the beam diameter over a range of about 1" to 2 feet away; change the distance of the lens from the LED and check again. Do this until the least divergent, non-converging, homogenous beam is obtained. The beam should be somewhat circular, may have a slightly polygonal shape, and should not be a clear image of the LED itself.
2. If you see an image of the LED, this means that the lens is not close enough to the LED. Move the lens closer to the LED until the image blurs and becomes homogenous – this is the point of collimation. Note: If the lens needs to be closer to the LED when using the DIY collimation assembly, use one retaining ring to secure the lens against the internal lip of the SM1V05.



Click to Enlarge  
**Image of the LED**



Click to Enlarge  
**Uncollimated Beam**



Click to Enlarge  
**Collimated Beam**

3. Once the proper collimation position of the lens has been found, lock the position of the lens in place.

The table below provides examples of how the half viewing angle changes for select LEDs with the addition of a Ø1" aspheric condenser lens.

Item #	Color	Nominal Wavelength <sup>a</sup>	Optimum Lens to Emitter Distance <sup>b</sup>	Half Viewing Angle <sup>c</sup>		
				+1 mm Out of Focus <sup>d</sup>	at Optimum Focusing Distance	-1 mm Out of Focus <sup>d</sup>
M365L2	UV	365 nm	12.7 mm	2.79°	1.32°	3.11°
M385L2	UV	385 nm	12.8 mm	2.68°	1.33°	3.06°
M405L2	UV	405 nm	12.9 mm	2.94°	1.63°	3.06°
M505L3	Cyan	505 nm	13.2 mm	3.52°	2.72°	3.46°
M625L3	Red	625 nm	14.4 mm	3.46°	2.27°	3.13°
M850L3	IR	850 nm	13.8 mm	3.29°	3.10°	3.93°
M940L3	IR	940 nm	13.9 mm	3.42°	2.46°	3.70°

- The specifications listed in the table above are nominal values specified by the LED manufacturer.
- Optimum distance between the respective mounted LED and the ACL2520U lens used to collimate the beam.
- Power loss to 1/e<sup>2</sup> (13.5%).
- ±1 mm out of focus from Optimum Distance between the respective mounted LED and the ACL2520U lens used to collimate the beam.
- Correlated Color Temperature.

*The divergence data was calculated using Zemax.*

PIN DIAGRAM

### Pin Connection - Male

The diagram to the right shows the male connector of the mounted LED assembly. It is a standard M8 x 1 sensor circular connector. Pins 1 and 2 are the connection to the LED. Pin 3 and 4 are used for the internal EEPROM in these LEDs. If using an LED driver that was not purchased from Thorlabs, be careful that the appropriate connections are made to Pin 1 and Pin 2 and that you do not attempt to drive the LED through the EEPROM pins.



Pin	Specification	Color
1	LED Anode	Brown
2	LED Cathode	White
3	EEPROM GND	Black
4	EEPROM IO	Blue

MULTI-LED SOURCE

### Creating a Custom Multi-LED Source for Microscope Illumination

Thorlabs offers the items necessary to create your own custom multi-LED light source using two or three of the mounted LEDs offered below. As configured in the following example, the light source is intended to be used with the illumination port of a microscope. However, it may be integrated with other applications using Thorlabs' versatile SM1 Lens Tube and 30 mm Cage Systems. Thorlabs also offers integrated, user-configurable 4-Wavelength LED Sources.



Click to Enlarge  
Multi-LED Source Coupled to Microscope Illumination Port

#### Design & Construction

First, light will be collimated by lenses mounted in lens tubes. Dichroic mirrors mounted in kinematic cage cubes then combine the output from the multiple LEDs. The mounted LEDs may be driven by LEDD1B Compact T-Cube LED Drivers (power supplies are sold separately). The LEDD1B LED Drivers allow each LED's output to be independently modulated and can provide up to 1200 mA of current. Please take care not to drive the LED sources above their max current ratings.

When designing your custom source, select mounted LEDs from below along with dichroic mirror(s) that have cutoff wavelength(s) between the LED wavelengths. The appropriate dichroic mirror(s) will reflect light from side-mounted LEDs and transmit light along the optical axis. Please note that most of these dichroic mirrors are "longpass" filters, meaning they transmit the longer wavelengths and reflect the shorter wavelengths. To superimpose light from three or more LEDs, add each in series (as shown below), starting from the back with longer wavelength LEDs when using longpass filters. Shortpass filters may also be used if the longer wavelength is reflected and the shorter wavelength is transmitted. Sample combinations of compatible dichroic mirrors and LEDs are offered in the three tables below.

It is also necessary to select an aspheric condenser lens for each source with AR coatings appropriate for the source. Before assembling the light source, collimate the light from each mounted LED as detailed in the *Collimation* tab. For mounting the aspheric lenses in the SM1V05 Lens Tubes using the included SM1RR retaining rings, we recommend the SPW801 Adjustable Spanner Wrench. A properly collimated LED source should have a resultant beam that is approximately homogenous and not highly divergent at a distance of approximately 2 feet (60 cm). An example of a well-collimated beam is shown on the *Collimation* tab.

After each LED source is collimated, thread the SM1V05 Lens Tubes at the end of each collimated LED assembly into their respective C4W Cage Cube ports using SM1T2 Lens Tube Couplers. Install each dichroic filter in an FFM1 Dichroic Filter Holder, and mount each filter holder onto a B4C Kinematic Cage Cube Platform. Each platform is then installed in the C4W Cage Cubes by partially threading the included screws into the bottom of the cube, and then inserting and rotating the B4C platform into place. Align the platform to the desired position and then firmly tighten the screws. To connect multiple cage cubes and the microscope adapter, use the remaining SM1T2 lens tube couplers along with an SM1L05 0.5" Lens Tube between adjacent cage cubes. Finally, adjust the rotation, tip, and tilt of each B4C platform to align the reflected and transmitted beams so they overlap as closely as possible.

If desired, a multi-LED source may be constructed that employs more than three LEDs. The limiting factors for the number of LEDs that can be practically used are the collimation of the light and the dichroic mirror efficiency over the specified range. Heavier multi-LED sources may be supported with our Ø1" or Ø1.5" Posts.



Click to Enlarge  
Three-LED Source Using Components Mounted LEDs and Dichroic Mirrors  
Detailed in Example Configuration 1

Parts List				
#	Product Description	Item #	2 LEDs	3 LEDs
			Item Qty.	



Click to Enlarge Beam Profile of Source with 3 Mounted LEDs



Click to Enlarge Two-LED source. This is the same as Example 1, but with the blue LED removed.


Parts List					
1	Microscope Illumination Port Adapter:	Olympus IX or BX	SM1A14	1	1
		Leica DMI	SM1A21		
		Zeiss Axioskop	SM1A23 <sup>a</sup>		
		Nikon Eclipse Ti	SM1A26		
2		Mounted LED <sup>b</sup>	-	2	3
-		T-Cube LED Driver, 1200 mA Max Drive Current	LEDD1B <sup>c</sup>	2	3
-		15 V Power Supply Unit for T-Cube	KPS101 <sup>c</sup>	2	3
3		4-Way Mounting 30 mm Cage Cube	C4W	1	2
4		Kinematic Cage Cube Platform for C4W/C6W	B4C	1	2
5		30 mm Cage-Compatible Dichroic Filter Mount	FFM1	1	2
6		Dichroic Filter(s) <sup>d</sup>	-	1	2
7		Externally SM1-Threaded End Cap	SM1CP2	1	2
8		SM1 (1.035"-40) Coupler, External Threads, 0.5" Long	SM1T2	3	5
9		Ø1" SM1 Lens Tube, 1/2" Long External Threads	SM1V05	2	3
-	Aspheric Condenser Lens	AR-Coated 350 - 700 nm	ACL2520U-A <sup>c,e</sup>	2	3
		AR-Coated 650 - 1050 nm	ACL2520U-B <sup>c,e</sup>		
10		SM1 Lens Tube, 0.3" Thread Depth	SM1L03	2	4
-		Blank Cover Plate with Rubber O-Ring for C4W/C6W	B1C <sup>c</sup>	1	2







- The SM1A23 Zeiss Axioskop Microscope Adapter is shown.
- Mounted LEDs are available below.
- Item not pictured.
- Please see the following tables for suggested compatible LED and dichroic filter combinations, or create your own by taking into account the transmission and reflection wavelength ranges of our Dichroic Filters.
- Lenses are mounted in the SM1V05 Lens Tube in front of each LED. For each lens, select an AR coating corresponding to the emission wavelength of the LED source.

Example Configuration 1		Example Configuration 2		Example Configuration 3	
Mounted LEDs		Mounted LEDs		Mounted LEDs	
#	Item #	#	Item #	#	Item #
2a	M625L4	2a	M625L4	2a	M1050L2
2b	M530L4	2b	M455L4	2b	MCWHL6
2c	M455L4	2c	M1050L2	Dichroic Filter(s)	
Dichroic Filter(s)		Dichroic Filter(s)		#	Item #
#	Item #	#	Item #	6a	DMLP900R
6a	DMLP605R	6a	DMLP505R		
6b	DMLP505R	6b	DMSP805R		



## RAY DATA

Ray data for Zemax is available for some of the bare LEDs incorporated into these high-powered light sources. This data is provided in a zipped folder that can be downloaded by clicking on the red document icons (  ) next to the part numbers in the pricing tables below. Every zipped folder contains an information file and one or more ray files for use with Zemax:

Item #	Information File	Available Ray Files	File Size	Click to Download
<b>M365L2</b>	M365_Info.pdf	100,000 Rays and 1 Million Rays	27.4 MB	
<b>M385L2</b>	M385_Info.pdf	1 Million Rays and 5 Million Rays	148 MB	
<b>M450LP1<sup>a</sup></b>	LD_CQAR_20150731_info.pdf	100,000 Rays, 500,000 Rays, and 5 Million Rays	123 MB	
<b>M505L3<sup>a</sup></b>	LV_CK7P_191212_info.pdf	100,000 Rays, 500,000 Rays, and 5 Million Rays	123 MB	
<b>M850L3<sup>a</sup></b>	SFH4715S_100413_info.pdf	100,000 Rays, 500,000 Rays, and 5 Million Rays	140 MB	
<b>M940L3<sup>a</sup></b>	SFH_4725S_110413_info.pdf	100,000 Rays, 500,000 Rays, and 5 Million Rays	140 MB	

- A radiometric color spectrum, bare LED CAD file, and sample Zemax file are also available for these LEDs.

- **Information File:** This document contains a summary of the types of data files included in the zipped folder and some basic information about their use. It includes a table listing each document type and the corresponding filenames.
- **Ray Files:** These are binary files containing ray data for use with Zemax.

For the LEDs marked with an superscript "a" in the table to the right, the following additional pieces of information are also included in the zipped folder:

- **Radiometric Color Spectrum:** This .spc file is also intended for use with Zemax.
- **CAD Files:** A file indicating the geometry of the bare LED. For the dimensions of the high-power mounted LEDs that include the package, please see the support drawings provided by Thorlabs.
- **Sample Zemax File:** A sample file containing the recommended settings and placement of the ray files and bare LED CAD model when used with Zemax.

The table to the right summarizes the ray files available for each LED and any other supporting documentation provided.

## Using Mounted LEDs in Cerna® Microscope Systems

Mounted LEDs, which can have either narrowband or broadband spectra, are useful for a range of applications within Thorlabs' Cerna microscopy platform:

- Fluorescence Microscopy
- Brightfield Microscopy
- Near Infrared/Infrared (NIR/IR) Microscopy

If you are interested in using a mounted LED with a Cerna modular microscopy system, the mounted LED can be attached by way of the single-cube epi-illuminator module (Item # WFA2001), which contains AR-coated optics optimized for the 350 - 700 nm wavelength range. The mounted LED and epi-illuminator module are connected together by an externally threaded coupler (Item # SM1T10, provided with the WFA2001), which includes two knurled locking rings (Item # SM1NT, also provided with the WFA2001) that are tightened by hand. The mounted LED is then powered by a driver, sold separately. Please see the *LED Drivers* tab to identify the appropriate driver for your mounted LED. If you wish to connect multiple mounted LEDs to the epi-illuminator module, contact Technical Support.


### Components for Cerna® Compatibility

#### Epi-Illumination

WFA2001 Epi-Illuminator Module

#### Trans-Illumination

Illumination Kits



Click to

Enlarge

An exploded view of the mounted LED and its connection with the WFA2001 epi-illuminator module.



Click to

Enlarge

Attaching the mounted LED is possible before or after connecting the epi-illuminator module to the microscope.



Click to





Enlarge

The mounted LED and epi-illuminator module attached to the Cerna microscope.

Please see the *Overview* tab to choose the appropriate color spectrum of mounted LED for your imaging needs. Again, note that the epi-illuminator module is optimized for 350 - 700 nm wavelength illumination sources.

Certain mounted LEDs are also compatible with our illumination kits for trans-illumination. Please contact Technical Support if you wish to use an LED not currently offered as a component of these kits, as the collimating optics are optimized for certain beam characteristics.











## LED DRIVERS

Compatible Drivers	LEDD1B	DC2200 <sup>a</sup>	DC4100 <sup>a,b,c</sup>	DC4104 <sup>a,b,c</sup>
Click Photos to Enlarge				
LED Driver Current Output (Max)	1.2 A	LED1 Terminal: 10.0 A LED2 Terminal: 2.0 A <sup>d</sup>	1.0 A per Channel	1.0 A per Channel
LED Driver Forward Voltage (Max)	12 V	50 V	5 V	5 V
Modulation Frequency Using External Input (Max)	5 kHz	250 kHz <sup>e,f</sup>	100 kHz <sup>f</sup> (Simultaneous Across all Channels)	100 kHz <sup>f</sup> (Independently Controlled Channels)
External Control Interface(s)	Analog (BNC)	USB 2.0 and Analog (BNC)	USB 2.0 and Analog (BNC)	USB 2.0 and Analog (8-Pin)
Main Driver Features	Very Compact Footprint 60 mm x 73 mm x 104 mm (W x H x D)	Touchscreen Interface with Internal and External Options for Pulsed and Modulated LED Operation	4 Channels <sup>b</sup>	4 Channels <sup>b</sup>
EEPROM Compatible: Reads Out LED Data for LED Settings	-	✓	✓	✓
LCD Display	-	✓	✓	✓

- Automatically limits to LED's max current via EEPROM readout.
- The DC4100 and DC4104 can power and control up to four LEDs simultaneously when used with the DC4100-HUB. The LEDs on this page all require the DC4100-HUB when used with the DC4100 or DC4104.
- These LED drivers have a maximum forward voltage rating of 5 V and can provide a maximum current of 1000 mA. As a result, they cannot be used to drive LEDs which have forward voltage ratings greater than 5 V. LEDs with maximum current ratings higher than 1.0 A can be driven using this driver, but will not reach full power.
- The mounted LEDs sold below are compatible with the LED2 Terminal.
- Small Signal Bandwidth: Modulation not exceeding 20% of full scale current. The driver accepts other waveforms, but the maximum frequency will be reduced.
- Several of these LEDs produce light by stimulating emission from phosphor, which limits their modulation frequencies. The M565L3, M595L3, and all purple or white LEDs may not turn off completely when modulated above 10 kHz at duty cycles below 50%. The MBB1L3 LED may not turn off completely when modulated at frequencies above 1 kHz with a duty cycle of 50%. When the MBB1L3 is modulated at frequencies above 1 kHz, the duty cycle may be reduced; for example, 10 kHz modulation is attainable with a duty cycle of 5%.

LED SELECTION GUIDE

Light Emitting Diode (LED) Selection Guide

(Click Representative Photo to Enlarge; Not to Scale)										
Wavelength	Unmounted LEDs	Pigtailed LEDs	LEDs in SMT Packages	PCB-Mounted LEDs	Heatsink-Mounted LEDs	Collimated LEDs for Microscopy (Item # Prefix <sup>a</sup> )	Fiber-Coupled LEDs <sup>b</sup>	High-Power LEDs for Microscopy	Multi-Wavelength LED Source Options <sup>c</sup>	LED Arrays
<b>Single Color LEDs</b>										
250 nm	LED250J (1 mW Min)	-	-	-	-	-	-	-	-	-
255 nm	LED255J (1 mW Min)	-	-	-	-	-	-	-	-	-
260 nm	LED260W (0.3 mW) LED260J (1 mW Min)	-	-	-	-	-	-	-	-	-
265 nm	-	-	-	M265D2 (10 mW Min)	M265L3 (10 mW Min)	-	-	-	-	-
				M265D3 (24 mW Min)	M265L4 (24 mW Min)					
275 nm	LED275W (0.8 mW) LED275J (1 mW Min)	-	-	M275D2 (45 mW Min)	M275L4 (45 mW Min)	-	-	-	-	-
280 nm	LED280J (1 mW Min)	-	-	-	-	-	-	-	-	-
285 nm	LED285W (0.8 mW)	-	-	M285D3 (50 mW Min)	M285L5 (50 mW Min)	-	M285F4 (420 μW)	-	-	-
290 nm	LED290W (0.8 mW)	-	-	-	-	-	-	-	-	-
300 nm	LED300W (0.5 mW)	-	-	M300D3 (26 mW Min)	M300L4 (26 mW Min)	-	M300F2 (320 μW)	-	-	-
315 nm	LED315W (0.6 mW)	-	-	-	-	-	-	-	-	-
340 nm	LED341W (0.33 mW)	-	-	M340D3 (53 mW Min)	M340L4 (53 mW Min)	-	M340F3 (1.06 mW)	-	-	-
365 nm	-	-	-	M365D1 (190 mW Min)	M365L2 (190 mW Min)	M365L2 (60 mW) <sup>d</sup>	M365F1 (4.1 mW)	SOLIS-365C (3.0 W) <sup>e</sup>	Chrolis (1130 mW)	LIU365A (31 mW)
				M365D2 (1150 mW Min)	M365LP1 (11-50 mW Min)	M365LP1 (350 mW) <sup>d</sup>	M365FP1 (15.5 mW)		4- Wavelength Source (85 mW)	
375 nm	LED375L (1 mW)	-	-	M375D4 (1270 mW Min)	M375L4 (1270 mW Min)	-	M375F2 (4.23 mW)	-	-	-
	LED370E (2.5 mW)									
385 nm	LED385L (5 mW)	-	-	M385D1 (270 mW Min)	M385L2 (270 mW Min)	M385L2 (90 mW) <sup>d</sup>	M385F1 (10.7 mW)	SOLIS-385C (5.8 W) <sup>e</sup>	Chrolis (1250 mW)	-
				M385D2 (1650 mW Min)	M385LP1 (1650 mW Min)	M385LP1 (520 mW) <sup>d</sup>	M385FP1 (23.2 mW)		4- Wavelength Source (95 mW)	
395 nm	LED395L (6 mW)	-	-	M395D3 (400 mW Min)	M395L4 (400 mW Min)	-	M395F3 (6.8 mW)	-	-	-

Light Emitting Diode (LED) Selection Guide

Wavelength	Unmounted LEDs	Pigtailed LEDs	LEDs in SMT Packages	PCB-Mounted LEDs	Heatsink-Mounted LEDs	Collimated LEDs for Microscopy (Item # Prefix <sup>a</sup> )	Fiber-Coupled LEDs <sup>b</sup>	High-Power LEDs for Microscopy	Multi-Wavelength LED Source Options <sup>c</sup>	LED Arrays
<b>Single Color LEDs</b>										
405 nm	LED405L (6 mW)	-	-	M405D2 (1500 mW Min)	M405L4 (1000 mW Min)	M405L3 (440 mW) <sup>d</sup> M405L4 (510 mW) <sup>f</sup>	M405F1 (3.7 mW)	SOLIS-405C (3.9 W) <sup>e</sup>	Chrolis (900 mW) 4-Wavelength Source (290 mW)	-
	LED405E (10 mW)				M405LP1 (1200 mW Min)	M405LP1 (450 mW) <sup>d</sup>	M405FP1 (24.3 mW)			
415 nm	-	-	-	M415D2 (1640 mW Min)	M415L4 (1310 mW Min)	-	M415F3 (21.3 mW)	SOLIS-415C (5.8 W) <sup>e</sup>	-	-
					M415LP1 (1640 mW Min)					
420 nm	-	-	-	-	-	-	-	-	Chrolis (710 mW) 4-Wavelength Source (95 mW)	-
430 nm	LED430L (8 mW)	-	-	M430D2 (490 mW Min)	M430L4 (490 mW Min)	-	-	-	-	-
445 nm	-	-	-	-	-	-	-	SOLIS-445C (5.4 W) <sup>e</sup>	-	-
450 nm	LED450L (7 mW)	-	LEDS450 (250 mW)	M450D3 (1850 mW Min)	M450LP1 (1850 mW Min)	-	-	-	-	-
455 nm	-	-	-	M455D3 (1150 mW Min)	M455L4 (1150 mW Min)	M455L3 (360 mW) <sup>d</sup>	M455F3 (24.5 mW)	-	4-Wavelength Source (310 mW)	-
						M455L4 (490 mW) <sup>d</sup>				
465 nm	LED465E (20 mW)	-	-	-	-	-	-	-	-	-
470 nm	LED470L (170 mW)	EP470S04 (18 mW Min)	-	M470D2 (650 mW Min)	M470L4 (760 mW Min)	M470L4 (330 mW) <sup>d</sup>	M470F3 (17.2 mW)	SOLIS-470C (3.0 W) <sup>e</sup>	4-Wavelength Source (250 mW)	LIU470A (253 mW)
		EP470S10 (100 mW Min)		M470D3 (760 mW Min)						
475 nm	-	-	-	-	-	-	-	-	Chrolis (630 mW)	-
490 nm	LED490L (3 mW)	-	-	M490D3 (205 mW Min)	M490L4 (205 mW Min)	-	M490F3 (2.3 mW)	-	Chrolis (120 mW)	-
									4-Wavelength Source (50 mW)	
505 nm	LED505L (4 mW)	-	-	M505D2 (400 mW Min)	M505L3 (400 mW Min)	M505L3 (150 mW) <sup>d</sup>	M505F3 (11.7 mW)	SOLIS-505C (1.0 W) <sup>e</sup>	4-Wavelength Source (170 mW)	-
				M505D3 (400 mW Min)	M505L4 (400 mW Min)	M505L4 (170 mW) <sup>d</sup>				
525 nm	LED525E (2.6 mW Max)	-	-	-	-	-	-	SOLIS-525C (2.4 W) <sup>e</sup>	Chrolis (180 mW)	LIU525A (111 mW)
	LED525L (4 mW)									
	LED528EHP (7 mW)									

**Light Emitting Diode (LED) Selection Guide**

530 nm	-	-	-	M530D2 (350 mW Min)	M530L4 (370 mW Min)	M530L3 (130 mW) <sup>d</sup>	M530F2 (6.8 mW)	-	4- Wavelength Source (100 mW)	-
				M530D3 (370 mW Min)		M530L4 (160 mW) <sup>d</sup>				
554 nm	-	-	-	MINTD3 (650 mW Min)	MINTL5 (650 mW Min)	-	MINTF4 (21 mW Min)	-	-	-
555 nm	LED555L (1 mW)	-	-	-	-	-	-	-	-	-
565 nm	-	-	-	M565D2 (880 mW Min)	M565L3 (880 mW Min)	-	M565F3 (13.5 mW)	SOLIS-4C (3.2 W) <sup>e</sup>	Chrolis (350 mW)	-
									4- Wavelength Source (106 mW)	
570 nm	LED570L (0.3 mW)	-	-	-	-	-	-	-	-	-
590 nm	LED590L (2 mW)	EP590S04 (3.5 mW Min)	-	M590D2 (160 mW Min)	M590L3 (160 mW Min)	M590L3 (60 mW) <sup>d</sup>	M590F3 (4.6 mW)	SOLIS-590C (350 mW) <sup>e</sup>	Chrolis (140 mW)	LIU590A (109 mW)
	LED591E (2 mW)	EP590S10 (18 mW Min)		M590D3 (230 mW Min)	M590L4 (230 mW Min)	M590L4 (100 mW) <sup>d</sup>			4- Wavelength Source (65 mW)	
595 nm	-	-	-	M595D2 (445 mW Min)	M595L3 (445 mW Min)	-	M595F2 (8.7 mW)	SOLIS-595C (700 mW) <sup>e</sup>	-	-
<b>Wavelength</b>	<b>Unmounted LEDs</b>	<b>Pigtailed LEDs</b>	<b>LEDs in SMT Packages</b>	<b>PCB-Mounted LEDs</b>	<b>Heatsink-Mounted LEDs</b>	<b>Collimated LEDs for Microscopy (Item # Prefix<sup>a</sup>)</b>	<b>Fiber-Coupled LEDs<sup>b</sup></b>	<b>High-Power LEDs for Microscopy</b>	<b>Multi-Wavelength LED Source Options<sup>c</sup></b>	<b>LED Arrays</b>
<b>Single Color LEDs</b>										
600 nm	LED600L (3 mW)	-	-	-	-	-	-	-	-	-
610 nm	LED610L (8 mW)	-	-	-	-	-	-	-	-	-
617 nm	-	-	-	M617D2 (600 mW Min)	M617L3 (600 mW Min)	M617L3 (230 mW) <sup>d</sup>	M617F2 (10.2 mW)	SOLIS-617C (1.5 mW) <sup>e</sup>	4- Wavelength Source (210 mW)	-
				M617D3 (660 mW Min)	M617L4 (660 mW Min)	M617L4 (280 mW) <sup>d</sup>				
623 nm	-	-	-	-	-	-	-	SOLIS-623C (3.8 W) <sup>e</sup>	-	-
625 nm	LED625L (12 mW)	-	-	M625D3 (700 mW Min)	M625L4 (700 mW Min)	M625L3 (270 mW) <sup>d</sup>	M625F1 (13.2 mW)	-	Chrolis (490 mW)	-
						M625L4 (490 mW) <sup>d</sup>			4- Wavelength Source (240 mW)	
630 nm	LED630L (16 mW)	-	-	-	-	-	-	-	-	LIU630A (208 mW)
635 nm	LED631E (4 mW)	-	-	-	-	-	-	-	-	-
	LED635L (170 mW)									
639 nm	LED630E (7.2 mW)	-	-	-	-	-	-	-	-	-
645 nm	LED645L (16 mW)	-	-	-	-	-	-	-	-	-

Light Emitting Diode (LED) Selection Guide

660 nm	LED660L (13 mW)	-	-	M660D2 (940 mW Min)	M660L4 (940 mW Min)	M660L4 (400 mW) <sup>d</sup>	M660F1 (14.5 mW)	SOLIS-660C (2.0 W) <sup>e</sup>	4- Wavelength Source (210 mW)	-
670 nm	LED670L (12 mW)	-	-	-	-	-	-	-	-	-
680 nm	LED680L (8 mW)	-	-	M680D2 (180 mW Min)	M680L4 (180 mW Min)	-	M680F3 (2.7 mW)	-	-	-
700 nm	-	EP700S04 (5 mW Min)	-	M700D2 (80 mW Min)	M700L4 (80 mW Min)	-	M700F3 (1.7 mW)	-	-	-
		EP700S10 (30 mW Min)								
730 nm	-	-	-	M730D3 (540 mW Min)	M730L5 (540 mW Min)	M730L4 (165 mW) <sup>d</sup>	-	-	-	-
740 nm	-	-	-	-	-	-	M740F2 (6.0 mW)	SOLIS-740C (2.0 W) <sup>e</sup>	-	-
750 nm	LED750L (18 mW)	-	-	-	-	-	-	-	-	-
760 nm	LED760L (24 mW)	-	-	-	-	-	-	-	-	-
770 nm	LED770L (22 mW)	-	-	-	-	-	-	-	-	-
780 nm	LED780E (18 mW)	-	-	M780D2 (200 mW Min)	M780L3 (200 mW Min)	M780L3 (130 mW) <sup>d</sup>	M780F2 (7.5 mW)	-	Chrolis (40 mW)	LIU780A (315 mW)
	LED780L (22 mW)			M780D3 (800 mW Min)	M780LP1 (800 mW Min)					
800 nm	LED800L (20 mW)	-	-	-	-	-	-	-	-	-
810 nm	LED810L (22 mW)	EP810S04 (16 mW Min)	-	M810D2 (325 mW Min)	M810L3 (325 mW Min)	M810L3 (210 mW) <sup>d</sup>	M810F2 (6.5 mW)	-	-	-
		EP810S10 (90 mW Min)		M810D3 (363 mW Min)	M810L4 (363 mW Min)					
830 nm	LED830L (22 mW)	-	-	-	-	-	-	-	-	-
840 nm	LED840L (22 mW)	-	-	-	-	-	-	-	-	-
850 nm	LED851L (13 mW)	-	-	M850D2 (900 mW Min)	M850L3 (900 mW Min)	M850L3 (330 mW) <sup>d</sup>	M850F2 (13.4 mW)	SOLIS-850C (2.7 W) <sup>e</sup>	-	LIU850A (322 mW)
				M850D3 (1400 mW)	M850LP1 (1400 mW Min)					
870 nm	LED870E (22 mW)	-	-	-	-	-	-	-	-	-
	LED870L (24 mW)									
880 nm	-	-	-	M880D2 (300 mW Min)	M880L3 (300 mW Min)	-	M880F2 (3.4 mW)	-	-	-
890 nm	LED890L (12 mW)	-	-	-	-	-	-	-	-	-
910 nm	LED910L (10 mW)	-	-	-	-	-	-	-	-	-
	LED910E (12 mW)									
930 nm	LED930L (15 mW)	-	-	-	-	-	-	-	-	-
940 nm	LED940E (18 mW)	-	-	M940D2 (800 mW Min)	M940L3 (800 mW Min)	M940L3 (320 mW) <sup>d</sup>	M940F3 (14.2 mW)	SOLIS-940C (2.5 W) <sup>e</sup>	-	-
970 nm	LED970L (5 mW)	-	-	M970D3 (600 mW Min)	M970L4 (600 mW Min)	-	M970F3 (8.1 mW)	-	-	-

Light Emitting Diode (LED) Selection Guide

Wavelength	Unmounted LEDs	Pigtailed LEDs	LEDs in SMT Packages	PCB-Mounted LEDs	Heatsink-Mounted LEDs	Collimated LEDs for Microscopy (Item # Prefix <sup>a</sup> )	Fiber-Coupled LEDs <sup>b</sup>	High-Power LEDs for Microscopy	Multi-Wavelength LED Source Options <sup>c</sup>	LED Arrays
<b>Single Color LEDs</b>										
1050 nm	LED1050E (2.5 mW)	-	-	M1050D1 (50 mW Min)	M1050L2 (50 mW Min)	-	-	-	-	-
	LED1050L (4 mW)	-	-	M1050D3 (160 mW Min)	M1050L4 (160 mW Min)	-	M1050F3 (3 mW)	-	-	-
1070 nm	LED1070L (4 mW)	-	-	-	-	-	-	-	-	-
	LED1070E (7.5 mW)	-	-	-	-	-	-	-	-	-
1085 nm	LED1085L (5 mW)	-	-	-	-	-	-	-	-	-
1200 nm	LED1200E (2.5 mW)	-	-	M1200D2 (30 mW Min)	M1200L3 (30 mW Min)	-	-	-	-	-
	LED1200L (5 mW)	-	-	-	-	-	-	-	-	-
1300 nm	LED1300E (2 mW)	-	-	M1300D2 (25 mW Min)	M1300L3 (25 mW Min)	-	-	-	-	-
	LED1300L (3.5 mW)	-	-	-	-	-	-	-	-	-
1450 nm	LED1450E (2 mW)	-	-	M1450D2 (31 mW Min)	M1450L3 (31 mW Min)	-	-	-	-	-
	LED1450L (5 mW)	-	-	-	-	-	-	-	-	-
1550 nm	LED1550E (2 mW)	-	-	M1550D2 (31 mW Min)	M1550L3 (31 mW Min)	-	-	-	-	-
	LED1550L (4 mW)	-	-	-	-	-	-	-	-	-
1600 nm	LED1600L (2 mW)	-	-	-	-	-	-	-	-	-
1650 nm	LED1600P (1.2 mW)	-	-	M1650D2 (13 mW)	M1650L4 (13 mW)	-	-	-	-	-
1750 nm	LED1700P (1.2 mW Quasi-CW, 30 mW Pulsed)	-	-	-	-	-	-	-	-	-
1850 nm	LED1800P (0.9 mW Quasi-CW, 20 mW Pulsed)	-	-	-	-	-	-	-	-	-
1950 nm	LED1900P (1.0 mW Quasi-CW, 25 mW Pulsed)	-	-	-	-	-	-	-	-	-
2050 nm	LED2050P (1.1 mW Quasi-CW, 28 mW Pulsed)	-	-	-	-	-	-	-	-	-



Light Emitting Diode (LED) Selection Guide

2350 nm	LED2350P (0.8 mW Quasi-CW, 16 mW Pulsed)	-	-	-	-	-	-	-	-	-
4200 nm	LED4300P (0.03 mW Quasi-CW, 0.2 mW Pulsed)	-	-	-	-	-	-	-	-	-
4500 nm	LED4600P (0.006 mW Quasi-CW, 0.12 mW Pulsed)	-	-	-	-	-	-	-	-	-
Wavelength	Unmounted LEDs	Pigtailed LEDs	LEDs in SMT Packages	PCB-Mounted LEDs	Heatsink-Mounted LEDs	Collimated LEDs for Microscopy (Item # Prefix <sup>a</sup> )	Fiber-Coupled LEDs <sup>b</sup>	High-Power LEDs for Microscopy	Multi-Wavelength LED Source Options <sup>c</sup>	LED Arrays
<b>Multi-Color, Broadband, and White LEDs</b>										
455 nm (12.5% <sup>g</sup> ) and 640 nm	-	-	-	MPRP1D2 (275 mW Min)	MPRP1L4 (275 mW Min)	-	-	-	-	-
572 nm and 625 nm	LEDGR (0.09 mW and 0.19 mW)	-	-	-	-	-	-	-	-	-
588 nm and 617 nm	LEDRY (0.09 mW and 0.19 mW)	-	-	-	-	-	-	-	-	-
467.5 nm, 525 nm, and 627.5 nm	LEDRGBE (5.8 mW, 6.2 mW, and 3.1 mW)	-	-	-	-	-	-	-	-	-
430 - 660 nm (White)	LEDWE-15 (13 mW)	-	-	-	-	-	-	-	-	-
	LEDW7E (15.0 mW)	-	-	-	-	-	-	-	-	-
	LEDW25E (15.0 mW)	-	-	-	-	-	-	-	-	-
470 - 850 nm (Broadband)	-	-	-	MBB1D1 (70 mW Min)	MBB1L3 (70 mW Min)	-	MBB1F1 (1.2 mW)	-	-	-
6500 K (Cold White)	-	-	-	MCWHD2 (800 mW Min)	MCWHL6 (990 mW Min)	MCWHL5 (440 mW) <sup>f</sup>	-	SOLIS-1C (3.3 W) <sup>e</sup>	-	-
	-	-	-	MCWHD4 (990 mW Min)	MCWHL1 (2350 mW Min)	MCWHL6 (354 mW) <sup>d</sup>				
	-	-	-	MCWHD3 (2350 mW Min)	-	-				
6200 K (Cold White)	-	-	-	-	-	-	MCWHF2 (21.5 mW)	-	-	-
5000 K (Cold White)	-	-	LEDSW50 (110 mW)	-	-	-	-	-	-	-
4600 - 9000 K (Cold White)	-	-	-	-	-	-	-	-	-	LIUCWHA (250 mW)
4000 K (Warm White)	-	-	LEDSW40 (115 mW)	-	-	-	MWWHF2 (16.3 mW)	-	-	-
3000 K (Warm White)	-	-	LEDSW30 (100 mW)	MWWHD3 (2000 mW Min)	MWWHL4 (570 mW Min)	-	-	SOLIS-2C (3.2 W) <sup>e</sup>	-	-

Light Emitting Diode (LED) Selection Guide										
5700 K (Day Light White)	-	-	-	-	MWWHLP1 (2000 mW Min)	-	-	-	SOLIS-3C (3.5 W)	-
					-					

- These Collimated LEDs are compatible with the standard and epi-illumination ports on the following microscopes: Olympus BX/IX (Item # Suffix: -C1), Leica DMI (Item # Suffix: -C2), Zeiss Axioskop (Item # Suffix: -C4), and Nikon Eclipse (Bayonet Mount, Item # Suffix: -C5).  
Typical power when used with MM Fiber with Ø400 µm core, 0.39 NA.
- Our Multi-Wavelength LED Sources are available with select combinations of the LEDs at these wavelengths.  
Typical power for LEDs with the Leica DMI collimation package (Item # Suffix: -C2).
- Minimum power for the collimated output of these LEDs. The collimation lens is installed with each LED.  
Typical power for LEDs with the Olympus BX and IX collimation package (Item # Suffix: -C1).
- Percentage of LED intensity that emits in the blue portion of the spectrum, from 400 nm to 525 nm.

### Deep UV Mounted LEDs (265 - 340 nm)

Please note that our deep UV LEDs radiate intense UV light during operation. Precautions must be taken to prevent looking directly at the UV light, and UV light protective glasses must be worn to avoid eye damage. Exposure of the skin and other body parts to UV light should be avoided.

















Item #	Info <sup>a</sup>	Nominal Wavelength <sup>b</sup>	Housing Type <sup>c</sup>	LED Output Power (Min / Typ.) <sup>b,d</sup>	Bandwidth (FWHM)	Irradiance (Typ.) <sup>e</sup>	Max Current (CW)	Forward Voltage (Typ.)	Viewing Angle (Full Angle at Half Max)	Recommended Driver
M265L3		265 nm		10 mW / 12 mW	11 nm	-	350 mA	6.8 V	130°	DC2200 or LEDD1B
M265L4		265 nm		24 mW / 35 mW	6.8 nm	0.47 µW/mm <sup>2</sup>	350 mA	6.0 V	120°	
M275L4		275 nm		45 mW / 80 mW	11 nm	0.8 µW/mm <sup>2</sup>	700 mA	7.3 V	118°	
M285L5		285 nm		50 mW / 70 mW	13 nm	0.7 µW/mm <sup>2</sup>	500 mA	5.9 V	120°	
M300L4		300 nm		26 mW / 32 mW	20 nm	0.3 µW/mm <sup>2</sup>	350 mA	8.0 V	130°	
M340L4		340 nm		53 mW / 60 mW	11 nm	2.22 µW/mm <sup>2</sup>	700 mA	4.6 V	110°	DC2200, LEDD1B, DC4100 <sup>f</sup> , or DC4104 <sup>f</sup>

- Click on the blue info icon for complete specifications and LED spectrum.
- Due to variations in the manufacturing process and operating parameters such as temperature and current, the actual spectral output of any given LED will vary. Output plots and nominal wavelength specs are only intended to be used as a guideline.
- Click for LED Product Photo
- When Driven at the Max Current
- Irradiance is measured at a distance of 200 mm from the LED.
- This is a four-channel driver and requires the DC4100-HUB connector hub to drive mounted LEDs.

Part Number	Description	Price	Availability
M265L3	265 nm, 10 mW (Min) Mounted LED, 350 mA	\$1,361.30	Today
M265L4	NEW! 265 nm, 24 mW (Min) Mounted LED, 350 mA	\$950.00	Today
M275L4	275 nm, 45 mW (Min) Mounted LED, 700 mA	\$371.32	Today
M285L5	285 nm, 50 mW (Min) Mounted LED, 500 mA	\$976.03	Today
M300L4	300 nm, 26 mW (Min) Mounted LED, 350 mA	\$497.78	Today
M340L4	340 nm, 53 mW (Min) Mounted LED, 700 mA	\$312.73	Today

## UV Mounted LEDs (365 - 405 nm)

Please note that our UV LEDs radiate intense UV light during operation. Precautions must be taken to prevent looking directly at the UV light, and UV light protective glasses must be worn to avoid eye damage. Exposure of the skin and other body parts to the UV light should be avoided.

























Item #	Info <sup>a</sup>	Nominal Wavelength <sup>b</sup>	Housing Type <sup>c</sup>	LED Output Power (Min / Typ.) <sup>b,d</sup>	Bandwidth (FWHM)	Irradiance (Typ.) <sup>e</sup>	Max Current (CW)	Forward Voltage (Typ.)	Viewing Angle (Full Angle at Half Max)	Recommended Driver
M365L2		365 nm		190 mW / 360 mW	7.5 nm	8.9 $\mu\text{W}/\text{mm}^2$	700 mA	4.4 V	120°	DC2200, LEDD1B, DC4100 <sup>f</sup> , or DC4104 <sup>f</sup>
M365LP1		365 nm		1150 mW / 1400 mW	9 nm	17.6 $\mu\text{W}/\text{mm}^2$	1700 mA	4.0 V	120°	DC2200
M375L4		375 nm		1270 mW / 1540 mW	9 nm	19.2 $\mu\text{W}/\text{mm}^2$	1400 mA	3.6 V	130°	
M385L2		385 nm		270 mW / 430 mW	10 nm	11.8 $\mu\text{W}/\text{mm}^2$	700 mA	4.3 V	120°	DC2200, LEDD1B, DC4100 <sup>f</sup> , or DC4104 <sup>f</sup>
M385LP1		385 nm		1650 mW / 1830 mW	12 nm	23.3 $\mu\text{W}/\text{mm}^2$	1700 mA	3.9 V	120°	DC2200
M395L4		395 nm		400 mW / 535 mW	16 nm	6.7 $\mu\text{W}/\text{mm}^2$	500 mA	4.5 V	126°	DC2200, LEDD1B, DC4100 <sup>f</sup> , or DC4104 <sup>f</sup>
M405L4		405 nm		1000 mW / 1300 mW	12.5 nm	14.53 $\mu\text{W}/\text{mm}^2$	1000 mA	3.4 V	140°	
M405LP1		405 nm		1200 mW / 1700 mW	12 nm	24.6 $\mu\text{W}/\text{mm}^2$	1400 mA	3.45 V	120°	DC2200

- Click on the blue info icon for complete specifications and LED spectrum.
- Due to variations in the manufacturing process and operating parameters such as temperature and current, the actual spectral output of any given LED will vary. Output plots and nominal wavelength specs are only intended to be used as a guideline.
- Click for LED Product Photo
- When Driven at the Max Current
- Irradiance is measured at a distance of 200 mm from the LED.
- This is a four-channel driver and requires the DC4100-HUB connector hub to drive mounted LEDs.

Part Number	Description	Price	Availability
M365L2	365 nm, 190 mW (Min) Mounted LED, 700 mA	\$518.34	Today
M365LP1	365 nm, 1150 mW (Min) Mounted LED, 1700 mA	\$460.99	Today
M375L4	375 nm, 1270 mW (Min) Mounted LED, 1400 mA	\$180.35	Today
M385L2	385 nm, 270 mW (Min) Mounted LED, 700 mA	\$518.34	Today
M385LP1	385 nm, 1650 mW (Min) Mounted LED, 1700 mA	\$460.99	Today
M395L4	395 nm, 400 mW (Min) Mounted LED, 500 mA	\$312.73	Today
M405L4	405 nm, 1000 mW (Min) Mounted LED, 1000 mA	\$233.40	Today
M405LP1	405 nm, 1200 mW (Min) Mounted LED, 1400 mA	\$460.99	Today

## Single-Color Cold Visible Mounted LEDs (420 - 565 nm)

Please note that the 415 nm (violet) LEDs radiate intense UV light during operation. Precautions must be taken to prevent looking directly at the UV light, and UV light protective glasses must be worn to avoid eye damage. Exposure of the skin and other body parts to the UV light should be avoided.





















Item #	Info <sup>a</sup>	Nominal Wavelength <sup>b,c</sup>	Housing Type <sup>d</sup>	LED Output Power (Min / Typ.) <sup>b,e</sup>	Bandwidth (FWHM)	Irradiance (Typ.) <sup>f</sup>	Max Current (CW)	Forward Voltage <sup>g</sup>	Viewing Angle (Full Angle at Half Max)	Recommended Driver
M415L4 <sup>h</sup>		415 nm (Violet)		1310 mW / 1550 mW	14 nm	15.6 $\mu\text{W}/\text{mm}^2$	1500 mA	3.1 V	138°	DC2200
M415LP1 <sup>h</sup>		415 nm (Violet)		1640 mW / 1940 mW	14 nm	19.5 $\mu\text{W}/\text{mm}^2$	2000 mA	3.15 V	138°	
M430L4		430 nm (Violet)		490 mW / 600 mW	15 nm	35.3 $\mu\text{W}/\text{mm}^2$	500 mA	3.8 V	22°	DC2200, LEDD1B, DC4100 <sup>i</sup> , or DC4104 <sup>i</sup>
M450LP1		450 nm (Royal Blue)		1850 mW / 2100 mW	18 nm	35.6 $\mu\text{W}/\text{mm}^2$	2000 mA	3.5 V	120°	DC2200
M455L4		455 nm (Royal Blue)		1150 mW / 1445 mW	18 nm	32 $\mu\text{W}/\text{mm}^2$	1000 mA	3.25 V	80°	DC2200, LEDD1B, DC4100 <sup>i</sup> , or DC4104 <sup>i</sup>
M470L4		470 nm (Blue)		760 mW / 965 mW	26 nm	19.9 $\mu\text{W}/\text{mm}^2$	1000 mA	3.2 V	80°	
M490L4		490 nm (Blue)		205 mW / 240 mW	26 nm	2.5 $\mu\text{W}/\text{mm}^2$	350 mA	3.8 V	128°	
M505L3		505 nm (Cyan)		400 mW / 440 mW	30 nm	11.1 $\mu\text{W}/\text{mm}^2$	1000 mA	3.3 V	80°	
M505L4		505 nm (Cyan)		400 mW / 520 mW	37 nm	5.94 $\mu\text{W}/\text{mm}^2$	1000 mA	3.5 V	130°	
M530L4		530 nm (Green)		370 mW / 480 mW	35 nm	9.46 $\mu\text{W}/\text{mm}^2$	1000 mA	3.6 V	80°	
MINTL5		554 nm (Mint)		650 mW / 1850 mW	-	12.4 $\mu\text{W}/\text{mm}^2$	1225 mA	3.5 V	120°	DC2200 or LEDD1B <sup>j</sup>
M565L3 <sup>k</sup>		565 nm (Lime)		880 mW / 979 mW	104 nm	11.7 $\mu\text{W}/\text{mm}^2$	1000 mA	3.1 V (Max)	125°	DC2200, LEDD1B, DC4100 <sup>i</sup> , or DC4104 <sup>i</sup>

- Click on the blue info icon for complete specifications and LED spectrum.
- Due to variations in the manufacturing process and operating parameters such as temperature and current, the actual spectral output of any given LED will vary. Output plots and nominal wavelength specs are only intended to be used as a guideline.
- The nominal wavelength indicates the wavelength at which the LED appears brightest to the human eye. The nominal wavelength for visible LEDs may not correspond to the peak wavelength as measured by a spectrometer.
- Click for LED Product Photo
- When Driven at the Max Current
- Irradiance is measured at a distance of 200 mm from the LED.
- Values are typical unless otherwise stated.
- This LED radiates intense UV light during operation. Precautions must be taken to prevent looking directly at the UV light and UV light protective glasses must be worn to avoid eye damage. Exposure of the skin and other body parts to the UV light should be avoided.
- This is a four-channel driver and requires the DC4100-HUB connector hub to drive mounted LEDs.
- Due to the maximum current that can be provided by this driver, while this mounted LED can be driven, it will not reach full power.
- This LED is phosphor-converted and may not turn off completely when modulated above 10 kHz at duty cycles below 50%.

Part Number	Description	Price	Availability
M415L4	415 nm, 1310 mW (Min) Mounted LED, 1500 mA	\$212.18	Today
M415LP1	415 nm, 1640 mW (Min) Mounted LED, 2000 mA	\$318.27	Today
M430L4	430 nm, 490 mW (Min) Mounted LED, 500 mA	\$175.05	Today
M450LP1	450 nm, 1850 mW (Min) Mounted LED, 2000 mA	\$325.72	Today
M455L4	455 nm, 1150 mW (Min) Mounted LED, 1000 mA	\$296.50	Today
M470L4	470 nm, 760 mW (Min) Mounted LED, 1000 mA	\$296.50	Today
M490L4	490 nm, 205 mW (Min) Mounted LED, 350 mA	\$206.68	Today
M505L3	505 nm, 440 mW (Typ.) Mounted LED, 1000 mA	\$229.69	Today
M505L4	505 nm, 520 mW (Typ.) Mounted LED, 1000 mA	\$296.50	Today
M530L4	530 nm, 370 mW (Min) Mounted LED, 1000 mA	\$296.50	Today

MINTL5	554 nm, 650 mW (Min) Mounted LED, 1225 mA	\$283.25	Today
M565L3	565 nm, 880 mW (Min) Mounted LED, 1000 mA	\$233.74	Today

































### Single-Color Warm Visible Mounted LEDs (590 - 730 nm)

Item #	Info <sup>a</sup>	Nominal Wavelength <sup>b,c</sup>	Housing Type <sup>d</sup>	LED Output Power (Min / Typ.) <sup>b,e</sup>	Bandwidth (FWHM)	Irradiance (Typ.) <sup>f</sup>	Max Current (CW)	Forward Voltage (Typ.)	Viewing Angle (Full Angle at Half Max)	Recommended Driver
M590L3		590 nm (Amber)		160 mW / 170 mW	18 nm	5.3 $\mu\text{W}/\text{mm}^2$	1000 mA	2.2 V	80°	DC2200, LEDD1B, DC4100 <sup>h</sup> , or DC4104 <sup>h</sup>
M590L4		590 nm (Amber)		230 mW / 300 mW	15 nm	6.0 $\mu\text{W}/\text{mm}^2$	1000 mA	2.5 V	80°	
M595L3 <sup>g</sup>		595 nm (Amber)		445 mW / 502 mW	80 nm	6.9 $\mu\text{W}/\text{mm}^2$	700 mA	3.05 V	125°	
M617L3		617 nm (Orange)		600 mW / 650 mW	18 nm	15.7 $\mu\text{W}/\text{mm}^2$	1000 mA	2.2 V	80°	
M617L4		617 nm (Orange)		660 mW / 860 mW	16 nm	19.86 $\mu\text{W}/\text{mm}^2$	1000 mA	2.6 V	80°	
M625L4		625 nm (Red)		700 mW / 920 mW	17 nm	21.9 $\mu\text{W}/\text{mm}^2$	1000 mA	2.5 V	80°	
M660L4		660 nm (Deep Red)		940 mW / 1050 mW	20 nm	20.88 $\mu\text{W}/\text{mm}^2$	1200 mA	2.6 V	120°	DC2200 or LEDD1B
M680L4		680 nm (Deep Red)		180 mW / 210 mW	22 nm	14.5 $\mu\text{W}/\text{mm}^2$	600 mA	2.5 V	18°	DC2200, LEDD1B, DC4100 <sup>h</sup> , or DC4104 <sup>h</sup>
M700L4		700 nm (Deep Red)		80 mW / 125 mW	20 nm	1.0 $\mu\text{W}/\text{mm}^2$	500 mA	2.7 V	128°	
M730L5		730 nm (Far Red)		540 mW / 680 mW	40 nm	13.1 $\mu\text{W}/\text{mm}^2$	1000 mA	2.25 V	80°	

- Click on the blue info icon for complete specifications and LED spectrum.
- Due to variations in the manufacturing process and operating parameters such as temperature and current, the actual spectral output of any given LED will vary. Output plots and nominal wavelength specs are only intended to be used as a guideline.
- The nominal wavelength indicates the wavelength at which the LED appears brightest to the human eye. The nominal wavelength for visible LEDs may not correspond to the peak wavelength as measured by a spectrometer.
- Click for LED Product Photo
- When Driven at the Max Current
- Irradiance is measured at a distance of 200 mm from the LED.
- This LED is phosphor-converted and may not turn off completely when modulated above 10 kHz at duty cycles below 50%.
- This is a four-channel driver and requires the DC4100-HUB connector hub to drive mounted LEDs.

Part Number	Description	Price	Availability
M590L3	590 nm, 160 mW (Min) Mounted LED, 1000 mA	\$164.80	Lead Time
M590L4	590 nm, 230 mW (Min) Mounted LED, 1000 mA	\$216.30	Today
M595L3	595 nm, 445 mW (Min) Mounted LED, 700 mA	\$233.74	Today
M617L3	617 nm, 600 mW (Min) Mounted LED, 1000 mA	\$164.80	Today
M617L4	617 nm, 660 mW (Min) Mounted LED, 1000 mA	\$216.30	Today
M625L4	625 nm, 700 mW (Min) Mounted LED, 1000 mA	\$216.30	Today
M660L4	660 nm, 940 mW (Min) Mounted LED, 1200 mA	\$233.74	Today
M680L4	Customer Inspired! 680 nm, 180 mW (Min) Mounted LED, 600 mA	\$209.93	Today
M700L4	700 nm, 80 mW (Min) Mounted LED, 500 mA	\$209.93	Today
M730L5	730 nm, 540 mW (Min) Mounted LED, 1000 mA	\$221.45	Today

## IR Mounted LEDs (780 - 1650 nm)



Item #	Info <sup>a</sup>	Nominal Wavelength <sup>b</sup>	Housing Type <sup>c</sup>	LED Output Power (Min / Typ.) <sup>b,d</sup>	Bandwidth (FWHM)	Irradiance (Typ.) <sup>e</sup>	Max Current (CW)	Forward Voltage (Typ.)	Viewing Angle (Full Angle at Half Max)	Recommended Driver
M780L3		780 nm		200 mW / 300 mW	28 nm	47.3 $\mu\text{W}/\text{mm}^2$	800 mA	2.0 V	20°	DC2200, LEDD1B, DC4100 <sup>f</sup> , or DC4104 <sup>f</sup>
M780LP1		780 nm		800 mW / 950 mW	30 nm	13.3 $\mu\text{W}/\text{mm}^2$	800 mA	6.6 V	120°	DC2200 or LEDD1B
M810L3		810 nm		325 mW / 375 mW	25 nm	61.8 $\mu\text{W}/\text{mm}^2$	500 mA	3.6 V	20°	DC2200, LEDD1B, DC4100 <sup>f</sup> , or DC4104 <sup>f</sup>
M810L4		810 nm		363 mW / 542 mW	32 nm	23.7 $\mu\text{W}/\text{mm}^2$	1000 mA	3.55 V	80°	
M850L3		850 nm		900 mW / 1100 mW	30 nm	22.9 $\mu\text{W}/\text{mm}^2$	1200 mA	2.95 V	90°	DC2200 or LEDD1B
M850LP1		850 nm		1400 mW / 1600 mW	30 nm	19.4 $\mu\text{W}/\text{mm}^2$	1500 mA	3.85 V	150°	DC2200
M880L3		880 nm		300 mW / 350 mW	50 nm	5.6 $\mu\text{W}/\text{mm}^2$	1000 mA	1.7 V	132°	DC2200, LEDD1B, DC4100 <sup>f</sup> , or DC4104 <sup>f</sup>
M940L3		940 nm		800 mW / 1000 mW	37 nm	19.1 $\mu\text{W}/\text{mm}^2$	1000 mA	2.75 V	90°	
M970L4		970 nm		600 mW / 720 mW	60 nm	7.4 $\mu\text{W}/\text{mm}^2$	1000 mA	1.9 V	130°	
M1050L2		1050 nm		50 mW / 70 mW	60 nm	1.9 $\mu\text{W}/\text{mm}^2$	700 mA	1.5 V	120°	
M1050L4		1050 nm		160 mW / 210 mW	37 nm	3.7 $\mu\text{W}/\text{mm}^2$	600 mA	1.4 V	128°	
M1200L3		1200 nm		30 mW / 35 mW	80 nm	0.7 $\mu\text{W}/\text{mm}^2$	700 mA	1.4 V	134°	
M1300L3		1300 nm		25 mW / 30 mW	80 nm	0.6 $\mu\text{W}/\text{mm}^2$	500 mA	1.4 V	134°	
M1450L3		1450 nm		31 mW / 36 mW	80 nm	0.4 $\mu\text{W}/\text{mm}^2$	700 mA	1.15 V	136°	
M1550L3		1550 nm		31 mW / 36 mW	102 nm	0.5 $\mu\text{W}/\text{mm}^2$	1000 mA	1.35 V	136°	
M1650L4		1650 nm		13 mW / 16 mW	120 nm	1.2 $\mu\text{W}/\text{mm}^2$	600 mA	1.1 V	20°	

- Click on the blue info icon for complete specifications and LED spectrum.
- Due to variations in the manufacturing process and operating parameters such as temperature and current, the actual spectral output of any given LED will vary. Output plots and nominal wavelength specs are only intended to be used as a guideline.
- Click for LED Product Photo
- When Driven at the Max Current
- Irradiance is measured at a distance of 200 mm from the LED.
- This is a four-channel driver and requires the DC4100-HUB connector hub to drive mounted LEDs.

Part Number	Description	Price	Availability
M780L3	780 nm, 200 mW (Min) Mounted LED, 800 mA	\$233.74	Today
M780LP1	780 nm, 800 mW (Min) Mounted LED, 800 mA	\$353.86	Today
M810L3	810 nm, 325 mW (Min) Mounted LED, 500 mA	\$217.51	Today
M810L4	810 nm, 363 mW (Min) Mounted LED, 1000 mA	\$255.00	Today
M850L3	850 nm, 900 mW (Min) Mounted LED, 1200 mA	\$233.74	Today
M850LP1	850 nm, 1400 mW (Min) Mounted LED, 1500 mA	\$370.09	Today
M880L3	880 nm, 300 mW (Min) Mounted LED, 1000 mA	\$233.74	Today
M940L3	940 nm, 800 mW (Min) Mounted LED, 1000 mA	\$233.74	Today
M970L4	970 nm, 600 mW (Min) Mounted LED, 1000 mA	\$180.35	Today
M1050L2	Customer Inspired! 1050 nm, 50 mW (Min) Mounted LED, 700 mA	\$251.05	Today
M1050L4	1050 nm, 160 mW (Min) Mounted LED, 600 mA	\$305.54	Today
M1200L3	Customer Inspired! 1200 nm, 30 mW (Min) Mounted LED, 700 mA	\$311.65	Today
M1300L3	Customer Inspired! 1300 nm, 25 mW (Min) Mounted LED, 500 mA	\$311.65	Today
M1450L3	1450 nm, 31 mW (Min) Mounted LED, 700 mA	\$311.65	Today
M1550L3	Customer Inspired! 1550 nm, 31 mW (Min) Mounted LED, 1000 mA	\$311.65	Today
M1650L4	1650 nm, 13 mW (Min) Mounted LED, 600 mA	\$310.84	Today

**Purple Mounted LED (455 nm / 640 nm)**

Our dual-peak LED was designed for applications requiring illumination in both red and blue portions of the spectrum, such as horticulture. This purple LED features dual peaks at 455 nm and 640 nm, respectively, to stimulate photosynthesis (see graph to compare the absorption peaks of photosynthesis pigments with the LED spectrum). The LED was designed to maintain the red/blue ratio of the emission spectrum over its lifetime to provide high uniformity of plant growth.











Item #	Info <sup>a</sup>	Nominal Wavelength <sup>b</sup>	Housing Type <sup>c</sup>	LED Output Power (Min / Typ.) <sup>b,d</sup>	Bandwidth (FWHM)	Irradiance (Typ.) <sup>e</sup>	Max Current (CW)	Forward Voltage (Typ.)	Viewing Angle (Full Angle at Half Max)	Recommended Driver
MPRP1L4 <sup>f</sup>		455 nm (12.5% <sup>g</sup> ) / 640 nm		275 mW / 325 mW	N/A	3.7 $\mu\text{W}/\text{mm}^2$	300 mA	3.1 V	115°	DC2200, LEDD1B, DC4100 <sup>h</sup> , or DC4104 <sup>h</sup>

- Click on the blue info icon for complete specifications and LED spectrum.
- Due to variations in the manufacturing process and operating parameters such as temperature and current, the actual spectral output of any given LED will vary. Output plots and nominal wavelength specs are only intended to be used as a guideline.
- Click for LED Product Photo
- When Driven at the Max Current
- Irradiance is measured at a distance of 200 mm from the LED.
- This LED is phosphor-converted and may not turn off completely when modulated above 10 kHz at duty cycles below 50%.
- Percentage of LED intensity that emits in the blue portion of the spectrum, from 400 nm to 525 nm. Click on the info icon for details.
- This is a four-channel driver and requires the DC4100-HUB connector hub to drive mounted LEDs.

Part Number	Description	Price	Availability
MPRP1L4	455 nm (12.5%) / 640 nm, 275 mW (Min) Mounted LED, 300 mA	\$159.14	Today

## White Mounted LEDs (400 - 700 nm Wavelength Range)

Our warm, neutral, and cold white LEDs feature broad spectra that span several hundred nanometers. The difference in appearance among these LEDs can be described using the correlated color temperature, which indicates that the LEDs color appearance is similar to a black body radiator at that temperature. In general, warm white LEDs offer a spectrum similar to a tungsten source, while cold white LEDs have a stronger blue component to the spectrum; neutral white LEDs provide a more even illumination spectrum over the visible range than warm white or cold white LEDs. Cold white LEDs are more suited for fluorescence microscopy applications or cameras with white balancing, because of a higher intensity at most wavelengths compared to warm white LEDs. Neutral white LEDs are ideal for horticultural applications.

Item #	Info <sup>a</sup>	Color Temperature <sup>b</sup>	Housing Type <sup>c</sup>	LED Output Power (Min / Typ.) <sup>b,d</sup>	Bandwidth (FWHM)	Irradiance (Typ.) <sup>e</sup>	Max Current (CW)	Forward Voltage (Typ.)	Viewing Angle (Full Angle at Half Max)	Recommended Driver
MWWHL4 <sup>f</sup>		3000 K (Warm White)		570 mW / 640 mW	N/A	9.4 $\mu\text{W}/\text{mm}^2$	1000 mA	3.0 V	120°	DC2200, LEDD1B, DC4100 <sup>g</sup> , or DC4104 <sup>g</sup>
MWWHLP1 <sup>f</sup>		3000 K (Warm White)		2000 mW / 2300 mW	N/A	37.0 $\mu\text{W}/\text{mm}^2$	700 mA	11.7 V	125°	DC2200 or LEDD1B
MNWHL4 <sup>f</sup>		4900 K (Neutral White)		740 mW / 880 mW	N/A	7.7 $\mu\text{W}/\text{mm}^2$	1225 mA	2.9 V	150°	DC2200, LEDD1B, DC4100 <sup>g,h</sup> , or DC4104 <sup>g,h</sup>
MCWHL6 <sup>f</sup>		6500 K (Cold White)		990 mW / 1430 mW	N/A	25.0 $\mu\text{W}/\text{mm}^2$	1200 mA	2.8 V	120°	DC2200, LEDD1B, DC4100 <sup>g,h</sup> , or DC4104 <sup>g,h</sup>
MCWHLP1 <sup>f</sup>		6500 K (Cold White)		2350 mW / 2700 mW	N/A	41.3 $\mu\text{W}/\text{mm}^2$	700 mA	11.7 V	125°	DC2200 or LEDD1B



- Click on the blue info icon for complete specifications and LED spectrum.
- Due to variations in the manufacturing process and operating parameters such as temperature and current, the actual spectral output of any given LED will vary. Output plots and nominal wavelength specs are only intended to be used as a guideline.
- Click for LED Product Photo
- When Driven at the Max Current
- Irradiance is measured at a distance of 200 mm from the LED.
- These LEDs are phosphor-converted and may not turn off completely when modulated above 10 kHz at duty cycles below 50%.
- This is a four-channel driver and requires the DC4100-HUB connector hub to drive mounted LEDs.
- Due to the maximum current that can be provided by this driver, while this mounted LED can be driven, it will not reach full power.

Part Number	Description	Price	Availability
MWWHL4	3000 K, 570 mW (Min) Mounted LED, 1000 mA	\$182.88	Today
MWWHLP1	3000 K, 2000 mW (Min) Mounted LED, 700 mA	\$331.12	Today
MNWHL4	4900 K, 740 mW (Min) Mounted LED, 1225 mA	\$159.14	Today
MCWHL6	6500 K, 990 mW (Min) Mounted LED, 1200 mA	\$215.00	Today
MCWHLP1	6500 K, 2350 mW (Min) Mounted LED, 700 mA	\$331.12	Today



**Broadband Mounted LED (470 - 850 nm)**

The MBB1L3 mounted broadband LED has been designed to have a relatively flat spectral emission over a wide wavelength range. Its FWHM bandwidth ranges from 500 nm to 780 nm, while the 10 dB bandwidth ranges between 470 nm and 850 nm.

Item #	Info <sup>a</sup>	Nominal Wavelength <sup>b</sup>	Housing Type <sup>c</sup>	LED Output Power (Min / Typ.) <sup>b,d</sup>	Bandwidth (FWHM)	Irradiance (Typ.) <sup>e</sup>	Max Current (CW)	Forward Voltage (Typ.)	Viewing Angle (Full Angle at Half Max)	Recommended Driver
MBB1L3 <sup>f</sup>		470 - 850 nm (10 dB Bandwidth)		70 mW	280 nm	12.5 $\mu\text{W}/\text{mm}^2$	500 mA	3.6 V	120°	DC2200, LEDD1B, DC4100 <sup>g</sup> , or DC4104 <sup>g</sup>

- Click on the blue info icon for complete specifications and LED spectrum.
- Due to variations in the manufacturing process and operating parameters such as temperature and current, the actual spectral output of any given LED will vary. Output plots and nominal wavelength specs are only intended to be used as a guideline.
- Click for LED Product Photo
- When Driven at the Max Current
- Irradiance is measured at a distance of 200 mm from the LED.
- The LED may not turn off completely when modulated at frequencies above 1 kHz with a duty cycle of 50%, as the broadband emission is produced by optically stimulating emission from phosphor. For modulation at frequencies above 1 kHz, the duty cycle may be reduced. For example, 10 kHz modulation is attainable with a duty cycle of 5%.
- This is a four-channel driver and requires the DC4100-HUB connector hub to drive mounted LEDs.

Part Number	Description	Price	Availability
MBB1L3	Broadband (470 - 850 nm), 70 mW (Min) Mounted LED, 500 mA	\$545.39	Today

### Adjustable Collimation Adapters for Ø1" (Ø25 mm) or Ø2" (Ø50 mm) Optics

- ▶ Integrate a Ø1" (Ø25 mm) or Ø2" (Ø50 mm) Collimation Optic with Thorlabs' Mounted LEDs
- ▶ Adjust and Set Lens Position via Rotating Ring with Locking Setscrew
- ▶ Available with or without AR-Coated Lens (See Table Below for Details)
- ▶ Compatible with Thorlabs' SM2-Threaded Microscope Port Adapters



Click to Enlarge  
SM2F Adapter Installed  
on a  
M365LP1 Mounted LED

These adapters allow Ø1" (Ø25 mm) or Ø2" (Ø50 mm) collimation optics to be integrated with the mounted LEDs sold above. The adapters can translate a Ø1" or Ø2" lens by up to 11 mm or 20 mm, respectively. They are offered in versions without a collimation optic or with a removable AR-coated aspheric condenser lens for 350 - 700 nm or 650 - 1050 nm. All of these adapters attach to the LED housing via external SM1 threads, allowing them to be used with both the Ø30.5 mm and Ø57.0 mm housings.

The collimation lens is mounted in an inner carriage that provides non-telescoping, rotating translation along the Z-axis by turning the knurled adjustment ring (engraved with the item # in the photos to the left) and is locked into position by turning the locking screw on the side of the adjustment ring with a 2 mm (5/64") hex key. Lines, spaced 2 mm apart, are engraved on the housing as a rough guide for how far the carriage has been translated. These collimation adapters use an extra-thick SM1-threaded or SM2-threaded retaining ring designed for holding aspheric condenser lenses. The retaining rings can be tightened or loosened using either an SPW602 (Ø1" versions) or SPW604 (Ø2" versions) spanner wrench.


The threading on the input and output apertures remain fixed during translation, allowing these adapters to be mounted between fixed lens tubes. These apertures are threaded for compatibility with various components; please see the table below for details.



#### Inserting or Removing Optics

To insert or remove an optic in these collimation adapters, use the adjustment ring to translate the inner carriage to the output end of the housing. Remove the included retaining ring using the spanner wrench. If there is a lens installed already, remove it from the carriage. Insert another Ø1" (Ø25 mm) or Ø2" (Ø50 mm) optic into the carriage, and use the retaining ring to secure it.

Using a lens with a substrate or AR coating that does not transmit the wavelength of your LED is not recommended. Deep UV LEDs (wavelengths ≤ 340 nm) require a lens fabricated from UV Fused Silica, since many standard varieties of glass do not transmit below 350 nm. IR LEDs that emit at wavelengths ≥ 1050 nm can be collimated using an uncoated condenser lens, such as the Ø50 mm ACL50832U which has a wavelength range of 380 - 2100 nm.

<b>LED Quick Links</b>
<b>Mounted LEDs</b>
Deep UV (265 - 340 nm)
UV (365 - 405 nm)
Cold Visible (420 - 565 nm)
Warm Visible (590 - 730 nm)
IR (780 - 1550 nm)
White (400 - 700 nm)
Broadband (470 - 850 nm)
<b>LED Collimation<sup>a</sup></b>
Adjustable Collimation Adapters
Microscope Collimation Adapters
<b>LED Mating Connector</b>
<b>LED Drivers</b>

- We offer suggestions for how to collimate most of our LEDs. Click on the info icons (  ) above for details.

Item #	Compatible Optic	Lens Travel Range	Input Threading	Output Threading	Included Lens	AR Coating Range	Lens Focal Length	Operating Temperature	Diagram	
SM1U <sup>a</sup>	Ø1" (Ø25 mm)	11 mm (0.43")	External SM1 (1.035"-40)	Internal SM2 (2.035"-40) <sup>b</sup>	N/A	N/A	N/A	15 - 60 °C (Non-Condensing)		
SM1U25-A					ACL2520U-A	350 - 700 nm	20.1 mm			
SM1U25-B					ACL2520U-B	650 - 1050 nm	20.1 mm			
SM2F <sup>a</sup>	Ø2" (Ø50 mm)	20 mm (0.79")	External SM1 (1.035"-40) <sup>c</sup>	Internal SM2 (2.035"-40) <sup>d</sup>	N/A	N/A	N/A			
SM2F32-A					ACL50832U-A	350 - 700 nm	32.0 mm			
SM2F32-B					ACL50832U-B	650 - 1050 nm	32.0 mm			

- The SM1U and SM2F do not include a collimation optic, allowing user-supplied optics, such as our aspheric condenser lenses, to be integrated with Thorlabs' mounted LEDs.
- This thread is part of a removable adapter; removing the adapter reveals internal M34 x 0.5 threading. The SM1A38 thread adapter can be used in place of this adapter for SM1 compatibility
- This thread is part of a removable adapter; removing the adapter reveals external SM2 (2.035"-40) threading.
- This thread is part of a removable adapter; removing the adapter reveals internal M62 x 0.75 threading.

Part Number	Description	Price	Availability
SM1U	<b>NEW!</b> Adjustable Collimation Adapter for Ø1" or Ø25 mm Optic	\$271.00	Today
SM1U25-A	<b>NEW!</b> Adjustable Collimation Adapter with Ø1" Lens, AR Coating: 350 - 700 nm	\$288.00	5-8 Days
SM1U25-B	<b>NEW!</b> Adjustable Collimation Adapter with Ø1" Lens, AR Coating: 650 - 1050 nm	\$288.00	Today
SM2F	Adjustable Collimation Adapter for Ø2" or Ø50 mm Optic	\$268.37	Today
SM2F32-A	Adjustable Collimation Adapter with Ø2" Lens, AR Coating: 350 - 700 nm	\$285.68	Today
SM2F32-B	Adjustable Collimation Adapter with Ø2" Lens, AR Coating: 650 - 1050 nm	\$285.68	Today

### Microscope Collimation Adapters with Ø50 mm Lens

- ▶ AR-Coated Aspheric Lens with Low f/# (Approximately 0.8)
- ▶ Compatible with Select Leica, Nikon, Olympus, or Zeiss Microscopes
- ▶ Easily Adjust Beam Collimation / Focus
- ▶ Requires SM2T2 Coupler and SM1A2 Adapter (Each Sold Separately) when Used with the LEDs Above



Click for Details

Installation of a collimation adapter to a mounted LED using the SM2T2 and SM1A2 thread adapters. The same setup can be used to attach the collimation adapter to the LEDs above that use a Ø57.0 mm housing.


Thorlabs offers collimation adapters with Ø50 mm AR-coated aspheric condenser lenses (EFL: 40 mm) for collimating the output from the mounted LEDs sold above. Two AR coating ranges (350 - 700 nm and 650 - 1050 nm) and four different collimator housings are available. Each housing is designed with a dovetail or bayonet mount to mate to the illumination port on selected Olympus\*, Leica, Nikon, or Zeiss microscopes. Compatible microscopes are listed in the Collimation Adapter Selection Guide table below.

Using an adapter with a substrate or AR coating that does not transmit the wavelength of your LED is not recommended. Deep UV LEDs (M265L3, M280L3, and M340L3) require a lens fabricated from UV Fused Silica, since many standard varieties of glass do not transmit below 350 nm. IR LEDs that emit beyond 1050 nm (M1200L3, M1300L3, M1450L3, and M1550L3) can be collimated using an uncoated condenser lens; the ACL5040U is an uncoated version of the Ø50 mm lenses used in the collimation packages below that has a wavelength range of 380 - 2100 nm. See the *Collimation Adapter* tab in the info icons above for additional collimation options.

The LED sources described above can be fitted to the collimators by using an SM2T2 Coupler and SM1A2 Adapter (not included) as shown in the image at right. This assembly can be easily adapted to different LED sources by unscrewing the LED housing.

\*Please note that due to the optical design of the transmitted lamphouse port of the BX and IX microscopes, it may be necessary to purchase a separate adapter, which is available from Olympus.

<b>LED Quick Links</b>
<b>Mounted LEDs</b>
Deep UV (265 - 340 nm)
UV (365 - 405 nm)
Cold Visible (420 - 565 nm)
Warm Visible (590 - 730 nm)
IR (780 - 1550 nm)
White (400 - 700 nm)
Broadband (470 - 850 nm)
<b>LED Collimation<sup>a</sup></b>
Adjustable Collimation Adapters
Microscope Collimation Adapters
<b>LED Mating Connector</b>
<b>LED Drivers</b>

- We offer suggestions for how to collimate most of our LEDs. Click on the info icons (  ) above for details.

Collimation Adapter Selection Guide

Compatible Microscopes			Olympus BX & IX <sup>a</sup>	Leica DMI	Zeiss Axioskop & Examiner <sup>b</sup>	Nikon Eclipse Ti
AR Coating Range of Condenser Lens	Lens Focal Length	Lens Item #				
			Click to Enlarge	Click to Enlarge	Click to Enlarge	Click to Enlarge
			COP1-A	COP2-A	COP4-A	COP5-A
350 - 700 nm	40.0 mm	ACL5040U-A	COP1-B	COP2-B	COP4-B	COP5-B
650 - 1050 nm	40.0 mm	ACL5040U-B				

- Please note that due to the optical design of the transmitted lamphouse port of the BX and IX microscopes it may be necessary to purchase a separate adapter which is available from Olympus.
- These adapters are compatible with any Zeiss microscopes that use the same dovetail as the Zeiss Axioskop or Examiner microscopes.



Part Number	Description	Price	Availability
COP1-A	Collimation Adapter for Olympus BX & IX, AR Coating: 350 - 700 nm	\$200.19	Today
COP1-B	Collimation Adapter for Olympus BX & IX, AR Coating: 650 - 1050 nm	\$233.74	Today
COP2-A	Collimation Adapter for Leica DMI, AR Coating: 350 - 700 nm	\$200.19	Today
COP2-B	Collimation Adapter for Leica DMI, AR Coating: 650 - 1050 nm	\$233.74	Today
COP4-A	Collimation Adapter for Zeiss Axioskop & Examiner, AR Coating: 350 - 700 nm	\$200.19	Today
COP4-B	Collimation Adapter for Zeiss Axioskop & Examiner, AR Coating: 650 - 1050 nm	\$233.74	Today
COP5-A	Collimation Adapter for Nikon Eclipse Ti, AR Coating: 350 - 700 nm	\$236.98	Today
COP5-B	Collimation Adapter for Nikon Eclipse Ti, AR Coating: 650 - 1050 nm	\$274.86	Today
SM1A2	Adapter with External SM1 Threads and Internal SM2 Threads	\$26.51	Today
SM2T2	SM2 (2.035"-40) Coupler, External Threads, 1/2" Long	\$37.61	Today

### Mounted LED Mating Connector

- ▶ Pico (M8) Receptacle
- ▶ Female 4-Pin for Front Mounting
- ▶ 0.5 m Long, 24 AWG Wires
- ▶ M8 x 0.5 Panel Mount Thread
- ▶ IP 67 and NEMA 6P Rated

The CON8ML-4 connector can be used to mate mounted LEDs featured on this page to user-supplied power supplies. We also offer a male 4-Pin M8 connector cable (item # CAB-LEDD1).

Pin	Color	Specification
1	Brown	LED Anode
2	White	LED Cathode
3	Black	EEPROM GND
4	Blue	EEPROM IO


CON8ML-4 Shown Connected to the 4-Pin M8 Plug of Mounted LED

Part Number	Description	Price	Availability
CON8ML-4	4-Pin Female Mating Connector for Mounted LEDs	\$33.28	Today

### M595L3 - 595 nm, 445 mW (Min) Mounted LED, 700 mA




Spectrum
Specs
Drawing
Collimation Adapter



Click [here](#) to download an Excel file containing the spectral data for a larger wavelength range than shown in the graph above.

Due to variations in the manufacturing process and operating parameters such as temperature and current, the actual spectral output of any given LED will vary. This plot is only intended to be used as a guideline.

Spectrum	Specs	Drawing	Collimation Adapter		
<b>M595L3 Characteristics</b>					
<b>Optical Specifications</b>		<b>MIN</b>	<b>TYP</b>	<b>MAX</b>	<b>UNIT</b>
Nominal Wavelength <sup>a</sup>	-	595	-	nm	
Dominant Wavelength	587.8	591.0	592.0	nm	
Bandwidth (FWHM)	-	80	-	nm	
LED Output Power <sup>b</sup>	445	502	-	mW	
Viewing Angle (Full Angle at Half Max)	-	125	-	deg.	
Irradiance <sup>c</sup>	-	-	6.9	$\mu\text{W}/\text{mm}^2$	
<b>Electrical Specifications</b>					
Current (CW)	-	-	700	mA	
Forward Voltage	-	3.05	-	V	
Electrical Power	-	2135	-	mW	
<b>General Specifications</b>					
<b>Characteristic</b>		<b>Value</b>			
Emitter Size		1 mm x 1 mm			
Lifetime <sup>d</sup>		50 000 h			
Operating Temperature (Non-Condensing)		0 to 40 °C			
Storage Temperature		-40 to 70 °C			
Risk Group <sup>e</sup>		RG0 - Exempt Group			
Housing Diameter		Ø30.5 mm			
Mechanical Compatibility		SM1 (1.035"-40) Internal Threads			
Cable Length		2 m			
<p>a. Due to variations in the manufacturing process and operating parameters such as temperature and current, the actual spectral output of any given LED will vary. The nominal wavelength is only intended to be used as a guideline.</p> <p>b. When Driven with the Test Current</p> <p>c. Measured at a Distance of 200 mm</p> <p>d. Thorlabs defines the lifetime of our LEDs as <math>B_{50}/L_{50}</math>, meaning that 50% of the LEDs with a given item # will fall below 50% of the initial optical power at the end of the specified lifetime. Please see the <i>Stability</i> tab for more details.</p> <p>e. According to the standard IEC 62471:2006, Photobiological safety of Lamps and Lamp Systems</p>					

Spectrum	Specs	Drawing	Collimation Adapter
			
<p>This LED features a Ø30.5 mm heat sink.</p>			

Spectrum

Specs

Drawing

Collimation Adapter

This mounted LED is compatible with a number of collimation adapters for microscope and SM2 compatibility, as well as a DIY adapter assembly that features a small profile and SM1 compatibility.

### Collimation Adapters (2" Optic)

Type	Microscope Adapters				Adjustable Adapter
Compatibility	Olympus BX & IX <sup>a</sup>	Leica DMI	Zeiss Axioskop & Examiner <sup>b</sup>	Nikon Eclipse	SM2
Item #	COP1-A	COP2-A	COP4-A	COP5-A	SM2F32-A
Included Lens	ACL50832U-A Aspheric Condenser Lens				

- a. Please note that, due to the optical design of the transmitted lamphouse port of the BX and IX microscopes, it may be necessary to purchase a separate adapter which is available from Olympus.  
 b. These adapters are compatible with any Zeiss microscopes that use the same dovetail as the Zeiss Axioskop or Examiner microscopes.

### DIY SM1-Threaded Collimation Assembly (1" Optic)

Item #	Qty.	Description
<a href="#">ACL2520U-A</a> or <a href="#">ACL2520U-DG6-A</a>	1	Aspheric Condenser Lens (with or without Diffuser)
<a href="#">SM1V05<sup>a</sup></a>	1	Ø1" Rotating Adjustable Length Lens Tube, 1/2" Long
<a href="#">SM1L03<sup>a</sup></a>	1	Ø1" Lens Tube, 0.30" Long
<a href="#">SPW801</a>	1	Adjustable Spanner Wrench

- a. The [SM1V10](#) Adjustable Lens Tube can be substituted for both the [SM1V05](#) and [SM1L03](#); however, the translation range of the optic cell will be reduced from 7.6 mm to 6 mm, and an additional [SM1RR](#) retaining ring must be purchased.

#### DIY Collimation Assembly Instructions

To install the optic in the adjustable lens tube, first use the spanner wrench ([SPW801](#)) to adjust a retaining ring ([SM1RR](#)) fitted in the lens tube so that it is closer to the inside lip of the tube. Carefully place the lens inside the lens tube with the curved side facing away from the male-threaded end of the tube.

Secure the lens in place with another retaining ring ([SM1RR](#)) using the spanner wrench. Note: Do not use the [SPW602](#) spanner wrench, as the thin [SM1RR](#) retaining ring does not provide sufficient clearance for the [SPW602](#) to avoid scratching the steeply curved surface of the lens.

Thread the [SM1L03](#) lens tube into the LED and gently tighten it. Partially thread the [SM1V05](#) adjustable length lens tube assembly into the LED assembly.

